


## **TOP VIEW**



## SIDE VIEW



## **BOTTOM VIEW**



Specifications			Notes		Revision History					
Description	Value	Unit	Notes		Version		Description			Approved
Technology	Electro-Mechanical		1) All dimensions are in mm unless otherwise noted		1	Released from Engineering			10/21/2013	J.S
Resonant Frequency	2,731	(Hz)	2) All parts meet RoHS							
Rated Voltage	3	(V)								
SPL @ 10cm	82	(dBA)								
Coil Resistance	20	(ohm)								
Mount Type	Thru Hole									
Voltage Range	2~5	(V)								
Max Rated Current	70	(mA)								
Housing Material	NORYL				Drawn by	Date	Checked by	Date	Approved by	Date
Operating Temperature	-20 ~ +70	°C			A.B.	10/21/2013	C.E.	10/21/2013	J.S	10/21/2013
Storage Temperature	-20 ~ +70	°C		Electro-Mechanical Trans	nical Transducer TE092703-2					
Weight	0.6	(g)		Lietti o-ivietiiaiiitai Traiisuutei		1 EU32/U3-Z				

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.