


		1		
Part Number:		DRAWN	5/20/2019	
TE122	312-3	CJ		
10122		CHECKED	5/21/2019	
		C.H.		
Description:	anical Indicator	APPROVED	5/21/2019	
Liecti o-Mech	ariicai Iriuicatoi	C.E.	3/21/2013	
Electro-Mech	anicai indicator	C.E.	3/21/2019	


This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.


Top View



Side View



Bottom View



Items	Specifications	Conditions						
Min. Sound Pressure Level	85	dB (@ 10cm)		REVISION HISTO	TORY			
Tone	Single		REV	DESCRIPTION	DATE	APPROVED		
Resonant Frequency	2,300	Hz		Released from Engineering	10/21/0213	J.S.		
Rated Voltage	12	V		Updated drawing template, temps, voltage range,	5/21/2019	C.F.		
Voltage Range	8 ~ 16	V	1	diameter, pin length, housing, weight		C.E.		
Max. Rated Current	30	mA	2	Updated SPL, diameter, length, wash tab, added	9/22/2022	P.D.		
Storage Temperature	-40 ~ +90	°C		tolerances		P.D.		
Operating Temperature	-40 ~ +85	°C		NOTES				
Connection Method	PC Pins			All dimensions are in mm unless otherwise noted				
Mount Type	Thru Hole			2) All tolerances are ± 0.5 mm unless otherwise noted				
Housing Material	PBT			3) All parts meet RoHS				
Weight	1.8	g		4) Subject to change or redrawn without notice				