SIEMENS

product brand name

Data sheet 3SE5212-0CK60

SIRIUS



Position switch Metal enclosure according to EN 50047, 31 mm Device connection 1 x (M20 x 1.5) 1 NO/1 NC quick action contacts adjustable-length twist lever with positive fit (grid hole) right/left adjustable with plastic roller 19 mm

product branch			
product designation	Mechanical position switches		
product type designation	3SE5		
manufacturer's article number			
 of the supplied actuator head for position switches 	3SE5000-0AK00		
 of the supplied operating lever 	3SE5000-0AA60		
 of the supplied switching contacts 	3SE5000-0CA00		
 of the supplied empty enclosure with cover 	3SE5212-0AC05		
suitability for use safety switch	Yes		
General technical data			
product function positive opening	Yes		
insulation voltage rated value	400 V		
degree of pollution	class 3		
surge voltage resistance rated value	6 kV		
protection class IP	IP66/IP67		
shock resistance			
according to IEC 60068-2-27	30g / 11 ms		
vibration resistance			
according to IEC 60068-2-6	0.35 mm/5g		
mechanical service life (switching cycles) typical	15 000 000		
electrical endurance (switching cycles) at AC-15 at 230 V typical	100 000		
electrical endurance (switching cycles) with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026 typical	10 000 000		
Electrical operating cycles in one hour with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026	6 000		
thermal current	10 A		
material of the enclosure of the switch head	metal		
reference code according to IEC 81346-2	В		
continuous current of the C characteristic MCB	1 A; for a short-circuit current smaller than 400 A		
continuous current of the quick DIAZED fuse link	10 A; for a short-circuit current smaller than 400 A		
continuous current of the DIAZED fuse link gG	6 A		
active principle	mechanical		
repeat accuracy	0.05 mm		
Substance Prohibitance (Date)	07/01/2006		
minimum actuating torque in directions of actuation	0.25 N·m		
length of the sensor	182 mm		
width of the sensor	31 mm		
design of the switching contact	mechanical		

operating frequency rated value	50 60 Hz		
number of NC contacts for auxiliary contacts	1		
number of NO contacts for auxiliary contacts	1		
operational current at AC-15			
at 24 V rated value	6 A		
at 120 V rated value	6 A		
at 240 V rated value	6 A		
at 400 V rated value	4 A		
operational current at DC-13			
at 24 V rated value	3 A		
at 125 V rated value	0.55 A		
at 250 V rated value	0.27 A		
at 400 V rated value	0.12 A		
design of the interface for safety-related communication	without		
Enclosure			
design of the housing	block, narrow		
material of the enclosure	metal		
coating of the enclosure	cathodic dip coating		
design of the housing according to standard	Yes		
Drive Head			
design of the actuating element	Adjustable twist lever, adjustable-length metal lever with positive fit, 100		
design of the actualing element	mm long, plastic roller 19 mm		
standard-compliant actuator head	EN 50047, design A		
shape of the switch head	roller		
design of the switching function	positive opening		
circuit principle	snap-action contacts		
number of switching contacts safety-related	1		
Connections/ Terminals			
type of electrical connection	screw-type terminals		
type of connectable conductor cross-sections			
• solid	1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²)		
 finely stranded with core end processing 	1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²)		
 at AWG cables solid 	1x (20 16), 2x (20 18)		
at AWG cables stranded	1x (20 16), 2x (20 18)		
cable entry type	1x (M20 x 1.5)		
Communication/ Protocol			
design of the interface	without		
Ambient conditions			
ambient temperature			
during operation	-25 +85 °C		
during storage	-40 +90 °C		
explosion protection category for dust	none		
Installation/ mounting/ dimensions			
mounting position	any		
fastening method	screw fixing		
Certificates/ approvals			
General Product Approval			



Confirmation









Functional Safety/Safety of Machinery	Declaration of Conformity	Test Certificates	other
---	---------------------------	-------------------	-------





Type Test Certificates/Test Report

Confirmation

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE5212-0CK60


Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE5212-0CK60

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3SE5212-0CK60

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SE5212-0CK60&lang=en



last modified:

3/23/2022