



Product Specification

Ningbo East Electronics Limited

NO. 88 East Jinhui Road, Yinzhou Ningbo 315100, P.R. China http://www.east-mingtao.com

| Product Name: | External-Driven Piezo Transducer |
|---------------|----------------------------------|
| Part Number: | TFM-01 |
| Version: | 1.03 |
| Date: | 2019-11-4 |
| Note: | |


East is an ISO 9001, IATF16949 and ISO 14001Certified Company

Revision History

| Rev. | Description | Author/Date | Checked By | Approver |
|------|------------------------------------|------------------|------------|----------|
| 1.03 | Quality management system revised | 汤礼东 2019-11-4 | 吕文斌 | 王建成 |
| 1.02 | Quality Certificate Symbol revised | 刘宁 2015-2-6 | 汤礼东 | 王建成 |
| 1.01 | Wire changed | 汤礼东 2011-6-17 | 张春雷 | 王建成 |

1. Part Number TFM-01

2. Dimension Drawing (Unit: mm)




3. Specification

| No. | Item | Specification |
|-----|---------------------------|--------------------------------------|
| 3-1 | Min. Sound Pressure Level | 75dB/1.3kHz/12Vp-p square wave /30cm |
| 3-2 | Allowed Input Voltage | 40Vp-p |
| 3-3 | Capacitance | 45±30%nF(At 120Hz) |
| 3-4 | Max. Consumption | 3.5mA/1.3kHz/12Vp-p square wave |
| 3-5 | Resonant Frequency | 1.3± 0.5kHz |
| 3-6 | Operating Temperature | -20~+70°C |
| 3-7 | Case Material /Color | ABS/BLACK |
| 3-8 | Weight | 3.6g |
| 3-9 | Wire Standard | UL1095-28AWG |

NOTES:

Test should be made under the conditions of room temperature $(20\pm10^{\circ}\text{C})$, normal humidity $(60\pm20\%)$ and normal atmospheric pressure. In this case, however, that the judgment is questionable, the test conditions are to be changed to room temperature $20\pm2^{\circ}\text{C}$, relative humidity $60\sim70\%$ and normal atmospheric pressure

4.Typical Frequency Response Curve



Note: Input Voltage 12Vp-p square wave


Distance 30 cm

5. Reliability Test


| No. | Item | Method of Test | Tolerance after Testing | |
|-----|---------------------------------------|---|---|--|
| 5-1 | Operating Temperature | -20~+70°C | Sound pressure level initial value ±10dB Max. consumption value ±20% Capacitance value ±20% | |
| 5-2 | Storage in high temperature | Storage in +70°C test box 96 hours then exposed to the room temperature for 2 hours | | |
| 5-3 | Storage in low temperature | Storage in -20°C test box 96 hours then exposed to the room temperature for 2 hours | | |
| 5-4 | Life test in the room temperature | Operate the product continuously 5 seconds on 5 seconds off 300 hours at rated voltage | | |
| 5-5 | Temperature / humidity cycle test | Storage in +40°C, 93±3%RH test box 96 hours then exposed to the room temperature for 2 hours | | |
| 5-6 | Temperature (high and low) cycle test | Conduct the test for 5 cycles without applying power then expose to the room temperature for 2 hours.(See Figure 5-6) | | |

| 5-7 | Vibration test | Conduct the test for the directions of X Y and Z for 0.5 hour each (total 1.5 hours). To-and Fri sweep time(from 10 to 55Hz and then 55 to 10) under single amplitude of 0.75mm is 3 minute, then expose to the room temperature for 2 hours |
|-----|----------------|--|
| 5-8 | Drop test | Drop a product naturally from the height of 700mm onto the surface of 100mm thick wooden board. Two directions: upper and side of the product are to be applied for this drop test once respectively |

Figure 5-6



6. Electrical Testing Method



| S.P.L.M | Sound Pressure Level Meter |
|---------|-------------------------------|
| T.S | Testing Sample |
| F.C | Frequency Counter |
| F.S.G | Frequency Signal Generator |
| A.V.M | AC Voltage Meter |
| A.A.M | AC Ampere Meter |

7. Packing Information

Packing:3200 pcs per export carton

Carton Size: 47× 30.5×19cm

G. Weight: 13.0 kgs N. Weight: 11.5 kgs