SIEMENS

Data sheet

3SE5212-0PC05-1CA0



Position switch with increased corrosion protection Metal enclosure according to EN 50047, 31 mm Device connection 1 x (M20 x 1.5) 2 NO/1 NC slow-action contacts Teflon plunger

product brand name	SIRIUS		
product designation	Mechanical position switches		
product type designation	3SE5		
manufacturer's article number			
 of the supplied switching contacts 	<u>3SE5000-0PA00</u>		
 of the supplied empty enclosure with cover 	<u>3SE5212-0AC05-1CA0</u>		
suitability for use safety switch	Yes		
General technical data			
product function positive opening	Yes		
insulation voltage rated value	250 V		
degree of pollution	class 3		
surge voltage resistance rated value	4 kV		
protection class IP	IP66/IP67		
shock resistance			
 according to IEC 60068-2-27 	30g / 11 ms		
vibration resistance			
 according to IEC 60068-2-6 	0.35 mm/5g		
mechanical service life (switching cycles) typical	15 000 000		
electrical endurance (switching cycles) at AC-15 at 230 V typical	100 000		
electrical endurance (switching cycles) with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026 typical	10 000 000		
Electrical operating cycles in one hour with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026	6 000		
thermal current	10 A		
material of the enclosure of the switch head	metal		
reference code according to IEC 81346-2	В		
continuous current of the C characteristic MCB	1 A; for a short-circuit current smaller than 400 A		
continuous current of the quick DIAZED fuse link	10 A; for a short-circuit current smaller than 400 A		
continuous current of the DIAZED fuse link gG	6 A		
active principle	mechanical		
repeat accuracy	0.05 mm		
Substance Prohibitance (Date)	07/01/2006		
minimum actuating force in directions of actuation	20 N		
length of the sensor	75.7 mm		
width of the sensor	31 mm		
design of the switching contact	mechanical		
operating frequency rated value	50 60 Hz		
number of NC contacts for auxiliary contacts	1		

General Product Approval	Safety/Safety of Machinery	Declaration of	of comorning		
	Functional		of Conformity	Test Certificates	CUL
	(Confirmatio	<u> </u>	KC	FAC
General Product App	roval				
fastening method Certificates/ approvals					
mounting position			any screw fixing		
Installation/ mounting/	dimensions				
· ·			none		
• during storage explosion protection category for dust		-40 +90 °C			
during operation		-25 +85 °C			
ambient temperature					
Ambient conditions					
design of the interfac			without		
Communication/ Protoc	col		(
• at AWG cables s	แลกแอน		1x (20 16), 2x (20 . 1x (M20 x 1.5)	10)	
 at AWG cables se at AWG cables si 			1x (20 16), 2x (20 . 1x (20 16), 2x (20 .		
-	ith core end processin	ıg	1x (0.5 1.5 mm ²), 2		
• solid	34h		1x (0.5 1.5 mm ²), 2		
type of connectable c	onductor cross-sect	ions			
type of electrical conr			screw-type terminals		
Connections/ Terminals	-				
number of switching co	ntacts safety-related		1		
circuit principle			slow-action contacts		
design of the switchir			positive opening		
shape of the switch h			rounded		
design of the actuating element standard-compliant actuator head		Rounded plunger, plastic plunger EN 50047, design B			
Drive Head			Dounded shusses sta	etie plunger	
design of the housing	according to standa	ard	Yes		
coating of the enclosu			cathodic dip coating		
material of the enclos	ure		metal		
design of the housing	J		block, narrow		
Enclosure	,				
design of the interface		munication	without		
 at 200 V rated value at 400 V rated value 			0.12 A		
 at 125 V rated va at 250 V rated va 			0.55 A 0.27 A		
 at 24 V rated valu at 125 V rated value 			3 A 0.55 A		
operational current at			2.4		
 at 400 V rated va 			4 A		
 at 240 V rated va 			6 A		
 at 120 V rated va 	llue		6 A		
 at 24 V rated value 	le		6 A		
operational current at	AC-15				

other

Confirmation

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE5212-0PC05-1CA0

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE5212-0PC05-1CA0

Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/3SE5212-0PC05-1CA0

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SE5212-0PC05-1CA0&lang=en

last modified:

3/23/2022 🖸