SIEMENS

Data sheet

3SU1200-6KC10-1AA0



acoustic signal device, compact, 22 mm, round, plastic, black, Continuous tone 2.4 kHz, IP40, Sound pressure min. 80 dB/10 cm, with holder, Operating voltage 110 V AC, screw terminal

product brand name	SIRIUS ACT
product designation	Acoustic signaling device
design of the product	Compact unit
product type designation	3SU1
product line	Plastic, black, 22 mm
manufacturer's article number of the supplied holder	3SU1550-0AA10-0AA0
Enclosure	
number of command points	1
Actuator	
color of the actuating element	black
material of the actuating element	plastic
shape of the actuating element	round
outer diameter of the actuating element	29.5 mm
Front ring	
product component front ring	No
Holder	
material of the holder	Plastic
General technical data	
loudness level at 10 cm distance	80 dB
insulation voltage rated value	320 V
degree of pollution	3
surge voltage resistance rated value	4 kV
consumed current at rated value of operating voltage maximum	32 mA
protection class IP	IP40
 of the terminal 	IP20, clamping screw tightened
degree of protection NEMA rating	1
shock resistance	
 according to IEC 60068-2-27 	sinusoidal half-wave 15g / 11 ms
 for railway applications according to EN 61373 	Category 1, Class B
vibration resistance	
 according to IEC 60068-2-6 	10 500 Hz: 5g
 for railway applications according to EN 61373 	Category 1, Class B
reference code according to IEC 81346-2	P
Substance Prohibitance (Date)	10/01/2014
relative positive tolerance of the operating voltage	20 %
relative negative tolerance of the operating voltage	20 %
Supply voltage	
type of voltage of the supply voltage of the acoustic signal	AC

element					
supply voltage at AC					
at 50 Hz rated value	110	110 V			
• at 60 Hz rated value	110	110 V			
Control circuit/ Control					
inrush current maximum	3 A				
Connections/ Terminals					
type of electrical connection	scre	screw-type terminals			
type of connectable conductor cross-se	ections				
 solid with core end processing 	2x (2x (0.5 0.75 mm²)			
 solid without core end processing 	2x (2x (1.0 1.5 mm ²)			
 finely stranded with core end proces 	ssing 2x (2x (0.5 1.5 mm ²)			
 finely stranded without core end pro 	cessing 2x (2x (1,0 1,5 mm ²)			
at AWG cables	-	2x (18 14)			
tightening torque of the screws in the b		1 1.2 N·m			
tightening torque with screw-type terminal		0.8 1 N·m			
Ambient conditions					
ambient temperature					
 during operation 	-25	-25 +70 °C			
 during storage 	-40	-40 +80 °C			
environmental category during operation a 60721		3M6, 3S2, 3B2, 3K6 (with relative air humidity of 10 95%, no condensation in operation permitted for all devices behind front panel)			
Installation/ mounting/ dimensions				, ,	
fastening method	fron	front plate mounting			
height	40 r	40 mm			
width	30 r	30 mm			
shape of the installation opening	rour	round			
mounting diameter	22.3	22.3 mm			
positive tolerance of installation diame	ter 0.4	0.4 mm			
mounting height	11.4	11.4 mm			
installation width	29.5	29.5 mm			
installation depth	49.6	49.6 mm			
Certificates/ approvals					
General Product Approval				Declaration of Conformity	
	<u>Confirmation</u>		EHC	UK CA	
Declaration of Conformity Test Certificates		other			

 Declaration of Conformity
 Test Certificates
 other

 Image: Conformity
 Type Test Certificates/Test Report
 Special Test Certificate
 Environmental Confirmations
 Confirmation

Further information

Information- and Downloadcenter (Catalogs, Brochures,...) https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1200-6KC10-1AA0

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1200-6KC10-1AA0

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3SU1200-6KC10-1AA0

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1200-6KC10-1AA0&lang=en last modified:

1/26/2022 🖸