		TOP	VIEW	SIDE V	IEW				
	<u>Ø19±0.2</u>		Ø27±0.10		0.41±0.1 0.20±0.05				
Spo	ecifications				. 	 Revisic	n History		
Spe Description	ecifications Value	Unit	No	otes	Version	 Revisio Description	-	Date	Approved
		Unit (Hz)	Nc 1) All dimensions are in mm unl		Version 1		-	Date 10/21/2013	Approved J.S
Description	Value					Description	-		
Description Resonant Frequency	Value 4,200	(Hz)	1) All dimensions are in mm unl			Description	-		
Description Resonant Frequency Resonant Impedance (Max)	Value 4,200 500	(Hz) (Ohm)	1) All dimensions are in mm unl			Description	-		
Description Resonant Frequency Resonant Impedance (Max) Max Input Voltage	Value 4,200 500 30	(Hz) (Ohm) (V)	1) All dimensions are in mm unl			Description	-		
Description Resonant Frequency Resonant Impedance (Max) Max Input Voltage Capacitance	Value 4,200 500 30 18,000	(Hz) (Ohm) (V)	1) All dimensions are in mm unl			Description	-		
Description Resonant Frequency Resonant Impedance (Max) Max Input Voltage Capacitance Plate Material	Value 4,200 500 30 18,000 Brass	(Hz) (Ohm) (V) (pF)	1) All dimensions are in mm unl			Description	-		
Description Resonant Frequency Resonant Impedance (Max) Max Input Voltage Capacitance Plate Material Operating Temperature	Value 4,200 500 30 18,000 Brass -20~+60	(Hz) (Ohm) (V) (pF) C	1) All dimensions are in mm unl			Description	-		

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.