

Rochester Electronics Manufactured Components

Rochester branded components are manufactured using either die/wafers purchased from the original suppliers or Rochester wafers recreated from the original IP. All recreations are done with the approval of the OCM.

Parts are tested using original factory test programs or Rochester developed test solutions to guarantee product meets or exceed the OCM data sheet.

Quality Overview

- ISO-9001
- AS9120 certification
- Qualified Manufacturers List (QML) MIL-PRF-35835
 - Class Q Military
 - Class V Space Level
- Qualified Suppliers List of Distributors (QSLD)

• Rochester is a critical supplier to DLA and meets all industry and DLA standards.

Rochester Electronics, LLC is committed to supplying products that satisfy customer expectations for quality and are equal to those originally supplied by industry manufacturers.

The original manufacturer's datasheet accompanying this document reflects the performance and specifications of the Rochester manufactured version of this device. Rochester Electronics guarantees the performance of its semiconductor products to the original OEM specifications. 'Typical' values are for reference purposes only. Certain minimum or maximum ratings may be based on product characterization, design, simulation, or sample testing.

TYPES SN54H102, SN74H102 AND-GATED J-K NEGATIVE-EDGE-TRIGGERED FLIP-FLOPS WITH PRESET AND CLEAR REVISED DECEMBER 1983

Package Options Include Plastic and Ceramic DIPs

 Dependable Texas Instruments Quality and Reliability

description

These monolithic J-K flip-flops are negative-edgetriggered. They feature gated J-K inputs and an asynchronous clear input. The AND gate inputs are inhibited while the clock input is low; when the clock goes high, the inputs are enabled and data will be accepted. Logical state of J and K inputs may be allowed to change when the clock pulse is in a high state and bistable will perform according to the truth table as long as minimum set-up times are observed. Input data is transferred to the outputs on the negative edge of the clock pulse.

The SN54H102 is characterized for operation over the full military temperature range of -55 °C to 125 °C. The SN74H102 is characterized for operation from 0 °C to 70 °C.

FUNCTION TABLE

	INP	ουτι	PUTS			
PRE	CLR	CLK	J	к	Q	ā
L	н	×	x	х	н	L
н	L	×	х	х	1 .	н
L	L	×	×	х	н†	н†
н	н	Ļ	L	L.	0 ₀	$\overline{\Omega}_0$
н	н	4	н	L	н	L
н	н	1	L	н	L	н
н	н	Ļ	н	н	100	IGLE
н	н	н	х	х	Ω ₀	<u>a</u> 0

† This configuration is nonstable; that is, it will not persist when preset and clear inputs return to their inactive (high) level.

positive logic

J = J1•J2•J3 K = K1•K2•K3

SN54H102 J PACKAGE
SN74H102 J OR N PACKAGE
(TOP VIEW)


	U14 Vcc
	13 PRE
J1 🗖 3	12 CLK
J2 []́4	11Д КЗ
J <u>3</u> 🛛 5	10] K2
Q 🗖 e	9Д К1
GND 7	8] Q

SN54H102 ... W PACKAGE (TOP VIEW)

К1	Сı	1	U 14	þ	кз
CLK	d:	2	13	þ	K2
PRE	4	3	12	þ	٥
Vcc	Ľ	4	11	þ	GND
CLR	d:	5	10	þ	ā
NC	d	6	9	þ	J3
J1	d.	7	8	þ	J2

NC - No internal connection

logic symbol




Pin numbers shown are for J and N packages.





TYPES SN54H102, SN74H102 AND-GATED J-K NEGATIVE-EDGE-TRIGGERED FLIP-FLOPS WITH PRESET AND CLEAR

logic diagram



schematics of inputs and outputs





absolute maximum ratings over operating free-air temperature range (unless otherwise noted)

Supply voltage, VCC (see Note 1)	
Input voltage	5.5 V
Operating free-air temperature range:	SN54H'
	SN74H',
Storage temperature range	$-65^{\circ}C$ to $150^{\circ}C$

NOTE 1: Voltage values are with respect to network ground terminal.



TYPES SN54H102, SN74H102 AND-GATED J-K NEGATIVE-EDGE-TRIGGERED FLIP-FLOPS WITH PRESET AND CLEAR

recommended operating conditions

				SN54H1	02	5	N74H1	02	UNIT
			MIN	NOM	MAX	MIN	NOM	MAX	UNIT
Vcc	Supply voltage		4.5	5	5.5	4.75	5	5.25	V
VIH	High-level input voltage		2			2			V
VIL	Low-level input voltage			_	0.8			0.8	V
юн	High-level output current				0.5			- 0.5	mA
^I OL	Low-level output current				20			20	mA
	High-level input voltage Low-level input voltage High-level output current	CLK high	10			10			
tw		CLK low	15			15			ns
		CLR or PRE low	16			16			ļ
		High-level data	10			10			
t _{su}	Setup time before CLK \$	Low-level data	13			13			ns
t _h	Hold time-data after CLK 4		0			0			ns
TA	Operating free-air temperature		- 55		125	0		70	°c

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

PARAMETER		TEST CONDITIONS [†]			SN54H1)2	5	UNIT			
FARA	AMETER		STCONDITION	N2 '	MIN	TYP‡	MAX	MIN	TYP‡	MAX	UNIT
Viк		V _{CC} = MIN,	l₁ = − 8 m A				- 1.5			- 1.5	V
∨он		V _{CC} = MIN, I _{OH} = - 0.5 mA	V _{IH} = 2 V,	V _{IL} = 0.8 V,	2.4	3.4		2.4	3.4		v
VOL		V _{CC} = MIN, I _{OL} = 20 mA	V _{IH} = 2 V,	V _{IL} = 0.8 V,		0.2	0.4		0.2	0.4	v
t _l		V _{CC} = MAX,	V ₁ = 5.5 V				1			1	mΑ
	Any J or K	Vcc = MAX,			_	50			50		
1	CLR					100			100	μA	
Чн	PRE	VCC - MAX,	V - 2.4 V			_	100			100	
	CLK				0		- 1	0		- 1	mA
	Any J or K					- 1	- 2		- 1	- 2	
1	CLR	V _{CC} = MAX,	$M_{\rm H} = 0.4 M$		- 1	- 2	-	- 1	- 2]	
μL	PRE		v] - 0.4 v			- 1	- 2		- 1	- 2	mA
	CLK					- 3	4.8		3	- 4.8	
los§		V _{CC} = MAX			- 40		- 100	- 40		- 100	mA
lcc		V _{CC} = MAX,	See Note 2			20	38		20	38	mA

† For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions.

[‡] All typical values are at $V_{CC} = 5 V$, $T_A = 25^{\circ}C$.

§ Not more than one output should be shorted at a time, and duration of short-circuit should not exceed one second.

NOTE 2: With all outputs open, I_{CC} is measured with the Q and \overline{Q} outputs high in turn. At the time of measurement, the clock input is grounded,

switching characteristics, VCC = 5 V, TA = 25° C (see note 3)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	TEST CONDITIONS	MIN	ТҮР	мах	UNIT
fmax				40	50		MHz
^t PLH	PRE or CLR	Q or Q	B 380 C		8	12	ns
	PRE or CLR (CLK high)	Q or Q	RL = 280 Ω, CL = 25 pF		15	20	
^t PHL	PRE or CLR (CLK low)	uoru			23	35	ns
^t PLH	CLK	Qorā			10	15	
^t PHL	ULK	u or u			16	20	ns

NOTE 3: See General Information Section for load circuits and voltage waveforms.

