



**MOTOROLA**

**MC74AC74  
MC74ACT74**

**Dual D-Type Positive  
Edge-Triggered Flip-Flop**


The MC74AC74/74ACT74 is a dual D-type flip-flop with Asynchronous Clear and Set inputs and complementary (Q,  $\bar{Q}$ ) outputs. Information at the input is transferred to the outputs on the positive edge of the clock pulse. Clock triggering occurs at a voltage level of the clock pulse and is not directly related to the transition time of the positive-going pulse. After the Clock Pulse input threshold voltage has been passed, the Data input is locked out and information present will not be transferred to the outputs until the next rising edge of the Clock Pulse input.

**Asynchronous Inputs:**

- LOW input to  $\bar{S}_D$  (Set) sets Q to HIGH level
- LOW input to  $\bar{C}_D$  (Clear) sets Q to LOW level
- Clear and Set are independent of clock
- Simultaneous LOW on  $\bar{C}_D$  and  $\bar{S}_D$  makes both Q and  $\bar{Q}$  HIGH

- Outputs Source/Sink 24 mA
- 'ACT74 Has TTL Compatible Inputs

**LOGIC SYMBOL**



**PIN NAMES**


- D<sub>1</sub>, D<sub>2</sub> Data Inputs
- CP<sub>1</sub>, CP<sub>2</sub> Clock Pulse Inputs
- $\bar{C}_D1$ ,  $\bar{C}_D2$  Direct Clear Inputs
- $\bar{S}_D1$ ,  $\bar{S}_D2$  Direct Set Inputs
- Q<sub>1</sub>,  $\bar{Q}_1$ , Q<sub>2</sub>,  $\bar{Q}_2$  Outputs

**TRUTH TABLE (Each Half)**


| Inputs      |             |            |   | Outputs        |             |
|-------------|-------------|------------|---|----------------|-------------|
| $\bar{S}_D$ | $\bar{C}_D$ | CP         | D | Q              | $\bar{Q}$   |
| L           | H           | X          | X | H              | L           |
| H           | L           | X          | X | L              | H           |
| L           | L           | X          | X | H              | H           |
| H           | H           | $\uparrow$ | H | H              | L           |
| H           | H           | $\uparrow$ | L | L              | H           |
| H           | H           | L          | X | Q <sub>0</sub> | $\bar{Q}_0$ |

- H - HIGH Voltage Level
- L - LOW Voltage Level
- X - Immaterial
- $\uparrow$  - LOW-to-HIGH Clock Transition
- Q<sub>0</sub>( $\bar{Q}_0$ ) - Previous Q( $\bar{Q}$ ) before LOW-to-HIGH Transition of Clock


**DUAL D-TYPE POSITIVE  
EDGE-TRIGGERED  
FLIP-FLOP**




**N SUFFIX  
CASE 646-06  
PLASTIC**



**D SUFFIX  
CASE 751A-02  
PLASTIC**



## MC74AC74 • MC74ACT74



Please note that this diagram is provided only for the understanding of logic operations and should not be used to estimate propagation delays.

### MAXIMUM RATINGS\*

| Symbol    | Parameter                                 | Value                  | Unit |
|-----------|-------------------------------------------|------------------------|------|
| $V_{CC}$  | DC Supply Voltage (Referenced to GND)     | 0.5 to +7.0            | V    |
| $V_{in}$  | DC Input Voltage (Referenced to GND)      | -0.5 to $V_{CC} + 0.5$ | V    |
| $V_{out}$ | DC Output Voltage (Referenced to GND)     | -0.5 to $V_{CC} + 0.5$ | V    |
| $I_{in}$  | DC Input Current, per Pin                 | +20                    | mA   |
| $I_{out}$ | DC Output Sink/Source Current, per Pin    | ±50                    | mA   |
| $I_{CC}$  | DC $V_{CC}$ or GND Current per Output Pin | ±50                    | mA   |
| $T_{stg}$ | Storage Temperature                       | -65 to +150            | °C   |

\*Maximum Ratings are those values beyond which damage to the device may occur. Functional operation should be restricted to the Recommended Operating Conditions.

### RECOMMENDED OPERATING CONDITIONS

| Symbol            | Parameter                                                               | Min                | Typ | Max      | Unit |   |
|-------------------|-------------------------------------------------------------------------|--------------------|-----|----------|------|---|
| $V_{CC}$          | Supply Voltage                                                          | 'AC                | 2.0 | 5.0      | 6.0  | V |
|                   |                                                                         | 'ACT               | 4.5 | 5.0      | 5.5  |   |
| $V_{in}, V_{out}$ | DC Input Voltage, Output Voltage (Ref. to GND)                          | 0                  |     | $V_{CC}$ | V    |   |
| $t_r, t_f$        | Input Rise and Fall Time (Note 1)<br>'AC Devices except Schmitt Inputs  | $V_{CC}$ (a 3.0 V) |     | 150      | ns/V |   |
|                   |                                                                         | $V_{CC}$ (a 4.5 V) |     | 40       |      |   |
|                   |                                                                         | $V_{CC}$ (a 5.5 V) |     | 25       |      |   |
| $t_r, t_f$        | Input Rise and Fall Time (Note 2)<br>'ACT Devices except Schmitt Inputs | $V_{CC}$ (a 4.5 V) |     | 10       | ns/V |   |
|                   |                                                                         | $V_{CC}$ (a 5.5 V) |     | 8.0      |      |   |
| $T_J$             | Junction Temperature (PDIP)                                             |                    |     | 140      | °C   |   |
| $T_A$             | Operating Ambient Temperature Range                                     | -40                | 25  | 85       | °C   |   |
| $I_{OH}$          | Output Current — High                                                   |                    |     | -24      | mA   |   |
| $I_{OL}$          | Output Current — Low                                                    |                    |     | 24       | mA   |   |

1.  $V_{in}$  from 30% to 70%  $V_{CC}$ ; see individual Data Sheets for devices that differ from the typical input rise and fall times.
2.  $V_{in}$  from 0.8 V to 2.0 V; see individual Data Sheets for devices that differ from the typical input rise and fall times.

MC74AC74 • MC74ACT74

DC CHARACTERISTICS

| Symbol | Parameter                         | VCC (V) | 74AC       |                   | 74ACT               |  | Units | Conditions                                             |
|--------|-----------------------------------|---------|------------|-------------------|---------------------|--|-------|--------------------------------------------------------|
|        |                                   |         | TA = +25°C |                   | TA = -40°C to +85°C |  |       |                                                        |
|        |                                   |         | Typ        | Guaranteed Limits |                     |  |       |                                                        |
| VIH    | Minimum High Level Input Voltage  | 3.0     | 1.5        | 2.1               | 2.1                 |  | V     | VOUT = 0.1 V or VCC - 0.1 V                            |
|        |                                   | 4.5     | 2.25       | 3.15              | 3.15                |  |       |                                                        |
|        |                                   | 5.5     | 2.75       | 3.85              | 3.85                |  |       |                                                        |
| VIL    | Maximum Low Level Input Voltage   | 3.0     | 1.5        | 0.9               | 0.9                 |  | V     | VOUT = 0.1 V or VCC - 0.1 V                            |
|        |                                   | 4.5     | 2.25       | 1.35              | 1.35                |  |       |                                                        |
|        |                                   | 5.5     | 2.75       | 1.65              | 1.65                |  |       |                                                        |
| VOH    | Minimum High Level Output Voltage | 3.0     | 2.99       | 2.9               | 2.9                 |  | V     | IOUT = 50 μA                                           |
|        |                                   | 4.5     | 4.49       | 4.4               | 4.4                 |  |       |                                                        |
|        |                                   | 5.5     | 5.49       | 5.4               | 5.4                 |  |       |                                                        |
|        |                                   | 3.0     |            | 2.56              | 2.46                |  | V     | *VIN = VIL or VIH<br>- 12 mA<br>IOH - 24 mA<br>- 24 mA |
|        |                                   | 4.5     |            | 3.86              | 3.76                |  |       |                                                        |
|        |                                   | 5.5     |            | 4.86              | 4.76                |  |       |                                                        |
| VOL    | Maximum Low Level Output Voltage  | 3.0     | 0.002      | 0.1               | 0.1                 |  | V     | IOUT = 50 μA                                           |
|        |                                   | 4.5     | 0.001      | 0.1               | 0.1                 |  |       |                                                        |
|        |                                   | 5.5     | 0.001      | 0.1               | 0.1                 |  |       |                                                        |
|        |                                   | 3.0     |            | 0.36              | 0.44                |  | V     | *VIN = VIL or VIH<br>12 mA<br>IOL 24 mA<br>24 mA       |
|        |                                   | 4.5     |            | 0.36              | 0.44                |  |       |                                                        |
|        |                                   | 5.5     |            | 0.36              | 0.44                |  |       |                                                        |
| IIN    | Maximum Input Leakage Current     | 5.5     |            | + 0.1             | + 1.0               |  | μA    | VI = VCC, GND                                          |
| IOLD   | †Minimum Dynamic Output Current   | 5.5     |            |                   | 75                  |  | mA    | VOLD = 1.65 V Max                                      |
| IOHD   |                                   | 5.5     |            |                   | 75                  |  | mA    | VOHD = 3.85 V Min                                      |
| ICC    | Maximum Quiescent Supply Current  | 5.5     |            | 4.0               | 40                  |  | μA    | VIN = VCC or GND                                       |

\*All outputs loaded, thresholds on input associated with output under test.

†Maximum test duration 2.0 ms, one output loaded at a time.

Note: IIN and ICC at 3.0 V are guaranteed to be less than or equal to the respective limit at 5.5 V VCC.

MC74AC74 • MC74ACT74

DC CHARACTERISTICS

| Symbol | Parameter                         | VCC (V) | 74ACT      |                   | 74ACT               |  | Units | Conditions            |
|--------|-----------------------------------|---------|------------|-------------------|---------------------|--|-------|-----------------------|
|        |                                   |         | TA = +25°C |                   | TA = -40°C to +85°C |  |       |                       |
|        |                                   |         | Typ        | Guaranteed Limits |                     |  |       |                       |
| VIH    | Minimum High Level Input Voltage  | 4.5     | 1.5        | 2.0               | 2.0                 |  | V     | VOUT or VCC 0.1 V     |
|        |                                   | 5.5     | 1.5        | 2.0               | 2.0                 |  |       |                       |
| VIL    | Maximum Low Level Input Voltage   | 4.5     | 1.5        | 0.8               | 0.8                 |  | V     | VOUT or VCC 0.1 V     |
|        |                                   | 5.5     | 1.5        | 0.8               | 0.8                 |  |       |                       |
| VOH    | Minimum High Level Output Voltage | 4.5     | 4.49       | 4.4               | 4.4                 |  | V     | IOUT 50 μA            |
|        |                                   | 5.5     | 5.49       | 5.4               | 5.4                 |  |       |                       |
|        |                                   | 4.5     |            | 3.86              | 3.76                |  | V     | *VIN VIL or VIH 24 mA |
|        |                                   | 5.5     |            | 4.86              | 4.76                |  |       |                       |
| VOL    | Maximum Low Level Output Voltage  | 4.5     | 0.001      | 0.1               | 0.1                 |  | V     | IOUT 50 μA            |
|        |                                   | 5.5     | 0.001      | 0.1               | 0.1                 |  |       |                       |
|        |                                   | 4.5     |            | 0.36              | 0.44                |  | V     | *VIN VIL or VIH 24 mA |
|        |                                   | 5.5     |            | 0.36              | 0.44                |  |       |                       |
| IIN    | Maximum Input Leakage Current     | 5.5     |            | 0.1               | 1.0                 |  | μA    | VI VCC, GND           |
| ΔICCT  | Additional Max. ICC Input         | 5.5     | 0.6        |                   | 1.5                 |  | mA    | VI VCC 2.1 V          |
| IOLD   | †Minimum Dynamic Output Current   | 5.5     |            |                   | 75                  |  | mA    | VOID 1.65 V Max       |
| IOLD   |                                   | 5.5     |            |                   | 75                  |  | mA    | VOHD 3.85 V Min       |
| ICC    | Maximum Quiescent Supply Current  | 5.5     |            | 4.0               | 40                  |  | μA    | VIN VCC or GND        |

\*All outputs loaded; thresholds on input associated with output under test

†Maximum test duration 2.0 ms, one output loaded at a time

AC CHARACTERISTICS (Figures and Waveforms — See Section 3)

| Symbol | Parameter                                   | VCC* (V) | 74AC                     |      |      | 74AC                              |      | Units | Fig. No. |
|--------|---------------------------------------------|----------|--------------------------|------|------|-----------------------------------|------|-------|----------|
|        |                                             |          | TA = +25°C<br>CL = 50 pF |      |      | TA = -40°C to +85°C<br>CL = 50 pF |      |       |          |
|        |                                             |          | Min                      | Typ  | Max  | Min                               | Max  |       |          |
| fmax   | Maximum Clock Frequency                     | 3.3      | 100                      | 125  | 95   |                                   | MHz  | 3-3   |          |
|        |                                             | 5.0      | 140                      | 160  | 125  |                                   |      |       |          |
| tPLH   | Propagation Delay<br>CDN or SDN to Qn or Qn | 3.3      | 5.0                      | 8.0  | 12.0 | 4.0                               | 13.0 | ns    | 3-6      |
|        |                                             | 5.0      | 3.5                      | 6.0  | 9.0  | 3.0                               | 10.0 |       |          |
| tPHL   | Propagation Delay<br>CDN or SDN to Qn or Qn | 3.3      | 4.0                      | 10.5 | 12.0 | 3.5                               | 13.5 | ns    | 3-6      |
|        |                                             | 5.0      | 3.0                      | 8.0  | 9.5  | 2.5                               | 10.5 |       |          |
| tPLH   | Propagation Delay<br>CPn to Qn or Qn        | 3.3      | 4.5                      | 8.0  | 13.5 | 4.0                               | 16.0 | ns    | 3-6      |
|        |                                             | 5.0      | 3.5                      | 6.0  | 10.0 | 3.0                               | 10.5 |       |          |
| tPHL   | Propagation Delay<br>CPn to Qn or Qn        | 3.3      | 3.5                      | 8.0  | 14.0 | 3.5                               | 14.5 | ns    | 3-6      |
|        |                                             | 5.0      | 2.5                      | 6.0  | 10.0 | 2.5                               | 10.5 |       |          |

\*Voltage Range 3.3 is 3.3 V ± 0.3 V

Voltage Range 5.0 is 5.0 V ± 0.5 V

5

MC74AC74 • MC74ACT74

AC OPERATING REQUIREMENTS

| Symbol           | Parameter                                                            | V <sub>CC</sub> * (V) | 74AC                                             |                    | 74AC                                                         |    | Units | Fig. No. |
|------------------|----------------------------------------------------------------------|-----------------------|--------------------------------------------------|--------------------|--------------------------------------------------------------|----|-------|----------|
|                  |                                                                      |                       | T <sub>A</sub> = +25°C<br>C <sub>L</sub> = 50 pF |                    | T <sub>A</sub> = -40°C<br>to +85°C<br>C <sub>L</sub> = 50 pF |    |       |          |
|                  |                                                                      |                       | Typ                                              | Guaranteed Minimum |                                                              |    |       |          |
| t <sub>s</sub>   | Set-up Time, HIGH or LOW<br>D <sub>n</sub> to CP <sub>n</sub>        | 3.3<br>5.0            | 1.5<br>1.0                                       | 4.0<br>3.0         | 4.5<br>3.0                                                   | ns | 3-9   |          |
| t <sub>h</sub>   | Hold Time, HIGH or LOW<br>D <sub>n</sub> to CP <sub>n</sub>          | 3.3<br>5.0            | 2.0<br>1.5                                       | 0.5<br>0.5         | 0.5<br>0.5                                                   | ns | 3-9   |          |
| t <sub>w</sub>   | CP <sub>n</sub> or C <sub>Dn</sub> or S <sub>Dn</sub><br>Pulse Width | 3.3<br>5.0            | 3.0<br>2.5                                       | 5.5<br>4.5         | 7.0<br>5.0                                                   | ns | 3-6   |          |
| t <sub>rec</sub> | Recovery Time<br>C <sub>Dn</sub> or S <sub>Dn</sub> to CP            | 3.3<br>5.0            | 2.5<br>2.0                                       | 0<br>0             | 0<br>0                                                       | ns | 3-9   |          |

\*Voltage Range 3.3 is 3.3 V ± 0.3 V  
Voltage Range 5.0 is 5.0 V ± 0.5 V

AC CHARACTERISTICS (Figures and Waveforms — See Section 3)

| Symbol           | Parameter                                                                                    | V <sub>CC</sub> * (V) | 74ACT                                            |     |      | 74ACT                                                        |      | Units | Fig. No. |
|------------------|----------------------------------------------------------------------------------------------|-----------------------|--------------------------------------------------|-----|------|--------------------------------------------------------------|------|-------|----------|
|                  |                                                                                              |                       | T <sub>A</sub> = +25°C<br>C <sub>L</sub> = 50 pF |     |      | T <sub>A</sub> = -40°C<br>to +85°C<br>C <sub>L</sub> = 50 pF |      |       |          |
|                  |                                                                                              |                       | Min                                              | Typ | Max  | Min                                                          | Max  |       |          |
| f <sub>max</sub> | Maximum Clock Frequency                                                                      | 5.0                   | 145                                              | 210 |      | 125                                                          |      | MHz   | 3-3      |
| t <sub>PLH</sub> | Propagation Delay<br>C <sub>Dn</sub> or S <sub>Dn</sub> to Q <sub>n</sub> or Q̄ <sub>n</sub> | 5.0                   | 3.0                                              | 5.5 | 9.5  | 2.5                                                          | 10.5 | ns    | 3-6      |
| t <sub>PHL</sub> | Propagation Delay<br>C <sub>Dn</sub> or S <sub>Dn</sub> to Q <sub>n</sub> or Q̄ <sub>n</sub> | 5.0                   | 3.0                                              | 6.0 | 10.0 | 3.0                                                          | 11.5 | ns    | 3-6      |
| t <sub>PLH</sub> | Propagation Delay<br>CP <sub>n</sub> to Q <sub>n</sub> or Q̄ <sub>n</sub>                    | 5.0                   | 4.0                                              | 7.5 | 11.0 | 4.0                                                          | 13.0 | ns    | 3-6      |
| t <sub>PHL</sub> | Propagation Delay<br>CP <sub>n</sub> to Q <sub>n</sub> or Q̄ <sub>n</sub>                    | 5.0                   | 3.5                                              | 6.0 | 10.0 | 3.0                                                          | 11.5 | ns    | 3-6      |

\*Voltage Range 5.0 is 5.0 V ± 0.5 V

AC OPERATING REQUIREMENTS

| Symbol           | Parameter                                                            | V <sub>CC</sub> * (V) | 74ACT                                            |                    | 74ACT                                                        |    | Units | Fig. No. |
|------------------|----------------------------------------------------------------------|-----------------------|--------------------------------------------------|--------------------|--------------------------------------------------------------|----|-------|----------|
|                  |                                                                      |                       | T <sub>A</sub> = +25°C<br>C <sub>L</sub> = 50 pF |                    | T <sub>A</sub> = -40°C<br>to +85°C<br>C <sub>L</sub> = 50 pF |    |       |          |
|                  |                                                                      |                       | Typ                                              | Guaranteed Minimum |                                                              |    |       |          |
| t <sub>s</sub>   | Set-up Time, HIGH or LOW<br>D <sub>n</sub> to CP <sub>n</sub>        | 5.0                   | 1.0                                              | 3.0                | 3.5                                                          | ns | 3-9   |          |
| t <sub>h</sub>   | Hold Time, HIGH or LOW<br>D <sub>n</sub> to CP <sub>n</sub>          | 5.0                   | 0.5                                              | 1.0                | 1.0                                                          | ns | 3-9   |          |
| t <sub>w</sub>   | CP <sub>n</sub> or C <sub>Dn</sub> or S <sub>Dn</sub><br>Pulse Width | 5.0                   | 3.0                                              | 5.0                | 6.0                                                          | ns | 3-6   |          |
| t <sub>rec</sub> | Recovery Time<br>C <sub>Dn</sub> or S <sub>Dn</sub> to CP            | 5.0                   | 2.5                                              | 0                  | 0                                                            | ns | 3-9   |          |

\*Voltage Range 5.0 is 5.0 V ± 0.5 V

CAPACITANCE

| Symbol          | Parameter                     | Value Typ | Units | Test Conditions       |
|-----------------|-------------------------------|-----------|-------|-----------------------|
| C <sub>IN</sub> | Input Capacitance             | 4.5       | pF    | V <sub>CC</sub> 5.0 V |
| C <sub>PD</sub> | Power Dissipation Capacitance | 35        | pF    | V <sub>CC</sub> 5.0 V |

FACT DATA