

2A, 20V - 150V Schottky Barrier Surface Mount Rectifier

FEATURES

- AEC-Q101 qualified
- Low power loss, high efficiency
- Ideal for automated placement
- Guard ring for overvoltage protection
- High surge current capability
- Moisture sensitivity level: level 1, per J-STD-020
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

APPLICATIONS

- Low voltage, high freq. inverter
- DC/DC converter
- Freewheeling diodes
- Reverse battery protection
- Car lighting

MECHANICAL DATA

- Case: DO-214AA (SMB)
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- Polarity: Indicated by cathode band
- Weight: 0.093g (approximately)

KEY PARAMETERS				
PARAMETER	VALUE	UNIT		
١ _F	2	А		
V _{RRM}	20 - 150	V		
I _{FSM}	50	А		
T _{J MAX}	125, 150	°C		
Package	DO-214AA	(SMB)		
Configuration	Single	die		



DO-214AA (SMB)



ABSOLUTE MAXIMUM RATINGS ($T_A = 25^{\circ}C$ unless otherwise noted)										
PARAMETER	SYMBOL	SS 22H	SS 23H	SS 24H	SS 25H	SS 26H	SS 29H	SS 210H	SS 215H	UNIT
Marking code on the device		SS 22	SS 23	SS 24	SS 25	SS 26	SS 29	SS 210	SS 215	
Repetitive peak reverse voltage	V _{RRM}	20	30	40	50	60	90	100	150	V
Reverse voltage, total rms value	V _{R(RMS)}	14	21	28	35	42	63	70	105	V
Forward current	I _F					2				Α
Surge peak forward current, 8.3ms single half sine-wave superimposed on rated load	I _{FSM}					50				А
Critical rate of rise of off-state voltage	dV/dt				10	0,000				V/µs
Junction temperature	TJ	- 5	5 to +1	25		-	55 to -	+150		°C
Storage temperature	T _{STG}				- 55	to +15	0			°C

Version: A2102



THERMAL PERFORMANCE

PARAMETER	SYMBOL	ТҮР	UNIT
Junction-to-lead thermal resistance	$R_{\Theta JL}$	24	°C/W
Junction-to-ambient thermal resistance	R _{eja}	70	°C/W

PARAMETER		CONDITIONS	SYMBOL	ТҮР	MAX	UNIT
	SS22H SS23H SS24H			-	0.50	V
Forward voltage ⁽¹⁾	SS25H SS26H	$I_F = 2A, T_J = 25^{\circ}C$	V _F	-	0.70	V
	SS29H SS210H			-	0.85	V
	SS215H	-		-	0.95	V
	SS22H SS23H SS24H			-	0.40	V
Forward voltage ⁽¹⁾	SS25H SS26H	I _F = 2A, T _J = 100°C	V _F	-	0.65	V
	SS29H SS210H			-	0.70	V
	SS215H			-	0.80	V
Reverse current @ rated $V_R^{(2)}$	SS22H SS23H SS24H SS25H SS26H	T _J = 25°C	I _R	-	0.4	mA
	SS29H SS210H SS215H			-	0.1	mA
Reverse current @ rated V _R ⁽²⁾ SS23 SS24 SS25 SS26 SS29 SS210	SS22H SS23H SS24H			-	10	mA
	SS25H SS26H	T _J = 100°C	I _R	-	5	mA
	SS29H SS210H SS215H			-	-	mA



SS22H – SS215H Taiwan Semiconductor

ELECTRICAL SPECIFICATIONS (T _A = 25°C unless otherwise noted)						
PARAMETER		CONDITIONS	SYMBOL	ТҮР	MAX	UNIT
	SS22H SS23H SS24H			-	-	mA
Reverse current @ rated V _R ⁽²⁾ SS25H SS26H SS29H SS210H SS215H		T _J = 125°C	I _R	-	-	mA
			-	5	mA	

Notes:

1. Pulse test with PW = 0.3ms

2. Pulse test with PW = 30ms

ORDERING INFORMATION				
ORDERING CODE ⁽¹⁾	PACKAGE	PACKING		
SS2xH	DO-214AA (SMB)	3,000 / Tape & Reel		

Notes:

1. "x" defines voltage from 20V(SS22H) to 150V(SS215H)



CHARACTERISTICS CURVES

(T_A = 25°C unless otherwise noted)




Fig.1 Forward Current Derating Curve





Fig.2 Typical Junction Capacitance

Fig.3 Typical Reverse Characteristics

Fig.4 Typical Forward Characteristics






CHARACTERISTICS CURVES

 $(T_A = 25^{\circ}C \text{ unless otherwise noted})$

Fig.5 Maximum Non-repetitive Forward Surge Current




NUMBER OF CYCLES AT 60 Hz


SS22H – SS215H Taiwan Semiconductor



PACKAGE OUTLINE DIMENSIONS


DO-214AA (SMB)





DIM.	Unit (mm)		Unit	Jnit (inch)	
	Min.	Max.	Min.	Max.	
A	1.95	2.65	0.077	0.104	
A1	0.05	0.20	0.002	0.008	
b	1.95	2.20	0.077	0.087	
с	0.15	0.31	0.006	0.012	
D	3.30	3.95	0.130	0.156	
E	5.10	5.60	0.201	0.220	
E1	4.05	4.60	0.159	0.181	
L	0.75	1.60	0.030	0.063	

SUGGESTED PAD LAYOUT



Symbol	Unit (mm)	Unit (inch)
A	2.30	0.091
В	2.50	0.098
С	4.30	0.169
D	1.80	0.071
E	6.80	0.268

MARKING DIAGRAM



P/N	= Marking Code
~	<u></u>

= Green Compound G YW = Date Code

F = Factory Code



Taiwan Semiconductor

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.