

3A, 150V Trench Schottky Surface Mount Rectifier

FEATURES

- Low power loss, high efficiency
- Ideal for automated placement
- High surge current capability
- Moisture sensitivity level: level 1, per J-STD-020
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

APPLICATIONS

- Switching mode power supply (SMPS)
- Adapters
- DC to DC converter

MECHANICAL DATA


- Case: TO-277A (SMPC)
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 1A whisker test
- · Polarity: Indicated by cathode band
- Weight: 0.095g (approximately)

KEY PARAMETERS			
PARAMETER	VALUE	UNIT	
I _F	3	Α	
V_{RRM}	150	V	
I _{FSM}	90	Α	
T _{J MAX}	150	°C	
Package	TO-277A (SMPC)		
Configuration	Single die		









ABSOLUTE MAXIMUM RATINGS (T _A = 25°C unless otherwise noted)				
PARAMETER	SYMBOL	TSP3H150S	UNIT	
Marking code on the device		3H150		
Repetitive peak reverse voltage	V _{RRM}	150	V	
Reverse voltage, total rms value	V _{R(RMS)}	105	V	
Forward current	I _F	3	А	
Surge peak forward current, 8.3ms single half sine wave superimposed on rated load	I _{FSM}	90	А	
Non-repetitive peak reverse current ⁽¹⁾	I _{RSM}	2	А	
Critical rate of rise of off-state voltage	dv/dt	10,000	V/µs	
Junction temperature	TJ	-55 to +175	°C	
Storage temperature	T _{STG}	-55 to +175	°C	

Notes:

1. Pulse width: 5µs / pulse No.: 10 times





THERMAL PERFORMANCE			
PARAMETER	SYMBOL	TYP	UNIT
Junction-to-lead thermal resistance	$R_{\Theta JL}$	16.0	°C/W
Junction-to-ambient thermal resistance	R _{OJA}	58.5	°C/W
Junction-to-case thermal resistance	R _{eJC}	21.5	°C/W

Thermal Performance Note: Units mounted on recommended PCB (16mm x 16mm Cu test board)

ELECTRICAL SPECIFICATIONS (T _A = 25°C unless otherwise noted)					
PARAMETER	CONDITIONS	SYMBOL	TYP	MAX	UNIT
Forward voltage ⁽¹⁾	$I_F = 1A, T_J = 25^{\circ}C$		0.65	0.74	V
	$I_F = 3A, T_J = 25^{\circ}C$	\	0.77	0.86	V
	I _F = 1A, T _J = 125°C	V _F	0.53	0.62	V
	$I_F = 3A, T_J = 125$ °C		0.62	0.71	V
Reverse current @ rated V _R ⁽²⁾	T _J = 25°C	ı	-	10	μA
	T _J = 125°C	$ I_R$	-	10	mA
Junction capacitance	1MHz, V _R = 4.0V	CJ	150	-	pF
Reverse recovery time	IF = 0.5A, IR = 1.0A Irr = 0.25A	t _{rr}	20	-	ns

Notes:

- 1. Pulse test with PW = 0.3ms
- 2. Pulse test with PW = 30ms

ORDERING INFORMATION			
ORDERING CODE	PACKAGE	PACKING	
TSP3H150S	TO-277A (SMPC)	6,000 / Tape & Reel	



CHARACTERISTICS CURVES

(T_A = 25°C unless otherwise noted)

Fig.1 Forward Current Derating Curve




Fig.3 Typical Reverse Characteristics




Fig.2 Typical Junction Capacitance







Fig.4 Typical Forward Characteristics






PACKAGE OUTLINE DIMENSIONS








DIM. Unit (mm)		Unit (nch)	
	Min.	Max.	Min.	Max.
Α	1.000	1.200	0.039	0.047
b	1.000	1.300	0.039	0.051
b2	1.850	2.150	0.073	0.085
С	0.175	0.325	0.007	0.013
D	4.550	4.650	0.179	0.183
D2	3.170	3.470	0.125	0.137
E	6.350	6.650	0.250	0.262
E1	5.650	5.750	0.222	0.226
E2	4.235	4.535	0.167	0.179
E3	3.540	3.840	0.139	0.151
е	1.930	2.230	0.076	0.088
L	1.043	1.343	0.041	0.053

SUGGESTED PAD LAYOUT




Symbol	Unit (mm)	Unit (inch)
Α	4.80	0.189
В	4.72	0.186
С	1.40	0.055
D	1.27	0.050
E	6.80	0.268
F	1.04	0.041

MARKING DIAGRAM



P/N = Marking Code YW = Date Code F = Factory Code





Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.