

## PolySwitch® PTC Devices

**Overcurrent Protection Device** 

PRODUCT: nanoASMDCH50F/24

DOCUMENT: SCD29488 REV LETTER: A

REV DATE: NOVEMBER 7, 2019

PAGE NO.: 1 OF 2

### **Specification Status: Released**

#### **Maximum Electrical Rating**

Voltage: 24V<sub>DC</sub>


**Short Circuit Current: 20A** 

#### Notes:

- 1. All terminations are tin plated.
- 2. Drawing not to scale

#### Marking

H50



#### **TABLE I. DIMENSIONS:**

mm: in:

Α		В		С		D		Е
MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN
3.00	3.40	1.16	1.46	1.37	1.80	0.25	0.75	0.076
(0.118)	(0.134)	(0.046)	(0.057)	(0.054)	(0.071)	(0.010)	(0.030)	(0.003)

#### **TABLE II. PERFORMANCE RATINGS:**

CURRENT RATINGS**						TIME TO TRIP**	RESISTANCE VALUES		TRIPPED-STATE POWER	
							DISSIPATION**			
AMPERES		AMPERES		AMPERES		SECONDS	OHMS		WATTS AT	
AT 0°C		AT 25°C		AT 60°C		AT 25°C, 8A	AT 25°C		25°C, 24V	
HOLD	TRIP	HOLD	TRIP	HOLD	TRIP	MAX	MIN	MAX*	MAX	
0.58	2.90	0.50	2.50	0.39	1.95	0.1	0.20	1.60	1.7	

<sup>\*</sup> Resistance is measured 1 hour after reflow.

Reference Document: PS300

Precedence: This specification takes precedence over documents referenced herein.

Effectivity: Reference documents shall be the issue in effect on the date of invitation for bid.

CAUTION: Operation beyond the rated voltage or current may result in rupture, electrical arcing or flame.

#### **Materials Information**

**ROHS Compliant** 

**ELV Compliant** 

Pb-Free

Halogen Free\*

Directive 2002/95/EC Compliant Directive 2000/53/EC Compliant



<sup>\*\*</sup> Values specified were determined using PCB's with 0.200"x 2.0 ounce copper traces.

<sup>\*</sup> Halogen Free refers to: Br≤900ppm, Cl≤900ppm, Br+Cl≤1500ppm.



# PolySwitch® PTC Devices

**Overcurrent Protection Device** 

PRODUCT: nanoASMDCH50F/24

DOCUMENT: SCD29488 REV LETTER: A

REV DATE: NOVEMBER 7, 2019

PAGE NO.: 2 OF 2

information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product elected for their own applications. Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, militierospace, medical, lifesaving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly se orth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to ittelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.