




File: E209153



ISO9001:2008 Certified

Mechanical Specifications (mm)

	D:	22.0	±	MAX
	T:	6.0	±	MAX
	Lead Diameter	1.0	±	10
	A:	7.8	±	10
	L:	38.0	±	10
	Coating Lead Run Down (straight Leads)	4.0	±	10
	B:	9.00	±	10
	C:	3.00	±	10



Electrical Specifications

	Resistance:	0.50 Ω	±	25 %
	Max Steady State Current upto 65°C:	16.00		A
	Max Rec. Energy Rating:	160.00		J
	Actual Failure Instantaneous Energy:	320.00		J
	Maximum Capacitance @ 120 VAC:	10000.00		µf
	Maximum Capacitance @ 240 VAC:	2480.00		µf
	Resistance @ 100% Max Current:	0.02		Ω
	Resistance @ 50% Max Current:	0.04		Ω
	Body Temperature at 100% Max Current:	184.00		°c
	Dissipation Constant:	32.40		mw/°c
	Thermal Time Constant:	94.00		Sec.
	Material Type (for Beta and Curve):	A		

SL22 0R516	
Date: 11/11/2008	Drawn by: Erin Landis
Ametherm, Inc. 3111 N. Deer Run Road Carson City, Nevada USA 89701 www.ametherm.com	Approved By: Mehdi Samii
	Revision: a