

APTD3216F3C-P22

3.2 x 1.6 mm Infrared Emitting Diode



DESCRIPTION

• F3 Made with Gallium Arsenide Infrared Emitting diodes


FEATURES

- 3.2 mm x 1.6 mm SMD LED, 1.8 mm thickness
- · Mechanically and spectrally matched to phototransistor
- Package: 2000 pcs / reel
- Moisture sensitivity level: 3
- Halogen-free
- RoHS compliant

APPLICATIONS


- · Infrared Illumination for cameras
- Machine vision systems
- Surveillance systems
- Industrial electronics
- IR data transmission
- Remote control

PACKAGE DIMENSIONS



RECOMMENDED SOLDERING PATTERN

(units : mm; tolerance : ± 0.1)



Notes: 1. All dimensions are in millimeters (inches). 2. Tolerance is ±0.2(0.008") unless otherwise noted. 3. The specifications, characteristics and technical data described in the datasheet are subject to these without origination to the specification of the specification of

change without prior notice. 4. The device has a single mounting surface. The device must be mounted according to the specifications.

SELECTION GUIDE

Part Number	Emitting Color	Lens Type	Po (mW/sr) @ 20mA ^[2]		Viewing Angle ^[1]	
Fait Number	(Material)	Lens Type	Min.	Тур.	201/2	
APTD3216F3C-P22	Infrared (GaAs)	Water Clear	5	10		
			*2	*5	40°	

Notes

- 1. 01/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.
 2. Radiant Intensity / luminous flux: +/-15%.
 * Radiant intensity value is traceable to CIE127-2007 standards.

Kingbright

ELECTRICAL / OPTICAL CHARACTERISTICS at T_A=25°C

Deventer	Querra had	Emitting Color	Value		11 14
Parameter	Symbol	Emitting Color	Тур.	Max.	Unit
Wavelength at Peak Emission I_F = 20mA	λ_{peak}	Infrared	940	-	nm
Spectral Bandwidth at 50% Φ REL MAX I_F = 20mA	Δλ	Infrared	50	-	nm
Capacitance	С	Infrared	90	-	pF
Forward Voltage I_F = 20mA	V _F ^[1]	Infrared	1.2	1.6	V
Reverse Current (V _R = 5V)	I _R	Infrared	-	10	μA
Temperature Coefficient of Wavelength I_F = 20mA, -10°C $\leq T \leq 85^\circ C$	TC _λ	Infrared	0.3	-	nm/°C
Temperature Coefficient of $~V_F$ I_F = 20mA, -10°C $\leq T \leq 85^\circ C$	TCv	Infrared	-1.2	-	mV/°C

Notes:

Forward voltage: ±0.1V.
 Wavelength value is traceable to CIE127-2007 standards.
 Excess driving current and / or operating temperature higher than recommended conditions may result in severe light degradation or premature failure.


ABSOLUTE MAXIMUM RATINGS at $T_A=25^{\circ}C$


Parameter	Symbol	Value	Unit
Power Dissipation	P _D	90	mW
Reverse Voltage	V _R	5	V
Junction Temperature	Tj	115	°C
Operating Temperature	T _{op}	-40 to +85	°C
Storage Temperature	T _{stg}	-40 to +85	°C
DC Forward Current	l _F	50	mA
Peak Forward Current	۱ _{FM} ^[1]	1200	mA
Electrostatic Discharge Threshold (HBM)	-	8000	V
Thermal Resistance (Junction / Ambient)	R _{th JA} ^[2]	710	°C/W
Thermal Resistance (Junction / Solder point)	R _{th JS} ^[2]	580	°C/W

Notes: 1. 1/100 Duty Cycle, 10µs Pulse Width. 2. R_{th JA}, R_{th JS} Results from mounting on PC board FR4 (pad size ≥ 16 mm² per pad). 3. Relative humidity levels maintained between 40% and 60% in production area are recommended to avoid the build-up of static electricity – Ref JEDEC/JESD625-A and JEDEC/J-STD-033.


Kingbright

TECHNICAL DATA







SPATIAL DISTRIBUTION




INFRARED

50












REFLOW SOLDERING PROFILE for LEAD-FREE SMD PROCESS



TAPE SPECIFICATIONS (units : mm)



REEL DIMENSION (units : mm)




Notes.

- Don't cause stress to the LEDs while it is exposed to high temperature.
 The maximum number of reflow soldering passes is 2 times.
 Reflow soldering is recommended. Other soldering methods are not recommended as they might
- cause damage to the product.

Kingbright

APTD3216F3C-P22

PACKING & LABEL SPECIFICATIONS



PRECAUTIONARY NOTES

- The information included in this document reflects representative usage scenarios and is intended for technical reference only.
- 2. The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to the latest datasheet for the updated specifications. When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If
- 3. 4
- customer usage exceeds the specified limits, Kingbright will not be responsible for any subsequent issues. The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening liabilities, such as automotive or medical usage, please consult with Kingbright representative for further assistance.
- The contents and information of this document may not be reproduced or re-transmitted without permission by Kingbright
 All design applications should refer to Kingbright application notes available at https://www.KingbrightUSA.com/Applicatio
- onNotes