SURFACE MOUNT SILICON DUAL, OPPOSING SCHOTTKY DIODE





www.centralsemi.com

DESCRIPTION:

The CENTRAL SEMICONDUCTOR CMKSH-3DO incorporates two (2) galvanically isolated, low V_F silicon diodes with an opposing Anode/Cathode configuration, in a space saving surface mount package, designed for fast switching applications requiring a low forward voltage drop.

MARKING CODE: KDO

FEATURES:

- Dual Opposing (DO) Schottky Diodes
- Small SOT-363 Package

- · Galvanically Isolated
- Low Forward Voltage (0.51V TYP @ 100mA)

| MAXIMUM RATINGS: (T _A =25°C) | SYMBOL | | UNITS |
|--|-----------------------------------|-------------|-------|
| Peak Repetitive Reverse Voltage | V_{RRM} | 30 | V |
| Continuous Forward Current | I _F | 100 | mA |
| Power Dissipation | P_{D} | 250 | mW |
| Operating and Storage Junction Temperature | T _J , T _{stg} | -65 to +150 | °C |
| Thermal Resistance | ΘιΛ | 500 | °C/W |


ELECTRICAL CHARACTERISTICS PER DIODE: (T_A=25°C unless otherwise noted)


| I _R | V _R =25V | MIN | TYP | MAX 500 | nA |
|-----------------|--|-----|------|-------------------|----|
| I_{R} | V _R =25V, T _A =100°C | | | 100 | μΑ |
| BV_R | I _R =100μA | 30 | | | V |
| V_{F} | I _F =2.0mA | | | 0.33 | V |
| V_{F} | I _F =15mA | | | 0.45 | V |
| V_{F} | I _F =100mA | | 0.51 | 1.00 | V |
| CJ | V _R =1.0V, f=1.0MHz | | 7.0 | | pF |
| t _{rr} | $I_F = I_R = 10$ mA, $I_{rr} = 1.0$ mA, $R_L = 100$ Ω | | | 5.0 | ns |
| | | | | | |

SURFACE MOUNT SILICON DUAL, OPPOSING SCHOTTKY DIODE




SOT-363 CASE - MECHANICAL OUTLINE





PIN CONFIGURATION



| DIMENSIONS | | | | | | | |
|------------|--------|-------|-------------|------|--|--|--|
| | INCHES | | MILLIMETERS | | | | |
| SYMBOL | MIN | MAX | MIN | MAX | | | |
| Α | 0.004 | 0.010 | 0.10 | 0.25 | | | |
| В | 0.005 | - | 0.12 | - | | | |
| С | 0.000 | 0.004 | 0.00 | 0.10 | | | |
| D | 0.031 | 0.043 | 0.80 | 1.10 | | | |
| E | 0.071 | 0.087 | 1.80 | 2.20 | | | |
| F | 0.051 | | 1.30 | | | | |
| G | 0.026 | | 0.65 | | | | |
| Н | 0.075 | 0.091 | 1.90 | 2.30 | | | |
| J | 0.043 | 0.055 | 1.10 | 1.40 | | | |
| K | 0.006 | 0.012 | 0.15 | 0.30 | | | |


SOT-363 (REV: R2)

1) Anode D1

- 2) NC
- 3) Cathode D2
- 4) Anode D2
- 5) NC
- 6) Cathode D1


MARKING CODE: KDO


R5 (11-February 2016)








TYPICAL ELECTRICAL CHARACTERISTICS
















TYPICAL ELECTRICAL CHARACTERISTICS







OUTSTANDING SUPPORT AND SUPERIOR SERVICES



PRODUCT SUPPORT

Central's operations team provides the highest level of support to insure product is delivered on-time.

- Supply management (Customer portals)
- · Inventory bonding
- · Consolidated shipping options

- · Custom bar coding for shipments
- · Custom product packing

DESIGNER SUPPORT/SERVICES

Central's applications engineering team is ready to discuss your design challenges. Just ask.

- Free guick ship samples (2nd day air)
- Online technical data and parametric search
- SPICE models
- · Custom electrical curves
- · Environmental regulation compliance
- · Customer specific screening
- · Up-screening capabilities

- Special wafer diffusions
- PbSn plating options
- · Package details
- Application notes
- · Application and design sample kits
- Custom product and package development

REQUESTING PRODUCT PLATING

- 1. If requesting Tin/Lead plated devices, add the suffix "TIN/LEAD" to the part number when ordering (example: 2N2222A TIN/LEAD).
- 2. If requesting Lead (Pb) Free plated devices, add the suffix "PBFREE" to the part number when ordering (example: 2N2222A PBFREE).

CONTACT US

Corporate Headquarters & Customer Support Team

Central Semiconductor Corp. 145 Adams Avenue Hauppauge, NY 11788 USA

Main Tel: (631) 435-1110 Main Fax: (631) 435-1824

Support Team Fax: (631) 435-3388

www.centralsemi.com

Worldwide Field Representatives: www.centralsemi.com/wwreps

Worldwide Distributors:

www.centralsemi.com/wwdistributors

For the latest version of Central Semiconductor's **LIMITATIONS AND DAMAGES DISCLAIMER**, which is part of Central's Standard Terms and Conditions of sale, visit: www.centralsemi.com/terms

www.centralsemi.com (001)