soberton inc.

Acoustic Product Specification

Product Number: WT-0904T



Release | Revision: A/2022

CONTENTS

This document contains the technical specifications for the electromagnetic buzzer.

Page 1 Specifications

Dimensions

Page 2 Reliability Test

Page 3

Electrical and Acoustical Measuring Condition


Frequency Response

Recommended Wave Soldering Temperature

	Specifications		
Item	Unit	Specifications	
Rated Voltage	Vo-p	3	
Operating Voltage	Vo-p	2~5	
Rated Current	mA	Max. 80 at 2.731KHz 50% duty cycle, square wave, 3 Vo-p	
Sound Output	dB	Min. 80 at 2.731KHz 50% duty cycle, square wave, 3 Vo-p	
Coil Resistance	Ω	16±4	
Resonant Frequency	Hz	2731	
Operating Temperature	°C	-20 ~ +70	
Storage Temperature	°C	-30 ~ +80	
Dimensions	mm	Ф9.2 × H4.0	
Pin Length	mm	L1 = 4.5 ± 0.5 , $\Phi = 0.6\pm0.1$	
Housing Material		Black PBT	
Net Weight	gram	Approx. 1.5	
Terminal		Pin Type	
Environmental Protection Regulation		RoHS 2.0	

Dimensions

Unit mm **Tolerance** ±0.5mm, except where specified





Housing Material: Black PBT

www.soberton.com



1

soberton inc. ELECTRO MAGNETIC BUZZER

Acoustic Product Specification

Product Number: WT-0904T



Release | Revision: A/2022

CONTENTS

This document contains the technical specifications for the electromagnetic buzzer.

Page 1 Specifications

Dimensions

Page 2 Reliability Test

Page 3 Electrical and Acoustical Measuring Condition

Frequency Response

Recommended Wave Soldering Temperature

Reliability Test

After any of the following tests the part shall meet specifications without any degradation in appearance and performance except SPL. SPL shall meet the specifications and shall not deviate more than -10dB from the initial value.

Standard Temperature Life Test

The part shall be subjected to 96 hours at 25±10°C.

Input rated voltage: 3 Vo-p

Resonant frequency: 2731Hz, 50% duty cycle, square wave.

High Temperature Test

The part shall be capable of withstanding a storage temperature of $+80^{\circ}$ C for 96 hours.

Low Temperature Test

The part shall be capable of withstanding a storage temperature of -30° C for 96 hours.

Humidity Test

Temperature +40°C±3°C

Relative Humidity 90% ~ 95%

Duration 48 hours and exposure to room temperature for 6 hours

Temperature Shock Test

Per cycle $70^{\circ}C/1 \text{ hour} \rightarrow 25^{\circ}C/3 \text{ hours} \rightarrow -30^{\circ}C/1 \text{ hour} \rightarrow 25^{\circ}C/3 \text{ hours}$

Total cycle 10 cycles

Drop Test

Standard Packaging from 1.2m

Drop on hardwood or board of 5cm thick, three sides, six plain

Vibration Test

Vibration 1000 cycles/min.

Amplitude 1.5mm

Page 4 Packing

Duration 1 hour in each 3 axes

Note

Please make sure that any foreign materials (e.g. magnetic powder, washing solvent, flux, corrosive gas) do not enter this product in your production processes. Contamination may result in a loss of some or all audio output.

www.soberton.com



soberton inc.

ELECTRO MAGNETIC BUZZER

Acoustic Product Specification

Product Number: WT-0904T



Release | Revision: A/2022

CONTENTS

This document contains the technical specifications for the electromagnetic buzzer.

Page 1 Specifications

Dimensions

Page 2 Reliability Test

Page 3 Electrical and Acoustical Measuring Condition

Frequency Response

Recommended Wave Soldering Temperature

Electrical and Acoustical Measuring Condition


Recommended Driving Circuit

Resonant frequency, 50% duty cycle, square wave.

Signal amplitude should be large enough to saturate the transistor.

5V p-p Signal in 2SC3199


Recommended Setting



71111


Frequency Response

3 Vo-p, 50% duty cycle, square wave, 10cm



Recommended Wave Soldering Temperature

Temperature (°C)



Page 4 Packing

www.soberton.com




millio

soberton inc. ELECTRO

MAGNETIC BUZZER

Acoustic Product Specification

Product Number: WT-0904T





Release | Revision: A/2022

CONTENTS

This document contains the technical specifications for the electromagnetic buzzer.

Page 1 Specifications


Dimensions

Page 2 Reliability Test

Page 3 Electrical and Acoustical Measuring Condition

Frequency Response

Recommended Wave Soldering Temperature



2

Packing Method	Quantity (pc)	Measurement (mm)
Per Tray	100	240x160x27
Bundle	1000	240x160x225
Carton	5000	500x420x270

Packing

Page 4 Packing

www.soberton.com



4