

### Main

Device Application	Heavy duty Universal mill switch Standard mill switch
Device short name	T
Series name	Severe duty

### Complementary

[Ith] conventional free air thermal current	20 A
[Ui] Rated Insulation Voltage	600 V
Base plate style	Style C
Body material	Cast zinc
Contact code designation	P600 A600
Contacts material	Silver flashed copper
Contact operation	Snap action
Maximum displacement angle	88 °
Positive opening	Without
Switch actuation	CW
Tilting angle	14 °
Torque Value	12 lbf.in (1.36 N.m)
Tripping angle	12 °

### Environment

Ambient Air Temperature for Operation	-10...185 °F (-23...85 °C)
Electrical shock protection class	Class 0
IP Degree of Protection	IP65 IP67 IP66
NEMA Degree of Protection	NEMA 1/2/4/12/13
Product Certifications	UL Listed[RETURN]CSA[RETURN]CE
Protective treatment	Corrosion resistant gray paint
Shock resistance	30 gn
Standards	UL 508

### Ordering and shipping details

Category	US10DS121497
Discount Schedule	0DS1
GTIN	785901169451
Returnability	No
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.99 in (17.742 cm)
Package 1 Width	2.75 in (6.985 cm)
Package 1 Length	17.74 in (45.064 cm)
Package 1 Weight	2.50 lb(US) (1.134 kg)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------