

PB PIEZO AUDIO BUZZER

Acoustic Product Specification

Product Number: PB-4739NL



Release | Revision: C/2018

CONTENTS

This document contains the technical specifications for the piezo audio buzzer.

Page 1

Specifications

Mechanical Characteristics

Page 2

Environment Test

Reliability Test

Page 3

Measuring Method (Speaker Mode)

Page 4

Dimensions

Page 5

Packing

Specifications					
Item	Unit	Specification	Condition		
Rated Voltage	VDC	12.0	<u> </u>		
Operating Volt	VDC	9.0 ~ 15.0	0V → VDC		
Current Consumption	mA	120 Max.	At 12.0 VDC		
Sound Output	dBA	105	At 30cm/12.0VDC		
Resonant Frequency	Hz	2500 ±1000			
Operating Temp	°C	-20 ~ +60			
Storage Temp	°C	-20 ~ +70			
Dimension	mm	47.0 x 39.0 x H23.5	See drawing		
Housing Material	gram	40			
Material		ABS (black)			
Terminal		Wire type	Wire (140mm) UL1007/AWG26#		
Environmental Protection Regulation		RoHS			

Test condition:

Temperature: +25±2 °C **Related humidity:** 65±5% Air Pressure:86~106KPa

Mechanical Characteristics				
Item	Test condition	Evaluation standard		
Lead Wire Pull Strength	The pull force shall be applied to double lead wire: Horizontal: 3.0N(0.306kg) for 30 seconds. Vertical: 2.0N(0.204kg) for 30 seconds.	No damage and cutting off		
Vibration	The buzzer will be measured after a vibration of amplitude of 1.5mm with 10Hz to 55Hz band of vibration frequency is applied to each of 3 perpendicular directions for 2 hours.	The value of oscillation frequency/current consumption should be in ±10% compared with initial ones.		
Drop Test	The part is dropped from a height of 70cm onto a 40mm thick wooden board 3 times in 3 axes(X,Y,Z). A total of 9 times.	The SPL should be in ±10dB compared with initial one.		



PB PIEZO AUDIO BUZZER

Acoustic Product Specification

Product Number: PB-4739NL



Release | Revision: C/2018

CONTENTS

This document contains the technical specifications for the piezo audio buzzer.

Page 1

Specifications

Mechanical Characteristics

Page 2

Environment Test

Reliability Test

Page 3

Measuring Method (Speaker Mode)

Page 4


Dimensions

Page 5

Packing

Environment Test					
Item	Test condition	Evaluation standard			
High temp. test	The part is placed in a chamber at +70°C for 96 hours	Being placed for 4 hours at +25°C, buzzer shall be measured.			
Low temp. test	The part is placed in a chamber at -30°C for 96 hours	The value of oscillation, frequency / current			
Humidity test	The part is placed in a chamber at +70°C and 90±5% relative humidity for 96 hours	consumption should be in ±10% compared with initial ones. The SPL should be in ±10dB compared with initial one.			

Temp cycle testThe part shall be subjected to 5 cycles.
Each cycle shall consist of:



Reliability Test					
Item	Test condition	Evaluation standard			
Operating Life Test	 Continuous life test 48 hours of continuous operation at +55°C with the maximum rated voltage applied. Intermittent life test A duty cycle of 1 minute on, 1 minutes off, a minimum of 1000 times at +25±2°C and the maximum rated voltage applied. 	After the test, the part shall meet specifications without any degradation in appearance and performance except SPL. After 4 hours at +25°C, the SPL should be in ±10dBA compared with initial one.			

Standard test condition:

a) Temperature: +5~+35°C

b) Humidity: 45~85%

c) Pressure: 860~1060mbar



PB PIEZO AUDIO BUZZER

Acoustic Product Specification

Product Number: PB-4739NL



Release | Revision: C/2018

CONTENTS

This document contains the technical specifications for the piezo audio buzzer.

Page 1

Specifications

Mechanical Characteristics

Page 2

Environment Test

Reliability Test

Page 3

Measuring Method (Speaker Mode)

Page 4


Dimensions

Page 5

Packing

S.P.L Measuring Circuit

Input Signal: 12.0 VDC



MIC: RION S.P.L meter UC30 or equivalent



PB PIEZO AUDIO BUZZER

Acoustic Product Specification

Product Number: PB-4739NL



Release | Revision: C/2018

CONTENTS

This document contains the technical specifications for the piezo audio buzzer.

Page 1

Specifications

Mechanical Characteristics

Page 2

Environment Test

Reliability Test

Page 3

Measuring Method (Speaker Mode)

Page 4


Dimensions


Page 5

Packing

Dimensions

Tolerance: ±0.5 (unit: mm)





No.	Part Name	Material	Quantity
1	Case	ABS	1
2	Case	ABS	1
3	Piezo	Brass + Ceramics	1
4	Cover	ABS	1
5	Cover	ABS	1
6	Wire	PVC + Copper	1
7	Wire (140mm)	UL1007/AWG26#	2
8	РСВ	Ероху	2
9	Transistor	Epoxy + Copper	1





PB PIEZO AUDIO BUZZER

Acoustic Product Specification

Product Number: PB-4739NL



Release | Revision: C/2018

CONTENTS

This document contains the technical specifications for the piezo audio buzzer.

Page 1

Specifications

Mechanical Characteristics

Page 2

Environment Test

Reliability Test

Page 3


Measuring Method (Speaker Mode)

Page 4

Dimensions

Page 5

Packing



Details

Size (mm) Quantity (pcs)

Carton 430 x 320 x 280 800