SIEMENS

Data sheet

3SE5132-0KA00-1CA0



Basic switch with increased corrosion protection for position switch 3SE513 Enclosure plastic according to EN 50041 Device connection 1 x (M20 x 1.5) 1 NO/2 NC slow-action contacts without actuator head

| product brand name | SIRIUS |
|---|--|
| product designation | Mechanical safety switches |
| product type designation | 3SE5 |
| manufacturer's article number | |
| of the supplied switching contacts | 3SE5000-0KA00 |
| of the supplied empty enclosure with cover | 3SE5132-0AA00-1CA, on request |
| suitability for use safety switch | Yes |
| General technical data | |
| product function positive opening | Yes |
| insulation voltage rated value | 400 V |
| degree of pollution | class 3 |
| surge voltage resistance rated value | 6 kV |
| protection class IP | IP66/IP67 |
| shock resistance | |
| according to IEC 60068-2-27 | 30g / 11 ms |
| vibration resistance according to IEC 60068-2-6 | 0.35 mm/5g |
| mechanical service life (switching cycles) typical | 15 000 000 |
| electrical endurance (switching cycles) at AC-15 at 230 V typical | 100 000 |
| electrical endurance (switching cycles) with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026 typical | 10 000 000 |
| Electrical operating cycles in one hour with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026 | 6 000 |
| thermal current | 10 A |
| reference code according to IEC 81346-2 | В |
| continuous current of the C characteristic MCB | 1 A; for a short-circuit current smaller than 400 A |
| continuous current of the quick DIAZED fuse link | 10 A; for a short-circuit current smaller than 400 A |
| continuous current of the DIAZED fuse link gG | 6 A |
| active principle | mechanical |
| repeat accuracy | 0.05 mm |
| Substance Prohibitance (Date) | 07/01/2006 |
| minimum actuating force in directions of actuation | 20 N |
| length of the sensor | 85.7 mm |
| width of the sensor | 40 mm |
| design of the switching contact | mechanical |
| operating frequency rated value | 50 60 Hz |
| number of NC contacts for auxiliary contacts | 2 |
| number of NO contacts for auxiliary contacts | 1 |
| operational current at AC-15 | |

| at 24 V rated value | 6 A |
|--|--|
| at 125 V rated value | 6 A |
| at 240 V rated value | 6 A |
| at 400 V rated value | 4 A |
| operational current at DC-13 | |
| at 24 V rated value | 3 A |
| at 125 V rated value | 0.55 A |
| at 250 V rated value | 0.27 A |
| at 400 V rated value | 0.12 A |
| design of the interface for safety-related communication | without |
| Enclosure | |
| design of the housing | block, narrow |
| material of the enclosure | plastic |
| coating of the enclosure | Other types |
| design of the housing according to standard | Yes |
| Drive Head | |
| design of the actuating element | Other, without, basic switch |
| design of the switching function | Positive opening with appropriate positive opening actuator head |
| circuit principle | slow-action contacts |
| number of switching contacts safety-related | 2 |
| Connections/ Terminals | |
| type of electrical connection | screw-type terminals |
| type of connectable conductor cross-sections | |
| • solid | 1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²) |
| finely stranded with core end processing | 1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²) |
| at AWG cables solid | 1x (20 16), 2x (20 18) |
| at AWG cables stranded | 1x (20 16), 2x (20 18) |
| cable entry type | 1x (M20 x 1.5) |
| Communication/ Protocol | <u>, </u> |
| design of the interface | without |
| Ambient conditions | |
| ambient temperature | |
| during operation | -25 +85 °C |
| during storage | 40 +90 °C |
| explosion protection category for dust | none |
| Installation/ mounting/ dimensions | |
| mounting position | any |
| fastening method | screw fixing |
| Certificates/ approvals | |
| Conord Draduct Amproval | |


General Product Approval





Confirmation







Functional Safety/Safety of Machinery

Declaration of Conformity

other

Type Examination Certificate





Confirmation

Further information

Information- and Downloadcenter (Catalogs, Brochures,...) https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE5132-0KA00-1CA0

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE5132-0KA00-1CA0

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3SE5132-0KA00-1CA0

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax de.aspx?mlfb=3SE5132-0KA00-1CA0&lang=en

last modified: 3/23/2022 🖸