SIEMENS

Data sheet

3SE5114-1CA00-1AF3



Basic switch for position switch 3SE51 Metal enclosure 40 mm according to EN 50041 1 NO/1 NC quick action contacts with M12 connector, 5-pole, fixed with 2 LEDs, yellow/green, 24 V DC without actuator head Pin assignment: Pin1=21, Pin2=22 Pin3=13 and LED green, Pin4=14 and LED yellow, Pin5=ground LED

product brand name	SIRIUS		
product designation	Mechanical safety switches		
product type designation	3SE5		
manufacturer's article number			
 of the supplied switching contacts 	<u>3SE5000-0CA00</u>		
suitability for use safety switch	Yes		
General technical data			
product function positive opening	Yes		
insulation voltage rated value	125 V		
degree of pollution	class 3		
surge voltage resistance rated value	0.8 kV		
protection class IP	IP66/IP67		
shock resistance			
according to IEC 60068-2-27	30g / 11 ms		
vibration resistance according to IEC 60068-2-6	0.35 mm/5g		
mechanical service life (switching cycles) typical	15 000 000		
electrical endurance (switching cycles) with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026 typical	10 000 000		
Electrical operating cycles in one hour with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026	6 000		
thermal current	4 A		
reference code according to IEC 81346-2	В		
continuous current of the C characteristic MCB	1 A; for a short-circuit current smaller than 400 A		
continuous current of the quick DIAZED fuse link	4 A; for a short-circuit current smaller than 400 A		
continuous current of the DIAZED fuse link gG	4 A		
active principle	mechanical		
repeat accuracy	0.05 mm		
operating resource protection class	III (according to EN 60536)		
Substance Prohibitance (Date)	07/01/2006		
minimum actuating force in directions of actuation	20 N		
length of the sensor	99.7 mm		
width of the sensor	40 mm		
design of the switching contact	mechanical		
number of NC contacts for auxiliary contacts	1		
number of NO contacts for auxiliary contacts	1		
operational current at DC-13			
• at 24 V rated value	3 A		
design of the interface for safety-related communication	without		

Enclosure				
design of the housing	block, narrow			
material of the enclosure	metal			
coating of the enclosure	cathodic dip coating			
design of the housing according to standard	Yes			
Drive Head				
design of the actuating element	Other, without, basic switch with LED and plug			
design of the switching function	Positive opening with appropriate positive opening actuator head			
circuit principle	snap-action contacts			
number of switching contacts safety-related	1			
Connections/ Terminals				
type of electrical connection	M12 plug, fixed			
cable entry type	M12 plug			
design of plug-in connection	M12 plug, 5-pole: Pin 1 = terminal 21, Pin 2 = 22, Pin 3 = 13/LED green, Pin 4 = 14/LED yelow, Pin 5 = ground LED			
Communication/ Protocol				
design of the interface	without			
Ambient conditions				
ambient temperature				
 during operation 	-25 +60 °C			
during storage	-40 +90 °C			
explosion protection category for dust	none			
Supply voltage				
type of voltage of the supply voltage of the optional LED display	DC			
supply voltage				
• of LED	24 V			
Installation/ mounting/ dimensions				
mounting position	any			
fastening method	screw fixing			
Certificates/ approvals				
General Product Approval				
Confirmat				
Functional Safety/Safety of Declaration of Conformity Machinery	Test Certificates other			
Type Examination Certificate	Type Test Certific- Confirmation ates/Test Report			

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)


https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE5114-1CA00-1AF3


Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE5114-1CA00-1AF3

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3SE5114-1CA00-1AF3 Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SE5114-1CA00-1AF3&lang=en





1	BN = Brown	\rightarrow	21
2	WH = White	\rightarrow	22
3	BU = Blue	\rightarrow	13+LED-Green
4	BK = Black	\rightarrow	14+LED-Yellow
5	GY = Grey	\rightarrow	GND LED

last modified:

3/23/2022 🖸