


INTELLIGENT POWER MODULE(IPM), 3 PHASE FULL-BRIDGE 500V/2A

DESCRIPTION

SD02M50DBE/DBS is a 3-phase brushless DC motor driver IC with highly-integrated and high reliability, using for small power motor drive applications such as fan motor, consisting of built-in 6 fast recovery MOSFET and 3 half-bridge HVIC for gate driving.

SD02M50DBE/DBS integrates under-voltage protection circuit, providing perfect protection and fail-safe operation. Each phase current of inverter can be monitored separately due to divided negative dc terminals.

SD02M50DBE/DBS is designed with good insulation, perfect thermal properties and low EMI. It is compact and suitable for built-in motors or any other applications requiring the compact installation.



FEATURES

- ◆ Built-in 500V/2A fast recovery MOSFET
- ◆ Built-in high-voltage Gate driver circuit (HVIC)
- ◆ Built-in under-voltage protection
- ◆ Built-in bootstrap diode
- ◆ Compliant with 3.3V and 5V MCU interface, active high
- ◆ 3 independent negative DC-link terminals for inverter current sensing
- ◆ Optimal adapted for low EMI
- ◆ Insulation class: 1500V_{rms}/min


APPLICATIONS

- ◆ Indoor/outdoor air conditioner
- ◆ Refrigerator compressor
- ◆ Smoke exhauster
- ◆ Fan
- ◆ Air purifiers
- ◆ Dishwasher pump

ORDERING INFORMATION

Part No	Package	Marking	Hazardous Substance Control	Packing
SD02M50DBE	DIP-23E	SD02M50DBE	Pb free	Tube
SD02M50DBS	SOP-23H	SD02M50DBS	Pb free	Tube

BLOCK DIAGRAM



ABSOLUTE MAXIMUM RATINGS

Characteristics	Symbol	Ratings	Unit
P-N Input voltage	V_{PN}	500	V
Each MOSFET Continuous Drain Current $T_C=25^{\circ}\text{C}$	I_{D25}	2.0	A
Each MOSFET Continuous Drain Current $T_C=80^{\circ}\text{C}$	I_{D80}	1.5	A
Each MOSFET Peak Drain Current (Peak value) $T_C=25^{\circ}\text{C}$, pulse width<100 μs	I_{DP}	3.0	A
Maximum Power Dissipation, $T_C=25^{\circ}\text{C}$	P_D	13.4	W
Control Supply Voltage	V_{CC}	20	V
High-side Bias Voltage	V_{BS}	20	V
Input Signal Voltage	V_{IN}	-0.3~ $V_{CC}+0.3$	V
Operating Junction Temperature Range	T_J	-40~150	$^{\circ}\text{C}$
Operating Case Temperature Range, $T_J \leq 150^{\circ}\text{C}$ (Note 1)	T_C	-40~125	$^{\circ}\text{C}$
Storage Temperature Range	T_{STG}	-40~125	$^{\circ}\text{C}$
Junction to Case Thermal Resistance	$R_{\theta JC}$	9.3	$^{\circ}\text{C}/\text{W}$
Insulation Voltage 60Hz, Sinusoidal, AC 1 minute, Connection Pins to Heatsink	V_{ISO}	1500	V_{rms}
Bootstrap Diode Forward Current, $T_C=25^{\circ}\text{C}$	I_F	0.5	A
Bootstrap Diode Forward Current(Peak), $T_C=25^{\circ}\text{C}$, Under 1ms Pulse Width	I_{FP}	1.5	A

Note 1: Test point for Case Temperature, please see figure 3.

RECOMMENDED OPERATING CONDITIONS

Characteristics	Symbol	Min	Typ	Max	Unit
Supply Voltage	V_{PN}	--	300	400	V
Control Supply Voltage	V_{CC}	13.5	15	16.5	V
High-side Bias Voltage	V_{BS}	13.5	15	16.5	V
Input ON Threshold Voltage	$V_{IN(ON)}$	3.0	--	V_{CC}	V
Input OFF Threshold Voltage	$V_{IN(OFF)}$	0	--	0.8	V
Dead Time for Preventing Arm-short $V_{CC}=V_{BS}=13.5\sim 16.5V, T_J \leq 150^\circ C$	T_{dead}	1.0	--	--	μs
PWM Switching Frequency, $T_J \leq 150^\circ C$	f_{PWM}	--	15	--	KHz

ELECTRICAL CHARACTERISTICS (Unless specified particularly $T_{amb}=25^\circ C, V_{CC}=V_{BS}=15V$)

Inverter Part (Each fast recovery MOSFET Unless Otherwise Specified)

Characteristics	Symbol	Test Conditions	Min	Typ	Max	Unit
Drain-Source Breakdown Voltage	BV_{DSS}	$V_{IN}=0V, I_D=250\mu A$ (Note 2)	500	--	--	V
Zero Gate Voltage Drain Current	I_{DSS}	$V_{IN}=0V, V_{DS}=500V$	--	--	250	μA
Static Drain-Source On-Resistance	$R_{DS(on)}$	$V_{CC}=V_{BS}=15V, V_{IN}=5V, I_D=1.0A$	--	3.0	4.0	Ω
Drain-Source Diode Forward Voltage	V_{SD}	$V_{CC}=V_{BS}=15V, V_{IN}=0V, I_D=-1.0A$	--	--	1.2	V
Switching Time	t_{ON}	$V_{PN} = 300V, V_{CC} = V_{BS} = 15V,$ $I_D = 0.5A, V_{IN} = 0V \sim 5V,$ Inductive load (Note 3)	--	800	--	ns
	t_{OFF}		--	600	--	ns
	t_{rr}		--	80	--	ns
	E_{ON}		--	70	--	μJ
	E_{OFF}		--	10	--	μJ




Figure 1. Switching Time Definition

Control Part (Each HVIC Unless Otherwise Specified)

Characteristics	Symbol	Test Conditions		Min	Typ	Max	Unit
Quiescent VCC Current	I_{QCC}	$V_{CC}=15V$, $V_{IN}=0V$	Between V_{CC} and COM	--	--	160	μA
Quiescent VBS Current	I_{QBS}	$V_{BS}=15V$, $V_{IN}=0V$	Between $V_{B(U)-U}$, $V_{B(V)-V}$, $V_{B(W)-W}$	--	--	100	μA
Low-side Undervoltage Protection (Figure 5)	UV_{CCD}	Detection Level		7.6	8.6	9.6	V
	UV_{CCR}	Reset Level		8.3	9.3	10.3	V
High-side Undervoltage Protection (Figure 6)	UV_{BSD}	Detection Level		7.6	8.6	9.6	V
	UV_{BSR}	Reset Level		8.3	9.3	10.3	V
ON Threshold Voltage	V_{IH}	Logic High Level	Applied between IN and COM	3.0	--	--	V
OFF Threshold Voltage	V_{IL}	Logic Low Level		--	--	0.8	V
Input Bias Current	I_{IH}	$V_{IN}=5V$	Applied between IN and COM	--	10	20	μA
	I_{IL}	$V_{IN}=0V$		--	--	2	μA

Note 2: BV_{DSS} is the maximum voltage applied to source-drain of each MOSFET. V_{PN} should be less than this value considering the effect of the stray inductance so that V_{DS} should not exceed BV_{DSS} in any case.

Note 3: t_{ON} and t_{OFF} consist of IC driving transmission delay. The value listed is tested under laboratory condition, and this value will change due to different PCB and wire. Please refer to switching time definition in figure 1 and switch test circuit in figure 4.

Note 4: Spike current and voltage of each MOSFET should be contained in SOA during switch operation, RBSOA test current is shown in figure 4.

Bootstrap Diode Part(Each Bootstrap diode Unless Otherwise Specified)

Characteristics	Symbol	Test Conditions	Min	Typ	Max	Unit
Forward Voltage	V_F	$I_F=0.1A$, $T_C=25^\circ C$	--	2.5	--	V
Reverse Recovery Time	t_{rr}	$I_F=0.1A$, $T_C=25^\circ C$	--	80	--	ns





Figure 2. Bootstrap Diode resistor characteristic

Note: Resistive characteristic: equivalent resistor: $\sim 15 \Omega$.

PIN CONFIGURATIONS



PIN DESCRIPTIONS

Pin No	Pin Name	Description
1	COM	Common Supply Ground
2	V _{BU}	Bias Voltage for U Phase High Side Driving
3	V _{CCU}	Bias Voltage for U Phase Low Side Driving
4	IN _{uH}	Signal Input for U Phase High-side
5	IN _{uL}	Signal Input for U Phase Low-side
6	NC	No connection
7	V _{BV}	Bias Voltage for V Phase High Side Driving
8	V _{CCV}	Bias Voltage for V Phase Low Side Driving
9	IN _{vH}	Signal Input for V Phase High-side
10	IN _{vL}	Signal Input for V Phase Low-side
11	NC	No connection
12	V _{BW}	Bias Voltage for W Phase High Side Driving
13	V _{CCW}	Bias Voltage for W Phase Low Side Driving
14	IN _{wH}	Signal Input for W Phase High-side
15	IN _{wL}	Signal Input for W Phase Low-side
16	NC	No connection
17	P	Positive DC-Link Input
18	U, V _{SU}	Output for U Phase and Bias Voltage Ground for U Phase High Side Driving

Pin No	Pin Name	Description
19	NU	Negative DC-Link Input for U Phase
20	NV	Negative DC-Link Input for V Phase
21	V,V _{sv}	Output for V Phase and Bias Voltage Ground for V Phase High Side Driving
22	NW	Negative DC-Link Input for W Phase
23	W,V _{sw}	Output for W Phase and Bias Voltage Ground for W Phase High Side Driving




Figure 3. Case temperature TC test point




Figure 4. Switching and RBSOA Test Circuit(Low-side)

CONTROL TIME SEQUENCE




Figure 5. Under-Voltage Protection(Low side)





Figure 6. Under-Voltage Protection(High side)

TYPICAL APPLICATION CIRCUIT




Note:

- (1) The wire of each pins should be as short as possible to avoid malfunction; RC filtering capacitor maybe connected to inputs to prevent surge noise caused by wrong input signal.
- (2) Each external capacitor should be placed as close as to IPM pin.
- (3) It is recommended to connect high frequency non-inductive capacitor besides filtering capacitor between PN with short wire to avoid surge destruction.
- (4) Better to connect a filtering capacitor which is 7 times larger than bootstrap capacitor C1 to VCC input.
- (5) It is recommended to adopt high frequency capacitor C1, whose value is larger than 2.2uF, as bootstrap capacitor to adsorb high frequency ripple.
- (6) The wire between current limit resistor R4 and IPM should be as short as possible to avoid IPM damage caused by surge voltage due to wire inductance.

PACKAGE OUTLINE


DIP-23E

UNIT: mm




SOP-23H

UNIT: mm



LAND PATTERN RECOMMENDATIONS





MOS DEVICES OPERATE NOTES:

Electrostatic charges may exist in many things. Please take following preventive measures to prevent effectively the MOS electric circuit as a result of the damage which is caused by discharge:

- The operator must put on wrist strap which should be earthed to against electrostatic.
- Equipment cases should be earthed.
- All tools used during assembly, including soldering tools and solder baths, must be earthed.
- MOS devices should be packed in antistatic/conductive containers for transportation.

Disclaimer :

- Silan reserves the right to make changes to the information herein for the improvement of the design and performance without prior notice! Customers should obtain the latest relevant information before placing orders and should verify that such information is complete and current.
- All semiconductor products malfunction or fail with some probability under special conditions. When using Silan products in system design or complete machine manufacturing, it is the responsibility of the buyer to comply with the safety standards strictly and take essential measures to avoid situations in which a malfunction or failure of such Silan products could cause loss of body injury or damage to property.
- Silan will supply the best possible product for customers!

Part No.: SD02M50DBE/DBS Document Type: Datasheet
Copyright: HANGZHOU SILAN MICROELECTRONICS CO.,LTD Website: <http://www.silan.com.cn>

Rev.: 1.0

Revision History:

1. First release
-