# **SIEMENS**

#### **Data sheet**

## 3SE5112-0CA00-1AC1



Basic switch for position switch 3SE51 Metal enclosure, according to EN 50041 Device connection 1 x (M20 x 1.5) 1 NO/1 NC quick action contacts without actuator head with gold-plated contacts

product brand name	SIRIUS
product designation	Mechanical safety switches
product type designation	3SE5
manufacturer's article number	
<ul> <li>of the supplied switching contacts</li> </ul>	3SE5000-0CA00-1AC1
<ul> <li>of the supplied empty enclosure with cover</li> </ul>	3SE5112-0AA00
suitability for use safety switch	Yes
General technical data	
product function positive opening	Yes
insulation voltage rated value	400 V
degree of pollution	class 3
surge voltage resistance rated value	6 kV
protection class IP	IP66/IP67
shock resistance	
• according to IEC 60068-2-27	30g / 11 ms
vibration resistance according to IEC 60068-2-6	0.35 mm/5g
mechanical service life (switching cycles) typical	15 000 000
electrical endurance (switching cycles) at AC-15 at 230 V typical	100 000
electrical endurance (switching cycles) with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026 typical	10 000 000
Electrical operating cycles in one hour with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026	6 000
thermal current	10 A
reference code according to IEC 81346-2	В
continuous current of the C characteristic MCB	1 A; for a short-circuit current smaller than 400 A
continuous current of the quick DIAZED fuse link	10 A; for a short-circuit current smaller than 400 A
continuous current of the DIAZED fuse link gG	6 A
active principle	mechanical
repeat accuracy	0.05 mm
Substance Prohibitance (Date)	07/01/2006
minimum actuating force in directions of actuation	20 N
length of the sensor	85.7 mm
width of the sensor	40 mm
design of the switching contact	mechanical
operating frequency rated value	50 60 Hz
number of NC contacts for auxiliary contacts	1
number of NO contacts for auxiliary contacts	1
operational current at AC-15	

<ul> <li>at 24 V rated value</li> </ul>	6 A
<ul> <li>at 125 V rated value</li> </ul>	6 A
<ul> <li>at 240 V rated value</li> </ul>	6 A
at 400 V rated value	4 A
operational current at DC-13	
<ul> <li>at 24 V rated value</li> </ul>	3 A
<ul> <li>at 125 V rated value</li> </ul>	0.55 A
<ul> <li>at 250 V rated value</li> </ul>	0.27 A
at 400 V rated value	0.12 A
design of the interface for safety-related communication	without
Enclosure	
design of the housing	block, narrow
material of the enclosure	metal
coating of the enclosure	cathodic dip coating
design of the housing according to standard	Yes
Drive Head	
design of the actuating element	Other, without, basic switch
design of the switching function	Positive opening with appropriate positive opening actuator head
circuit principle	snap-action contacts
number of switching contacts safety-related	1
Connections/ Terminals	
type of electrical connection	screw-type terminals
type of connectable conductor cross-sections	
• solid	1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²)
<ul> <li>finely stranded with core end processing</li> </ul>	1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²)
<ul> <li>at AWG cables solid</li> </ul>	1x (20 16), 2x (20 18)
at AWG cables stranded	_ 1x (20 16), 2x (20 18)
cable entry type	1x (M20 x 1.5)
Communication/ Protocol	,
design of the interface	without
Ambient conditions	
ambient temperature	
<ul><li>during operation</li></ul>	-25 +85 °C
during storage	40 +90 °C
explosion protection category for dust	none
Installation/ mounting/ dimensions	
mounting position	any
fastening method	screw fixing
Certificates/ approvals	
Concret Breduct Ampreyal	

### **General Product Approval**





Confirmation







Functional Safety/Safety of Machinery

**Declaration of Conformity** 

**Test Certificates** 

other

Type Examination Certificate





Type Test Certificates/Test Report

Confirmation

#### Further information

Information- and Downloadcenter (Catalogs, Brochures,...) <a href="https://www.siemens.com/ic10">https://www.siemens.com/ic10</a>

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE5112-0CA00-1AC1


Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE5112-0CA00-1AC1

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3SE5112-0CA00-1AC1

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) <a href="http://www.automation.siemens.com/bilddb/cax">http://www.automation.siemens.com/bilddb/cax</a> de.aspx?mlfb=3SE5112-0CA00-1AC1&lang=en



1/26/2022 last modified: