SIEMENS

Data sheet 3SE5122-0PE01



Position switch Metal enclosure 56 mm wide Device connection 3x (M20x 1.5) 2 NO/1 NC slow-action contacts Roller lever, Metal lever and plastic roller 22 mm

product brand name	SIRIUS	
product designation	Mechanical position switches	
product type designation	3SE5	
manufacturer's article number		
 of the supplied basic switch 	3SE5122-0PA00	
 of the supplied actuator head for position switches 	3SE5000-0AE01	
 of the supplied switching contacts 	3SE5000-0PA00	
of the supplied empty enclosure with cover	3SE5122-0AA00	
suitability for use safety switch	Yes	
General technical data		
product function positive opening	Yes	
insulation voltage rated value	250 V	
degree of pollution	class 3	
surge voltage resistance rated value	4 kV	
protection class IP	IP66/IP67	
shock resistance		
according to IEC 60068-2-27	30g / 11 ms	
vibration resistance according to IEC 60068-2-6	0.35 mm/5g	
mechanical service life (switching cycles) typical	15 000 000	
electrical endurance (switching cycles) at AC-15 at 230 V typical	100 000	
electrical endurance (switching cycles) with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026 typical	10 000 000	
Electrical operating cycles in one hour with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026	6 000	
thermal current	10 A	
material of the enclosure of the switch head	plastic	
reference code according to IEC 81346-2	В	
continuous current of the C characteristic MCB	1 A; for a short-circuit current smaller than 400 A	
continuous current of the quick DIAZED fuse link	10 A; for a short-circuit current smaller than 400 A	
continuous current of the DIAZED fuse link gG	6 A	
active principle	mechanical	
repeat accuracy	0.05 mm	
Substance Prohibitance (Date)	07/01/2006	
minimum actuating force in directions of actuation	10 N	
length of the sensor	119 mm	
width of the sensor	56 mm	
design of the switching contact	mechanical	
operating frequency rated value	50 60 Hz	

and the state of NO and the few and the state of the stat	
number of NC contacts for auxiliary contacts	_ 1
number of NO contacts for auxiliary contacts	2
operational current at AC-15	
• at 24 V rated value	6 A
• at 125 V rated value	6 A
• at 240 V rated value	6 A
at 400 V rated value	4 A
operational current at DC-13	
at 24 V rated value	3 A
 at 125 V rated value 	0.55 A
at 250 V rated value	0.27 A
at 400 V rated value	0.12 A
design of the interface for safety-related communication	without
Enclosure	
design of the housing	block, wide
material of the enclosure	metal
coating of the enclosure	cathodic dip coating
design of the housing according to standard	No
Drive Head	
design of the actuating element	Roller lever, metal lever, plastic roller
standard-compliant actuator head	EN 50041
shape of the switch head	roller
design of the switching function	positive opening
circuit principle	slow-action contacts
number of switching contacts safety-related	1
Connections/ Terminals	
type of electrical connection	screw-type terminals
type of connectable conductor cross-sections	
• solid	1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²)
 finely stranded with core end processing 	1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²)
 at AWG cables solid 	1x (20 16), 2x (20 18)
 at AWG cables stranded 	1x (20 16), 2x (20 18)
cable entry type	3x (M20 x 1.5)
Communication/ Protocol	
design of the interface	without
Ambient conditions	
ambient temperature	
 during operation 	-25 +85 °C
during storage	-40 +90 °C
explosion protection category for dust	none
Installation/ mounting/ dimensions	
mounting position	any
fastening method	screw fixing
Certificates/ approvals	
General Product Approval	





Confirmation







Functional Safety/Safety of Declaration of Conformity Machinery	Test Certificates	other
---	-------------------	-------





Type Test Certificates/Test Report

Confirmation

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE5122-0PE01

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE5122-0PE01

 ${\bf Service \& Support~(Manuals,~Certificates,~Characteristics,~FAQs,...)}$

https://support.industry.siemens.com/cs/ww/en/ps/3SE5122-0PE01

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SE5122-0PE01&lang=en

last modified:	1/26/2022