SIEMENS

Data sheet

3SE5232-0CK62-1AJ0



Position switch Plastic 31 mm according to EN 50047 Increased corrosion protection Device connection 1 x (M20 x 1.5) 1 NO/1 NC quick action contacts Twist lever, adjustable length with grid hole on the right and/or left adjustable, with Stainless steel lever and plastic roller 19 mm functional at -40 °C Shock and vibration test according to EN 61373, Category 1B

product brand name	SIRIUS
product designation	Mechanical position switches
product type designation	3SE5
manufacturer's article number	
 of the supplied actuator head for position switches 	3SE5000-0AK00-1AJ0
 of the supplied operating lever 	3SE5000-0AA62-1AJ0
 of the supplied switching contacts 	3SE5000-0CA00
suitability for use safety switch	Yes
General technical data	
product function positive opening	Yes
insulation voltage rated value	400 V
degree of pollution	class 3
surge voltage resistance rated value	6 kV
protection class IP	IP65
shock resistance	
according to IEC 60068-2-27	30g / 11 ms
 for railway applications according to EN 61373 	Category 1, Class B
vibration resistance	
according to IEC 60068-2-6	0.35 mm/5g
 for railway applications according to EN 61373 	Category 1, Class B
mechanical service life (switching cycles) typical	15 000 000
electrical endurance (switching cycles) at AC-15 at 230 V typical	100 000
electrical endurance (switching cycles) with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026 typical	10 000 000
Electrical operating cycles in one hour with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026	6 000
thermal current	10 A
material of the enclosure of the switch head	plastic
reference code according to IEC 81346-2	В
continuous current of the C characteristic MCB	1 A; for a short-circuit current smaller than 400 A
continuous current of the quick DIAZED fuse link	10 A; for a short-circuit current smaller than 400 A
continuous current of the DIAZED fuse link gG	6 A
active principle	mechanical
repeat accuracy	0.05 mm
Substance Prohibitance (Date)	07/01/2006
minimum actuating torque in directions of actuation	0.25 N·m
length of the sensor	182 mm
width of the sensor	31 mm

design of the switching contact	mechanical
design of the switching contact	50 60 Hz
operating frequency rated value	1 1 00 HZ
number of NC contacts for auxiliary contacts	1
number of NO contacts for auxiliary contacts	
operational current at AC-15	G A
at 24 V rated valueat 120 V rated value	6 A 6 A
at 240 V rated value at 240 V rated value	6 A
at 400 V rated value at 400 V rated value	4 A
operational current at DC-13	4 A
• at 24 V rated value	3 A
at 125 V rated value	0.55 A
at 250 V rated value at 250 V rated value	0.27 A
at 400 V rated value	0.12 A
design of the interface for safety-related communication	without
Enclosure	Without
	block parrow
design of the housing material of the enclosure	block, narrow
	plastic Other types
coating of the enclosure design of the housing according to standard	Other types Yes
Drive Head	165
	Adjustable twist lover adjustable length metal lover with positive fit 100
design of the actuating element	Adjustable twist lever, adjustable-length metal lever with positive fit, 100 mm long, plastic roller 19 mm
standard-compliant actuator head	EN 50047, design A
shape of the switch head	roller
design of the switching function	positive opening
circuit principle	snap-action contacts
number of switching contacts safety-related	1
Connections/ Terminals	
type of electrical connection	screw-type terminals
type of connectable conductor cross-sections	
• solid	1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²)
 finely stranded with core end processing 	1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²)
 at AWG cables solid 	1x (20 16), 2x (20 18)
at AWG cables stranded	1x (20 16), 2x (20 18)
cable entry type	1x (M20 x 1.5)
Communication/ Protocol	
design of the interface	without
Ambient conditions	
ambient temperature	
during operation	-40 +85 °C
during storage	-40 +90 °C
explosion protection category for dust	none
Installation/ mounting/ dimensions	
mounting position	any
fastening method	screw fixing
Certificates/ approvals	
General Product Approval	





Confirmation







Safety/Safety of Declaration of Conformity Test Certificates other Machinery





Type Test Certificates/Test Report

Confirmation

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE5232-0CK62-1AJ0

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE5232-0CK62-1AJ0

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3SE5232-0CK62-1AJ0

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SE5232-0CK62-1AJ0&lang=en

last modified:	3/23/2022