SIEMENS

Data sheet

3SE5232-0MC05-1CA0



Position switch with increased corrosion protection Plastic enclosure according to EN 50047, 31 mm Device connection 1 x (M20 x 1.5) 1 NO/2 NC slow-action contacts with make-before-break Teflon plunger


product brand name	SIRIUS
product designation	Mechanical position switches
product type designation	3SE5
manufacturer's article number	0020
of the supplied switching contacts	3SE5000-0MA00
 of the supplied switching contacts of the supplied empty enclosure with cover 	3SE5232-0AC05-1CA0
suitability for use safety switch	Yes
General technical data	
product function positive opening	Yes
insulation voltage rated value	250 V
degree of pollution	class 3
surge voltage resistance rated value	4 kV
protection class IP	IP65
shock resistance	
according to IEC 60068-2-27	30g / 11 ms
vibration resistance	009711110
according to IEC 60068-2-6	0.35 mm/5g
mechanical service life (switching cycles) typical	15 000 000
electrical endurance (switching cycles) at AC-15 at 230 V	100 000
typical	
electrical endurance (switching cycles) with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026 typical	10 000 000
Electrical operating cycles in one hour with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026	6 000
thermal current	10 A
material of the enclosure of the switch head	plastic
reference code according to IEC 81346-2	В
continuous current of the C characteristic MCB	1 A; for a short-circuit current smaller than 400 A
continuous current of the quick DIAZED fuse link	10 A; for a short-circuit current smaller than 400 A
continuous current of the DIAZED fuse link gG	6 A
active principle	mechanical
repeat accuracy	0.05 mm
Substance Prohibitance (Date)	07/01/2006
minimum actuating force in directions of actuation	20 N
length of the sensor	75.7 mm
width of the sensor	31 mm
design of the switching contact	mechanical
operating frequency rated value	50 60 Hz
number of NC contacts for auxiliary contacts	2


Functional Safety/Safety of Declaration of Conformity Machinery	Test Certificates other
Confirmation Confirmation	DA UN CALL CALL
General Product Approval	
Certificates/ approvals	
fastening method	screw fixing
Installation/ mounting/ dimensions mounting position	any
explosion protection category for dust	none
ouring storage overlapion protection category for dust	^ -40 +90 °C
during operation	-25 +85 °C
ambient temperature	
Ambient conditions	
design of the interface	without
Communication/ Protocol	
cable entry type	1x (20 16), 2x (20 18) 1x (M20 x 1.5)
 at AWG cables solid at AWG cables stranded 	1x (20 16), 2x (20 18) 1x (20 16), 2x (20 18)
finely stranded with core end processing at AWC cables colid	1x (0.5 1.5 mm ²), 2x (0.5 0.75 mm ²)
• solid	1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²)
type of connectable conductor cross-sections	
type of electrical connection	screw-type terminals
Connections/ Terminals	
number of switching contacts safety-related	2
circuit principle	slow-action contacts
shape of the switch head design of the switching function	positive opening
standard-compliant actuator head	EN 50047, design B rounded
design of the actuating element	Rounded plunger, plastic plunger
Drive Head	
design of the housing according to standard	Yes
coating of the enclosure	Other types
material of the enclosure	plastic
design of the housing	block, narrow
Enclosure	Wallout
design of the interface for safety-related communication	without
 at 250 V rated value at 400 V rated value 	0.27 A 0.12 A
• at 125 V rated value	0.55 A
at 24 V rated value	3 A
operational current at DC-13	
• at 400 V rated value	4 A
• at 240 V rated value	6 A
• at 120 V rated value	6 A
at 24 V rated value	6 A
number of NO contacts for auxiliary contacts operational current at AC-15	_ 1


Further information

Information- and Downloadcenter (Catalogs, Brochures,...) https://www.siemens.com/ic10 Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE5232-0MC05-1CA0 Cax online generator http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE5232-0MC05-1CA0 Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/3SE5232-0MC05-1CA0 Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macr

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SE5232-0MC05-1CA0&lang=en







last modified:

