

ICL7663S

CMOS Programmable Micropower **Positive Voltage Regulator**

April 1994

Features

- · Guaranteed 10µA Maximum Quiescent Current Over All Temperature Ranges
- . Wider Operating Voltage Range 1.6V to 16V
- · Guaranteed Line and Load Regulation Over Entire Operating Temperature Range Optional
- 1% Output Voltage Accuracy (ICL7663SA)
- Output Voltage Programmable from 1.3V to 16V
- Improved Temperature Coefficient of Output Voltage
- 40mA Minimum Output Current with Current Limiting
- Output Voltages with Programmable Negative Temperature Coefficients
- · Output Shutdown via Current-Limit Sensing or External Logic Level
- · Low Input-to-Output Voltage Differential
- · Improved Direct Replacement for Industry Standard ICL7663B and Other Second-Source Products

Applications

- Low-Power Portable Instrumentation
- Pagers
- Handheld Instruments
- LCD Display Modules
- Remote Data Loggers
- Battery-Powered Systems

Description

The ICL7663S Super Programmable Micropower Voltage Regulator is a low power, high efficiency positive voltage regulator which accepts 1.6V to 16V inputs and provides adjustable outputs from 1.3V to 16V at currents up to 40mA.


It is a direct replacement for the industry standard ICL7663B offering wider operating voltage and temperature ranges, improved output accuracy (ICL7663SA), better temperature coefficient, guaranteed maximum supply current, and guaranteed line and load regulation. All improvements are highlighted in the electrical characteristics section. Critical parameters are guaranteed over the entire commercial and industrial temperature ranges. The ICL7663S/SA programmable output voltage is set by two external resistors. The 1% reference accuracy of the ICL7663SA eliminates the need for trimming the output voltage in most applications.

The ICL7663S is well suited for battery powered supplies, featuring 4µA quiescent current, low VIN to VOLIT differential, output current sensing and logic input level shutdown control. In addition, the ICL7663S has a negative temperature coefficient output suitable for generating a temperature compensated display drive voltage for LCD displays.

The ICL7663S is available in either an 8 lead Plastic DIP, Ceramic DIP, or SOIC package.

Pinout

ICL7663S (PDIP, CERDIP, SOIC) TOP VIEW



Ordering Information

PART NUMBER	TEMPERATURE RANGE	PACKAGE
ICL7663SCBA	0°C to +70°C	8 Lead SOIC (N)
ICL7663SCPA		8 Lead Plastic DIP
ICL7663SCJA		8 Lead CerDIP
ICL7663SACBA		8 Lead SOIC (N)
ICL7663SACPA		8 Lead Plastic DIP
ICL7663SACJA		8 Lead CerDIP
ICL7663SIBA	-25°C to +85°C	8 Lead SOIC (N)
ICL7663SIPA		8 Lead Plastic DIP
ICL7663SIJA		8 Lead CerDIP
ICL7663SAIBA		8 Lead SOIC (N)
ICL7663SAIPA		8 Lead Plastic DIP
ICL7663SAIJA		8 Lead CerDIP

Specifications ICL7663S

Absolute Maximum Ratings	Thermal Information		
Input Supply Voltage. +18V Any Input or Output Voltage (Note 1) Terminals 1, 2, 3, 5, 6, 7	Thermal Resistance Ceramic DIP Package Plastic DIP Package Plastic SOIC Package Maximum Junction Temperature Plastic DIP Package CerDIP Package Storage Temperature Range Lead Temperature (Soldering 10s) (SOIC - Lead Tips Only)	180°C/W	+175°C to +150°C

CAUTION: Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress only rating and operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied.

Operating Conditions

Operating Temperature Range	
ICL7663SC	0°C to +70°C
ICL7663SI	25°C to +85°C

Electrical Specifications Specifications Below Applicable to Both ICL7663S and ICL7663SA, Unless Otherwise Specified.

V+IN = 9V, Vout = 5V, TA = +25°C, Unless Otherwise Specified. Notes 4, 5. See Test Circuit, Figure 7

PARAMETERS	SYMBOL	TEST CONDITIONS		MIN	TYP	MAX	UNITS
Input Voltage	V+IN	ICL7663S T _A = +25°C		1.5	-	- 16	٧
			0°C < T _A < +70°C	1.6	-	16	V
			-25°C < T _A < +85°C	1.6	-	16	٧
		ICL7663SA	0°C < T _A < +70°C	1.6	-	. 16	٧
			-25°C < T _A < +85°C	1.6	-	_28	٧
Quiescent Current	la	1.4V ≤ V _{OUT} ≤ 8.5V, No Load					
		V+ _{IN} = 9V	0°C < T _A < +70°C	-	٠.	10	μА
			-25°C < T _A < +85°C	-		110	μĀ
		V+IN = 16V	0°C < T _A < +70°C	-	-	1/2	μА
			-25°C < T _A < +85°C	· ·	-	12	μА
Reference Voltage	V _{SET}	I _{OUT1} = 100μA, V _{OUT} = V _{SET}					
		ICL7663S	T _A = +25°C	1.2	1.3	1.4	٧
		ICL7663SA	T _A = +25°C	1275	120	(3)	٧
Temperature	ΔV _{SET}	0°C < T _A < +70°C -25°C < T _A < +85°C		-	100	-	ppm
Coefficient	ΔΤ			·	100	-	ppm
Line Regulation	ΔV _{SET}	2V < V _{IN} < 15V	0°C < T _A < +70°C	-	0.03	-	%∕∨
	V _{SET} AV _{IN}		-25°C < T _A < +85°C	<u> </u>	0.03	613	%∕∨
V _{SET} Input Current	I _{SET}	0°C < T _A < +70°C		-	0.01	(0)	nA
		-25°C < T _A < +85°C		-	0.01	100	nA
Shutdown Input Current	I _{SHDN}			•	±0.01	10	nA
Shutdown Input Voltage	V _{SHDN}	V _{SHDN} HI: Both V _{OUT} Disabled		1.4		-	V
		V _{SHDN} LO: Both V _{OUT} Enable		-		0.3	
Sense Pin Input Current	SENSE			-	0.01	10	nA
Sense Pin Input Thresh- old	V _{CL}			-	0.5	•	٧
Input-Output Saturation	R _{SAT}	V+1N = 2V, I _{OUT1} = 1mA			17/0	230	Ω
Resistance (Note 2)		V+ _{IN} = 9V, I _{OUT1} = 2mA		-	60		Ω
		V+ _{IN} = 15V, I _{OUT1} = 5mA		-	\$860 MARCH 1113		Ω
Load Regulation	ΔV _{OUT}	1mA < I _{OUT2} < 20mA		-	1		Ω
	ΔΙουτ	50μA < I _{OUT1} < 5mA			2		Ω

Specifications ICL7663S

Electrical Specifications Specifications Below Applicable to Both ICL7663S and ICL7663SA, Unless Otherwise Specified.


V+IN = 9V, V_{OUT} = 5V, T_A = +25°C, Unless Otherwise Specified. Notes 4, 5. See Test Circuit, Figure 7 (Continued)

PARAMETERS	SYMBOL	TEST CONDITIONS		MIN	TYP	MAX	UNITS
Available Output Current (V _{OUT2})	l _{OUT2}	3V ≤ V _{IN} ≤ 16V, V _{IN} - V _{OUT2} ≈ 1.5V		40	•		mA
		Open Circuit Voltage	n Circuit Voltage		0.9		٧
(Note 3)	I _{TC}	Maximum Sink Current		0	8	2.0	mA
Temperature Coefficient	ΔV _{TC}	Open Circuit		•	+2.5	-	mV/ºC
Minimum Load Current	I _{L(MIN)}	Includes V _{SET} Divider	T _A = +25°C	-	-	1.0	μА
			0°C < TA < +70°C	1 - 1	0.2	5.0	μА
			-25°C < T _A < +85°C	1 - 1	0.2	5.0	μА

NOTES:

- Connecting any terminal to voltages greater than (V+_{IN} + 0.3V) or less than (GND 0.3V) may cause destructive device latch-up. It is recommended that no inputs from sources operating on external power supplies be applied prior to ICL7663S power-up.
- This parameter refers to the saturation resistance of the MOS pass transistor. The minimum input-output voltage differential at low current (under 5mA), can be determined by multiplying the load current (including set resistor current, but not quiescent current) by this resistance.
- This output has a positive temperature coefficient. Using it in combination with the inverting input of the regulator at V_{SET}, a negative coefficient results in the output voltage. See Figure 9 for details. Pin will not source current.
- 4. All pins are designed to withstand electrostatic discharge (ESD) levels in excess of 2000V.
- 5. All significant improvements over the industry standard ICL7663 are highlighted.

Functional Diagram



Typical Performance Curves




FIGURE 1. V_{OUT2} OUTPUT VOLTAGE AS A FUNCTION OF OUTPUT CURRENT




FIGURE 2. V_{OUT1} INPUT-OUTPUT DIFFERENTIAL vs OUTPUT CURRENT




FIGURE 3. V_{OUT2} INPUT-OUTPUT DIFFERENTIAL V8 OUTPUT CURRENT




FIGURE 4. INPUT POWER SUPPLY REJECTION RATIO




FIGURE 5. QUIESCENT CURRENT AS A FUNCTION OF INPUT VOLTAGE




FIGURE 6. QUIESCENT CURRENT AS A FUNCTION OF TEM-PERATURE

Detailed Description

The ICL7663S is a CMOS integrated circuit incorporating all the functions of a voltage regulator plus protection circuitry on a single monolithic chip. Referring to the Functional Diagram, the main blocks are a bandgap-type voltage reference, an error amplifier, and an output driver with both PMOS and NPN pass transistors.

The bandgap output voltage, trimmed to 1.29V \pm 15mV for the ICL7663SA, and the input voltage at the V_{SET} terminal are compared in amplifier A. Error amplifier A drives a P-channel pass transistor which is sufficient for low (under about 5mA) currents. The high current output is passed by an NPN bipolar transistor connected as a follower. This configuration gives more gain and lower output impedance.

Logic-controlled shutdown is implemented via a N-channel MOS transistor. Current-sensing is achieved with comparator C, which functions with the V_{CUT2} terminal. The ICL7663S has an output (V_{TC}) from a buffer amplifier (B), which can be used in combination with amplifier A to generate programmable-temperature-coefficient output voltages.

The amplifier, reference and comparator circuitry all operate at bias levels well below 1µA to achieve extremely low quiescent current. This does limit the dynamic response of the circuits, however, and transients are best dealt with outside the regulator loop.

Basic Operation


The ICL7663S is designed to regulate battery voltages in the 5V to 15V region at maximum load currents of about 5mA to 30mA. Although intended as low power devices, power dissipation limits must be observed. For example, the power dissipation in the case of a 10V supply regulated down to 2V with a load current of 30mA clearly exceeds the power dissipation rating of the Mini-DIP:

$$(10 - 2) (30) (10^{-3}) = 240 \text{mW}$$

The circuit of Figure 8 illustrates proper use of the device.

CMOS devices generally require two precautions: every input pin must go somewhere, and maximum values of applied voltages and current limits must be rigorously observed. Neglecting these precautions may lead to, at the least, incorrect or nonoperation, and at worst, destructive device failure. To avoid the problem of latchup, do not apply inputs to any pins before supply voltage is applied.

Input Voltages - The ICL7663S accepts working inputs of 1.5V to 16V. When power is applied, the rate-of-rise of the input may be hundreds of volts per microsecond. This is potentially harmful to the regulators, where internal operating currents are in the nanoampere range. The 0.047μF capacitor on the device side of the switch will limit inputs to a safe level around 2V/μs. Use of this capacitor is suggested in all applications. In severe rate-of-rise cases, it may be advisable to use an RC network on the SHutDowN pin to delay output turn-on. Battery charging surges, transients, and assorted noise signals should be kept from the regulators by RC filtering, zener protection, or even fusing.



NOTES:

- 1. S₁ when closed disables output current limiting.
- Close S₂ for V_{OUT1}, open S₂ for V_{OUT2}.

3.
$$V_{OUT} = \frac{R_2 + R_1}{R_1} V_{SET}$$
.

- 4. IQ quiescent currents measured at GND pin by meter M.
- S₃ when ON, permits normal operation, when OFF, shuts down both V_{OUT1} and V_{OUT2}.

FIGURE 7. ICL7663S TEST CIRCUIT

Output Voltages - The resistor divider R_2/R_1 is used to scale the reference voltage, V_{SET} , to the desired output using the formula $V_{OUT} = (1 + R_2/R_1) \, V_{SET}$. Suitable arrangements of these resistors, using a potentiometer, enables exact values for V_{OUT} to be obtained. In most applications the potentiometer may be eliminated by using the ICL7663SA. The ICL7663SA has V_{SET} voltage guaranteed to be 1.29V $\pm 15 \text{mV}$ and when used with $\pm 1\%$ tolerance resistors for R_1 and R_2 the initial output voltage will be within $\pm 2.7\%$ of ideal.

The low leakage current of the V_{SET} terminal allows R_1 and R_2 to be tens of megohms for minimum additional quiescent drain current. However, some load current is required for proper operation, so for extremely low-drain applications it is necessary to draw at least $1\mu A$. This can include the current for R_2 and R_1 .

Output voltages up to nearly the V_{IN} supply may be obtained at low load currents, while the low limit is the reference voltage. The minimum input-output differential in each regulator is obtained using the V_{OUT_1} , terminal. The input-output differential increases to 1.5V when using V_{OUT_2} .

Output Currents - Low output currents of less than 5mA are obtained with the least input-output differential from the V_{OUT_1} terminal (connect V_{OUT_2} to V_{OUT_1}). Where higher currents are needed, use V_{OUT_2} (V_{OUT_1} , should be left open in this case).

High output currents can be obtained only as far as package dissipation allows. It is strongly recommended that output current-limit sensing be used in such cases.

Current-Limit Sensing - The on-chip comparator (C in the Functional Diagram) permits shutdown of the regulator

output in the event of excessive current drain. As Figure 8 shows, a current-limiting resistor, R_{CL} , is placed in series with $V_{\rm CUT2}$ and the SENSE terminal is connected to the load side of R_{CL} . When the current through R_{CL} is high enough to produce a voltage drop equal to V_{CL} (0.5V) the voltage feedback is by-passed and the regulator output will be limited to this current. Therefore, when the maximum load current ($I_{\rm LOAD}$) is determined, simply divide V_{CL} by $I_{\rm LOAD}$ to obtain the value for $R_{\rm CL}$.




FIGURE 8. POSITIVE REGULATOR WITH CURRENT LIMIT


Logic-Controllable Shutdown - When equipment is not needed continuously (e.g., in remote data-acquisition systems), it is desirable to eliminate its drain on the system until it is required. This usually means switches, with their unreliable contacts. Instead, the ICL7663S can be shut down by a logic signal, leaving only Iq (under 4µA) as a drain on the power source. Since this pin must not be left open, it should be tied to ground if not needed. A voltage of less than 0.3V for the ICL7663S will keep the regulator ON, and a voltage level of more than 1.4V but less than V+IN will turn the outputs OFF. If there is a possibility that the control signal could exceed the regulator input (V+IN) the current from this signal should be limited to 100µA maximum by a high value (1M Ω) series resistor. This situation may occur when the logic signal originates from a system powered separately from that of the regulator.

Additional Circuit Precautions - This regulator has poor rejection of voltage fluctuations from AC sources above 10Hz or so. To prevent the output from responding (where this might be a problem), a reservoir capacitor across the load is advised. The value of this capacitor is chosen so that the regulated output voltage reaches 90% of its final value in 20ms. From:

$$I = C \frac{\Delta V}{\Delta t}, C = I_{OUT} \frac{(20 \times 10^{-3})}{0.9V_{OUT}} = 0.022 \frac{I_{OUT}}{V_{OUT}}$$

In addition, where such a capacitor is used, a current-limiting resistor is also suggested (see "Current-Limit Sensing").

Producing Output Voltages with Negative Temperature Coefficients - The ICL7663S has an additional output which is 0.9V relative to GND and has a tempco of +2.5mV/°C. By applying this voltage to the inverting input of amplifier A (i.e., the V_{SET} pin), output voltages having negative TC may be produced. The TC of the output voltage is controlled by the R₂/R₃ ratio (see Figure 9 and its design equations).



EQ. 1:
$$V_{OUT} = V_{SET} \left(1 + \frac{R_2}{R_1}\right) + \frac{R_2}{R_3} (V_{SET} - V_{TC})$$

EQ. 2: TC
$$V_{OUT} = -\frac{R_2}{R_3}$$
 (TC V_{TC}) in mV/°C

Where: $V_{SET} = 1.3V$ $V_{TC} = 0.9V$

 $TCV_{TC} = +2.5mV/^{\circ}C$

FIGURE 9. GENERATING NEGATIVE TEMPERATURE COEFFICIENTS

Applications

Boosting Output Current with External Transistor

The maximum available output current from the ICL7663S is 40mA. To obtain output currents greater than 40mA, an external NPN transistor is used connected as shown in Figure 10.




FIGURE 10. BOOSTING OUTPUT CURRENT WITH EXTERNAL TRANSISTOR

Generating a Temperature Compensated Display Drive Voltage

Temperature has an important effect in the variation of threshold voltage in multiplexed LCD displays. As temperature rises, the threshold voltage goes down. For applications where the display temperature varies widely, a

temperature compensated display voltage, V_{DISP} can be generated using the ICL7663S. This is shown in Figure 11 for the ICM7233 triplexed LCD display driver.




FIGURE 11. GENERATING A MULTIPLEXED LCD DISPLAY DRIVE VOLTAGE