3SE5122-0CC02-1AA7

Data sheet



Position switch Metal enclosure 56 mm wide Device connection 3 x (M20 x 1.5) 1 NO/1 NC quick action contacts Rounded plunger, with 3 mm overtravel made of stainless steel Actuating/restoring force 30 N only available as complete unit

product brand name	SIRIUS		
product designation	Mechanical position switches		
product type designation	3SE5		
manufacturer's article number			
 of the supplied switching contacts 	3SE5000-0CA00		
suitability for use safety switch	Yes		
General technical data			
product function positive opening	Yes		
insulation voltage rated value	400 V		
degree of pollution	class 3		
surge voltage resistance rated value	6 kV		
protection class IP	IP66/IP67		
shock resistance			
• according to IEC 60068-2-27	30g / 11 ms		
vibration resistance according to IEC 60068-2-6	0.35 mm/5g		
mechanical service life (switching cycles) typical	3 000 000		
electrical endurance (switching cycles) at AC-15 at 230 V typical	100 000		
electrical endurance (switching cycles) with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026 typical	3 000 000		
Electrical operating cycles in one hour with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026	6 000		
thermal current	10 A		
material of the enclosure of the switch head	metal		
reference code according to IEC 81346-2	В		
continuous current of the C characteristic MCB	1 A; for a short-circuit current smaller than 400 A		
continuous current of the quick DIAZED fuse link	10 A; for a short-circuit current smaller than 400 A		
continuous current of the DIAZED fuse link gG	6 A		
active principle	mechanical		
repeat accuracy	0.05 mm		
Substance Prohibitance (Date)	07/01/2006		
minimum actuating force in directions of actuation	30 N		
length of the sensor	103.5 mm		
width of the sensor	56 mm		
design of the switching contact	mechanical		
operating frequency rated value	50 60 Hz		
number of NC contacts for auxiliary contacts	1		
number of NO contacts for auxiliary contacts	1		
operational current at AC-15			

• at 24 V rated value	6 A		
at 125 V rated value	6 A		
 at 240 V rated value 	6 A		
at 400 V rated value	_ 4 A		
operational current at DC-13			
at 24 V rated value	3 A		
at 125 V rated value	0.55 A		
at 250 V rated value	0.27 A		
at 400 V rated value	0.12 A		
design of the interface for safety-related communication	without		
Enclosure			
design of the housing	_ block, wide		
material of the enclosure	metal		
coating of the enclosure	_ cathodic dip coating		
design of the housing according to standard	No		
Drive Head			
design of the actuating element	Rounded plunger, high-grade steel plunger		
standard-compliant actuator head	EN 50041, design B		
shape of the switch head	rounded		
design of the switching function	positive opening		
circuit principle	snap-action contacts		
number of switching contacts safety-related	1		
Connections/ Terminals			
type of electrical connection	screw-type terminals		
type of connectable conductor cross-sections			
• solid	1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²)		
 finely stranded with core end processing 	1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²)		
 at AWG cables solid 	1x (20 16), 2x (20 18)		
at AWG cables stranded	1x (20 16), 2x (20 18)		
cable entry type	3x (M20 x 1.5)		
Communication/ Protocol			
design of the interface	without		
Ambient conditions			
ambient temperature			
during operation	-25 +85 °C		
during storage	40 +90 °C		
explosion protection category for dust	none		
Installation/ mounting/ dimensions			
mounting position	any		
fastening method	screw fixing		
Certificates/ approvals			
General Product Approval			

General Product Approval





Confirmation







Functional Safety/Safety of Machinery	Declaration of Conformity	Test Certificates	other
---	---------------------------	-------------------	-------

Type Examination Certificate





Type Test Certificates/Test Report

Confirmation

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE5122-0CC02-1AA7

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE5122-0CC02-1AA7

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3SE5122-0CC02-1AA7

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SE5122-0CC02-1AA7&lang=en

1/26/2022 last modified: