






REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
A	NEW	INTERIM INITIAL RELEASE.	2017.06.03	谢青平
B	更新图纸		2022.06.22	钟建虾




Specifications
 Voltage rating:100V AC/DC
 Current Rating:2A AC/DC
 Withstanding Voltage:800V AC
 Insulation Resistance:1000MΩ Min.
 Contact Resistance:20mΩ Max.
 After environmental testing: ≤20mΩ
 Operating Temperature:-25°C to +85°C
 Materials
 Insulator Material:PA66 94V-0
 All materials must meet GREENCONN hazardous substances control standards.
 Mating With:
 Wafer:GWFB123-A001
 Terminal:GRF143-T1



4P以上 示意图



3P 示意图



2P 示意图

Ordering Information

GWFB181 - XX A XX

No. of Pins
02~16

Materials /Color
M=YN66/White
M1=YN66/Black

No. of Pins/Row	Dimension Information	
	A	B
02	2.00	4.60
03	4.00	6.60
04	6.00	8.60
05	8.00	10.60
06	10.00	12.60
07	12.00	14.60
08	14.00	16.60
09	16.00	18.60
10	18.00	20.60
11	20.00	22.60
12	22.00	24.60
13	24.00	26.60
14	26.00	28.60
15	28.00	30.60
16	30.00	32.60

格菱股份有限公司
Greenconn Corporation

GENERAL TOLERANCE	
X.*±	X.±
.X*±2.0°	.X±0.30
.XX*±1.0°	.XX±0.20
.XXX*±	.XXX±0.10

DESIGNED: 钟建虾
 CHECKED:
 APPROVED:

DATE: 2022.06.22
 DATE:
 DATE:

DWG. NO.
GWFB181-HA
 PART NO.
GWFB181-XXAXX

TITLE.
Pitch 2.0 Housing