CTML1206HCF

Series From .47µH to 4.7µH



CHARACTERISTICS

Description: Ferrite core, multi-layer chip inductor. Magnetic shielded.

Applications: LC resonant circuits such as oscillator and signal generators, RF filters, disk drives, audio and video equipment, TV, radio and telecomunication equipment.

Operating Temperature: -40° C to 125° C Inductance Tolerance: $M = \pm 20\%$

Testing: Inductance and Q are tested on an HP4287A at 1MHz,

250mV

Packaging: Tape & Reel.

Marking: Reels marked with inductance code and tolerance.

Miscellaneous: RoHS Compliant.

Additional Information: Additional electrical & physical

information available upon request.

 $\label{thm:condition} \textbf{Samples available. See website for ordering information.}$

SPECIFICATIONS

Parts are available in ±20% inductance tolerance only.

Part Number	Inductance (µH)	Test Freq. (MHz)	SRF Min. (MHz)	DCR ±30% (Ω)	IDC Max. (mA)
CTML1206HCF-R47M CTML1206HCF-R68M CTML1206HCF-R82M	0.47 0.68 0.82	1MHz 1MHz 1MHz	100 90 80	0.14 0.15 0.16	1500 1500 1500
CTML1206HCF-1R0M CTML1206HCF-1R2M CTML1206HCF-1R5M CTML1206HCF-1R5M CTML1206HCF-2R2M CTML1206HCF-3R3M CTML1206HCF-3R3M CTML1206HCF-4R7M	1.0 1.2 1.5 1.8 2.2 3.3 4.7	1MHz 1MHz 1MHz 1MHz 1MHz 1MHz 1MHz	60 60 50 50 40 30 20	0.16 0.16 0.20 0.20 0.22 0.22 0.24 0.30	1400 1400 1200 1200 1200 1100 1100

PHYSICAL DIMENSIONS

Size	A	В	C	D
mm inches	3.2±0.2 0.126±0.008	1.60±0.2 0.062±0.008	1.1±0.2 0.043±0.008	0.5±0.3 0.020±0.012
		→ D ←		
				C
-	,	A	В	
-		A	B	

