SIEMENS

Data sheet

3SE5162-0DA00



Basic switch for position switch 3SE5162 Metal enclosure XL, 56 mm wide Device connection $3x(M20 \times 1.5)$ IP66/IP67 2 x (1 NO/2 NC) Slow-action contacts with make-before-break without actuator head

product brand name	SIRIUS		
product designation	Mechanical safety switches		
product type designation	3SE5		
manufacturer's article number			
 of the supplied switching contacts 	1x 3SE5000-0MA00, 1x 3SE5060-0MA00		
 of the supplied empty enclosure with cover 	3SE5162-0AA00		
suitability for use safety switch	Yes		
General technical data			
product function positive opening	Yes		
insulation voltage rated value	250 V		
degree of pollution	class 3		
surge voltage resistance rated value	4 kV		
protection class IP	IP66/IP67		
shock resistance			
 according to IEC 60068-2-27 	30g / 11 ms		
vibration resistance according to IEC 60068-2-6	0.35 mm/5g		
mechanical service life (switching cycles) typical	5 000 000		
electrical endurance (switching cycles) at AC-15 at 230 V typical	100 000		
electrical endurance (switching cycles) with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026 typical	5 000 000		
Electrical operating cycles in one hour with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026	6 000		
thermal current	10 A		
reference code according to IEC 81346-2	В		
continuous current of the C characteristic MCB	1 A; for a short-circuit current smaller than 400 A		
continuous current of the quick DIAZED fuse link	10 A; for a short-circuit current smaller than 400 A		
continuous current of the DIAZED fuse link gG	6 A		
active principle	mechanical		
repeat accuracy	0.05 mm		
Substance Prohibitance (Date)	07/01/2006		
minimum actuating force in directions of actuation	30 N		
length of the sensor	107.7 mm		
width of the sensor	56 mm		
design of the switching contact	mechanical		
operating frequency rated value	50 60 Hz		
number of NC contacts for auxiliary contacts	4		
number of NO contacts for auxiliary contacts	2		
operational current at AC-15			

 at 24 V rated value 	alue	6	A				
 at 125 V rated v 	value	6	A				
 at 240 V rated v 	value	6	A				
 at 400 V rated v 	value	4	A				
operational current	at DC-13						
 at 24 V rated value 	alue	3	A				
• at 125 V rated	value	0	55 A				
• at 250 V rated	value	0	27 A				
• at 400 V rated	value	0	0.12 A				
design of the interface	e for safety-related commu	inication w	without				
Enclosure	, ,						
design of the housin	20	h	ock, wide				
material of the enclo	-		metal				
				ting			
_	coating of the enclosure design of the housing according to standard			cathodic dip coating No			
-	ig according to standard		0				
Drive Head							
				Other, without, basic switch			
design of the switching function			Positive opening with appropriate positive opening actuator head				
circuit principle				slow-action contacts			
number of switching contacts safety-related 4							
Connections/ Termina	als						
type of electrical co	nnection	s	crew-type terminals				
type of connectable	conductor cross-section	าร					
 solid 		1	1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²)				
 finely stranded with core end processing 		1	1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²)				
 at AWG cables 	at AWG cables solid		1x (20 16), 2x (20 18)				
at AWG cables stranded			1x (20 16), 2x (20 18)				
cable entry type			3x (M20 x 1.5)				
Communication/ Prot	ocol						
		10	ithout				
design of the interface		Vi	without				
Ambient conditions							
ambient temperature			05				
during operation			-25 +85 °C				
during storage			-40 +90 °C				
explosion protection category for dust		n	none				
Installation/ mounting	/ dimensions						
mounting position		а	ny				
fastening method		s	screw fixing				
Certificates/ approval							
General Product Ap	proval						
	Confirmation	\frown	\sim				
(SP)	oommation	(\mathfrak{m})	<i>(</i> Ui)	FAC	103		
				ΓΠΙ	ΓΠΙ		
CSA		ccc	UL				
Functional							
Safety/Safety of	Declaration of Conform	nity	Test Certificates	other			
Machinery							
Type Examination	UK	~~	Type Test Certific-	Confirmation			
Certificate		(E	ates/Test Report				
		EG-Konf.					
Eurther information							

Further information

Information- and Downloadcenter (Catalogs, Brochures,...) https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE5162-0DA00


Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE5162-0DA00

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3SE5162-0DA00

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SE5162-0DA00&lang=en



last modified:

3/23/2022 🖸