SIEMENS

Data sheet

3SE5212-0CC05



Position switch Metal enclosure according to EN 50047, 31 mm Device connection 1 x (M20 x 1.5) 1 NO/1 NC quick action contacts (replaceable) Rounded plunger, Form B

we duct buyed name	SIRIUS
product brand name	
product designation	Mechanical position switches
product type designation	3SE5
manufacturer's article number	
of the supplied switching contacts	<u>3SE5000-0CA00</u>
of the supplied empty enclosure with cover	<u>3SE5212-0AC05</u>
suitability for use safety switch	Yes
General technical data	
product function positive opening	Yes
insulation voltage rated value	400 V
degree of pollution	class 3
surge voltage resistance rated value	6 kV
protection class IP	IP66/IP67
shock resistance	
according to IEC 60068-2-27	30g / 11 ms
vibration resistance	
 according to IEC 60068-2-6 	0.35 mm/5g
mechanical service life (switching cycles) typical	15 000 000
electrical endurance (switching cycles) at AC-15 at 230 V typical	100 000
electrical endurance (switching cycles) with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026 typical	10 000 000
Electrical operating cycles in one hour with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026	6 000
thermal current	10 A
material of the enclosure of the switch head	metal
reference code according to IEC 81346-2	В
continuous current of the C characteristic MCB	1 A; for a short-circuit current smaller than 400 A
continuous current of the quick DIAZED fuse link	10 A; for a short-circuit current smaller than 400 A
continuous current of the DIAZED fuse link gG	6 A
active principle	mechanical
repeat accuracy	0.05 mm
Substance Prohibitance (Date)	07/01/2006
minimum actuating force in directions of actuation	20 N
length of the sensor	75.7 mm
width of the sensor	31 mm
design of the switching contact	mechanical
operating frequency rated value	50 60 Hz
number of NC contacts for auxiliary contacts	1

Certificates/ approvals General Product Approval Image: Confirmation of Confirmation of Conformity Machinery Confirmation of Conformity	ion ERC ERC Test Certificates other
Certificates/ approvals General Product Approval	
Certificates/ approvals	screw fixing
-	screw fixing
	screw fixing
fastening method	-
mounting position	any
Installation/ mounting/ dimensions	
• during storage explosion protection category for dust	none
during operation	-25 +85 °C -40 +90 °C
ambient temperature	25 105 %
Ambient conditions	
design of the interface	without
Communication/ Protocol	
cable entry type	1x (M20 x 1.5)
at AWG cables stranded	1x (20 16), 2x (20 18)
• at AWG cables solid	1x (20 16), 2x (20 18)
 finely stranded with core end processing 	1x (0.5 1.5 mm ²), 2x (0.5 0.75 mm ²)
solid	1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²)
type of electrical connection type of connectable conductor cross-sections	screw-type terminals
Connections/ Terminals	scrow type terminals
number of switching contacts safety-related	1
circuit principle	snap-action contacts
design of the switching function	positive opening
shape of the switch head	rounded
standard-compliant actuator head	EN 50047, design B
design of the actuating element	Rounded plunger, plastic plunger
Drive Head	
design of the housing according to standard	Yes
coating of the enclosure	cathodic dip coating
material of the enclosure	metal
design of the housing	block, narrow
Enclosure	without
• at 400 V rated value design of the interface for safety-related communication	0.12 A without
• at 250 V rated value	0.27 A
• at 125 V rated value	0.55 A
• at 24 V rated value	3 A
operational current at DC-13	
• at 400 V rated value	4 A
• at 240 V rated value	6 A
at 120 V rated value	6 A
at 24 V rated value	6 A
number of NO contacts for auxiliary contacts operational current at AC-15	

Further information

Information- and Downloadcenter (Catalogs, Brochures,...) https://www.siemens.com/ic10 Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE5212-0CC05 Cax online generator http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE5212-0CC05 Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/3SE5212-0CC05 Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SE5212-0CC05&lang=en

last modified:

3/23/2022 🖸