

## Features

- Ultra low leakage: nA level
- Operating voltage: 15V
- Ultra low capacitance 0.8pF (typ)
- Low clamping voltage
- Complies with following standards:
  - IEC 61000-4-2 (ESD) immunity test
    - Air discharge:  $\pm 30\text{kV}$
    - Contact discharge:  $\pm 30\text{kV}$
  - IEC61000-4-4 (EFT) 40A (5/50ns)
  - IEC61000-4-5 (Lightning)10A (8/20 $\mu\text{s}$ )
- RoHS Compliant


## Mechanical Characteristics

- Package: SOT-143
- Lead Finish: Matte Tin
- Case Material: "Green" Molding Compound.
- UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 3 per J STD 020
- Shipping Qty :3000pcs/7Inch Tape & Reel

## Applications

- Ethernet - 10/100 Base T
- Cellular Phones
- Audio & Video Inputs
- FireWire, SCSI & USB Interfaces

## Dimensions and Pin Configuration



**Marking: 15L**

**Absolute Maximum Ratings** (Tamb=25°C unless otherwise specified)


Parameter	Symbol	Value	Unit
Peak Pulse Power (8/20µs)	Ppk	350	W
Peak Pulse Current (8/20µs)	Ipp	10	A
ESD per IEC 61000-4-2 (Air)	VESD	±30	kV
ESD per IEC 61000-4-2 (Contact)		±30	
Operating Temperature Range	TJ	-55 to +125	°C
Storage Temperature Range	Tstg	-55 to +150	°C

**Electrical Characteristics** (TA=25°C unless otherwise specified)


Parameter	Symbol	Min	Typ	Max	Unit	Test Condition
Reverse Working Voltage	VRWM			15	V	
Breakdown Voltage	VBR	16			V	IT = 1mA
Reverse Leakage Current	IR			0.2	µA	VRWM = 15V
Clamping Voltage	VC			25	V	Ipp = 1A (8 x 20µs pulse)
Clamping Voltage	VC			33	V	Ipp = 10A (8 x 20µs pulse)
Junction Capacitance	CJ		0.8	1.0	pF	VR = 0V, f = 1MHz (IO to GND)

**Typical Performance Characteristics ( $T_A=25^\circ\text{C}$  unless otherwise Specified)**


**Fig1. 8/20 $\mu\text{s}$  Pulse Waveform**




**Fig2. ESD Pulse Waveform (according to IEC 61000-4-2)**



**Fig3. Power Derating Curve**



### Outline Drawing - SOT-143



### Land Pattern -SOT-143

