## **SIEMENS**

## **Data sheet**

## 3SE5232-0LK62-1AJ0



Position switch Plastic 31 mm according to EN 50047 Increased corrosion protection Device connection 1 x (M20 x 1.5) 1 NO/2 NC quick action contacts Twist lever, adjustable length with grid hole on the right and/or left adjustable, with Stainless steel lever and plastic roller 19 mm functional at  $^{\rm 40}$  °C Shock and vibration test according to EN 61373, Category 1B

product brand name	SIRIUS		
product designation	Mechanical position switches		
product type designation	3SE5		
manufacturer's article number			
<ul> <li>of the supplied actuator head for position switches</li> </ul>	3SE5000-0AK00-1AJ0		
<ul> <li>of the supplied operating lever</li> </ul>	3SE5000-0AA62-1AJ0		
of the supplied switching contacts	3SE5000-0LA00		
suitability for use safety switch	Yes		
General technical data			
product function positive opening	Yes		
insulation voltage rated value	400 V		
degree of pollution	class 3		
surge voltage resistance rated value	6 kV		
protection class IP	IP65		
shock resistance			
<ul><li>according to IEC 60068-2-27</li></ul>	30g / 11 ms		
<ul> <li>for railway applications according to EN 61373</li> </ul>	Category 1, Class B		
vibration resistance			
<ul> <li>according to IEC 60068-2-6</li> </ul>	0.35 mm/5g		
<ul> <li>for railway applications according to EN 61373</li> </ul>	Category 1, Class B		
mechanical service life (switching cycles) typical	15 000 000		
electrical endurance (switching cycles) at AC-15 at 230 V typical	100 000		
electrical endurance (switching cycles) with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026 typical	10 000 000		
Electrical operating cycles in one hour with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026	6 000		
thermal current	10 A		
material of the enclosure of the switch head	plastic		
reference code according to IEC 81346-2	В		
continuous current of the C characteristic MCB	1 A; for a short-circuit current smaller than 400 A		
continuous current of the quick DIAZED fuse link	10 A; for a short-circuit current smaller than 400 A		
continuous current of the DIAZED fuse link gG	6 A		
active principle	mechanical		
repeat accuracy	0.05 mm		
Substance Prohibitance (Date)	07/01/2006		
minimum actuating torque in directions of actuation	0.25 N·m		
length of the sensor	182 mm		
width of the sensor	31 mm		

design of the switching contact	mechanical		
operating frequency rated value	50 60 Hz		
number of NC contacts for auxiliary contacts	2		
number of NO contacts for auxiliary contacts	1		
operational current at AC-15	·		
at 24 V rated value	6 A		
at 120 V rated value	6 A		
• at 240 V rated value	6 A		
at 400 V rated value	4 A		
operational current at DC-13			
at 24 V rated value	3 A		
at 125 V rated value	0.55 A		
at 250 V rated value	0.27 A		
at 400 V rated value	0.12 A		
design of the interface for safety-related communication	without		
Enclosure			
design of the housing	block, narrow		
material of the enclosure	plastic		
coating of the enclosure	Other types		
design of the housing according to standard	Yes		
Drive Head			
design of the actuating element	Adjustable twist lever, adjustable-length metal lever with positive fit, 100		
accign of the actualing cicinent	mm long, plastic roller 19 mm		
standard-compliant actuator head	EN 50047, design A		
shape of the switch head	roller		
design of the switching function	positive opening		
circuit principle	snap-action contacts		
number of switching contacts safety-related	2		
Connections/ Terminals			
type of electrical connection	screw-type terminals		
type of connectable conductor cross-sections			
• solid	1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²)		
<ul> <li>finely stranded with core end processing</li> </ul>	1x (0.5 1.5 mm²), 2x (0.5 0.75 mm²)		
<ul> <li>at AWG cables solid</li> </ul>	1x (20 16), 2x (20 18)		
<ul> <li>at AWG cables stranded</li> </ul>	1x (20 16), 2x (20 18)		
cable entry type	1x (M20 x 1.5)		
Communication/ Protocol			
design of the interface	without		
Ambient conditions			
ambient temperature			
during operation	-40 +85 °C		
during storage	-40 +90 °C		
explosion protection category for dust	none		
Installation/ mounting/ dimensions			
mounting position	any		
fastening method	screw fixing		
Certificates/ approvals			
General Product Approval			
General Floudct Approval			



Confirmation









Functional Safety/Safety of Machinery	Declaration of Conformity	Test Certificates	other
---	---------------------------	-------------------	-------



Type Test Certificates/Test Report

Confirmation

## **Further information**

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE5232-0LK62-1AJ0

Cax online generator


 $\underline{http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en\&mlfb=3SE5232-0LK62-1AJ0}$ 


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3SE5232-0LK62-1AJ0

 $Image\ database\ (product\ images,\ 2D\ dimension\ drawings,\ 3D\ models,\ device\ circuit\ diagrams,\ EPLAN\ macros,\ ...)$ 

http://www.automation.siemens.com/bilddb/cax\_de.aspx?mlfb=3SE5232-0LK62-1AJ0&lang=en





last modified: 3/23/2022 🖸