

8A, 20V - 100V Schottky Barrier Surface Mount Rectifier

FEATURES

- AEC-Q101 qualified
- Low power loss, high efficiency
- Ideal for automated placement
- Guard ring for over-voltage protection
- High surge current capability
- Moisture sensitivity level: level 1, per J-STD-020
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

APPLICATIONS

- Low voltage, high freq. inverter
- DC/DC converter
- Freewheeling diodes
- Reverse battery protection
- Car lighting

MECHANICAL DATA

- Case: DO-214AB (SMC)
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- Polarity: Indicated by cathode band
- Weight: 0.210g (approximately)

KEY PARAMETERS				
PARAMETER VALUE UN				
I _F	8	А		
V _{RRM}	20 - 100	V		
I _{FSM}	150 A			
T _{J MAX}	125, 150 °C			
Package	DO-214AB (SMC)			
Configuration	Single die			



DO-214AB (SMC)



ABSOLUTE MAXIMUM RATINGS (T _A = 25°C unless otherwise noted)								
PARAMETER	SYMBOL	SK 82CH	SK 83CH	SK 84СН	SK 85CH	SK 86CH	SK 810CH	UNIT
Marking code on the device		SK 82C	SK 83C	SK 84C	SK 85C	SK 86C	SK 810C	
Repetitive peak reverse voltage	V _{RRM}	20	30	40	50	60	100	V
Reverse voltage, total rms value	V _{R(RMS)}	14	21	28	35	42	70	V
Forward current	I _F	8					А	
Surge peak forward current, 8.3ms single half sine-wave superimposed on rated load	I _{FSM}	I _{FSM} 150				A		
Critical rate of rise of off-state voltage	dV/dt 10,000			V/µs				
Junction temperature	TJ	- 55 to +125 - 55 to +150			°C			
Storage temperature	T _{STG}	- 55 to +150			°C			



THERMAL PERFORMANCE				
PARAMETER	SYMBOL	ТҮР	UNIT	
Junction-to-ambient thermal resistance	R _{eja}	20	°C/W	

ELECTRICAL SPECIFICATIONS ($T_A = 25^{\circ}C$ unless otherwise noted)						
PARAMETER		CONDITIONS	SYMBOL	ТҮР	MAX	UNIT
(1)	SK82CH SK83CH SK84CH	I _F = 8A, T _J = 25°C	V _F	-	0.55	V
Forward voltage ⁽¹⁾	SK85CH SK86CH			-	0.75	V
	SK810CH			-	0.90	V
Reverse current @ rated $V_R^{(2)}$		$T_J = 25^{\circ}C$	I _R	-	0.5	mA
Reverse current @ rated V _R ⁽²⁾	SK82CH SK83CH SK84CH	- T _J = 100°C	I _R -	-	15	mA
	SK85CH SK86CH SK810CH			-	10	mA

Notes:

- 1. Pulse test with PW = 0.3ms
- 2. Pulse test with PW = 30ms

ORDERING INFORMATION				
ORDERING CODE ⁽¹⁾	PACKAGE	PACKING		
SK8xCH	DO-214AB (SMC)	3,000 / Tape & Reel		

Notes:

1. "x" defines voltage from 20V(SK82CH) to 100V(SK810CH)



CHARACTERISTICS CURVES

 $(T_A = 25^{\circ}C \text{ unless otherwise noted})$




Fig.3 Typical Reverse Characteristics

Fig.1 Forward Current Derating Curve




Fig.2 Typical Junction Capacitance

Fig.4 Typical Forward Characteristics




Fig.5 Maximum Non-Repetitive Forward Surge Current



CHARACTERISTICS CURVES

 $(T_A = 25^{\circ}C \text{ unless otherwise noted})$






Fig.6 Typical Transient Thermal Characteristics




PACKAGE OUTLINE DIMENSIONS





DIM.	Unit	(mm)	Unit (inch)		
	Min.	Max.	Min.	Max.	
A	2.00	2.62	0.079	0.103	
A1	0.10	0.20	0.004	0.008	
b	2.90	3.20	0.114	0.126	
с	0.15	0.31	0.006	0.012	
D	5.59	6.22	0.220	0.245	
E	7.75	8.13	0.305	0.320	
E1	6.60	7.11	0.260	0.280	
L	1.00	1.60	0.039	0.063	

SUGGESTED PAD LAYOUT



Symbol	Unit (mm)	Unit (inch)
A	3.30	0.130
В	2.50	0.098
С	6.90	0.272
D	4.40	0.173
E	9.40	0.370

MARKING DIAGRAM



- P/N = Marking Code
- G = Green Compound

YW = Date Code

F = Factory Code



Taiwan Semiconductor

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.