







403DMQ080 403DMQ100 SCHOTTKY RECTIFIER



Features

- 175℃ T_J operation
- Center tap module
- High purity, high temperature epoxy encapsulation for
- enhanced mechanical strength and moisture resistance
- Low forward voltage drop
- High frequency operation
- Guard ring for enhanced ruggedness and long term reliability
- Base plate: Nickel plated; Terminals: Nickel plated
- This is a Pb Free Device
- All SMC parts are traceable to the wafer lot
- Additional testing can be offered upon request

Circuit Diagram



Applications

- · High current switching power supply
- Plating power supply
- Free-Wheeling diodes
- Reverse battery protection
- Converters
- UPS System
- Welding

Maximum Ratings(limiting values, at 25 °C unless otherwise specified)

Characteristics	Symbol	Condition		Max.	Units
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage	V _{RRM} V _{RWM}	-	80	403CMQ080/R	V
DC Blocking Voltage	VRWM VR		100	403CMQ100/R	V
Average Rectified Forward Current	I _{F(AV)}	50% duty cycle @T _C =85°C,	200(Per Leg)		А
Average rectified Forward Outrent		rectangular wave form	400(Per Device)		
Peak One Cycle Non-Repetitive Surge Current (Per Leg)	I _{FSM}	8.3 ms, half Sine pulse	3960		Α
Non-Repetitive Avalanche Energy(Peg Leg)	E _{AS}	T _J =25℃,I _{AS} =1A,L=30mH	15		mJ
Repetitive Avalanche Current (Peg Leg)	I _{AR}	Current decaying linearly to zero in 1 µsec Frequency limited by T _J max. V _A =1.5×V _R typical	1		А

- China Germany Korea Singapore United States •
- http://www.smc-diodes.com sales@ smc-diodes.com •









Electrical Characteristics:

Characteristics	Symbol	Condition	Тур.	Max.	Units
Forward Voltage Drop(Per Leg)*	V _{F1}	@ 200A, Pulse, T _J = 25 °C @ 400A, Pulse, T _J = 25 °C	0.80 0.88	0.83 0.97	V
	V _{F2}	@ 200A, Pulse, T _J = 125 °C @ 400A, Pulse, T _J = 125 °C	0.70 0.77	0.75 0.82	V
Reverse Current(Per Leg)*	I _{R1}	@V _R = rated V _R , T _J = 25 °C	0.003	6	mA
	I _{R2}	$@V_R = \text{rated } V_{R}, T_J = 125 ^{\circ}\text{C}$	1.2	140	mA
Junction Capacitance(Per leg)	Ст	$@V_R = 5V, T_C = 25 °C$ $f_{SIG} = 1MHz$	5340	5500	pF
Voltage Rate of Change	dv/dt	-	-	10,000	V/μs

^{*} Pulse width < 300 µs, duty cycle < 2%

Thermal-Mechanical Specifications:


Characteristics	Symbol	Condition	Specification		Units
Junction Temperature	Τ _J	-	-55 to +175		°C
Storage Temperature	T_{stg}	-	-55 to +175		°C
Typical Thermal Resistance Junction to Case(Per leg)	R ₀ JC	DC operation	0.30		°C/W
Typical Thermal Resistance Junction to Case(Per package)	R _θ JC	DC operation	0.15		°C/W
Typical Thermal Resistance, case to Heat Sink	$R_{ heta cs}$	Mounting surface, smooth and greased	0.05		°C/W
Mounting Torque	T _M	-	Mounting Torque Terminal	24(min) 35(max) 35(min)	Kg-cm
			Torque	46(max)	
Approximate Weight	wt	-	110 g		g
Case Style	PRM4 Isolated				







Ratings and Characteristics Curves













Mechanical Dimensions PRM4 Isolated(Millimeters/Inches)





SYMBOL	Millimeters		Inches	
STIVIBUL	Min.	Max.	Min.	Max.
А	78.74	81.28	3.100	3.200
В	37.47	42.55	1.475	1.675
С	6.89	7.69	0.271	0.303
D	19.51	24.59	0.768	0.968
E	33.02	38.10	1.300	1.500
F	17.78	20.32	0.700	0.800
G	60.96	64.77	2.400	2.550
Н	17.56	23.55	0.691	0.927
I	90.17	92.71	3.550	3.650
J	3.02	3.68	0.119	0.145
К	15.75	17.50	0.620	0.689

Marking Diagram

1 2 3 SS XXXX 403DMQ080 1 2 3

Where XXXX is YYWW

403DMQ080 = Part name SS = SS YY = Year WW = Week

Cautions: Molding resin

Epoxy resin UL:94V-0

Ordering Information

Device Package		Shipping	
403DMQ SERIES	PRM4 Isolated (Pb-Free)	9 pcs/box	

[•] China - Germany - Korea - Singapore - United States •

[•] http://www.smc-diodes.com - sales@ smc-diodes.com •









DISCLAIMER:

- 1- The information given herein, including the specifications and dimensions, is subject to change without prior notice to improve product characteristics. Before ordering, purchasers are advised to contact the SMC Diode Solutions sales department for the latest version of the datasheet(s).
- 2- In cases where extremely high reliability is required (such as use in nuclear power control, aerospace and aviation, traffic equipment, medical equipment, and safety equipment), safety should be ensured by using semiconductor devices that feature assured safety or by means of users' fail-safe precautions or other arrangement.
- 3- In no event shall SMC Diode Solutions be liable for any damages that may result from an accident or any other cause during operation of the user's units according to the datasheet(s). SMC Diode Solution assumes no responsibility for any intellectual property claims or any other problems that may result from applications of information, products or circuits described in the datasheets.
- 4- In no event shall SMC Diode Solutions be liable for any failure in a semiconductor device or any secondary damage resulting from use at a value exceeding the absolute maximum rating.
- 5- No license is granted by the datasheet(s) under any patents or other rights of any third party or SMC Diode Solutions.
- 6- The datasheet(s) may not be reproduced or duplicated, in any form, in whole or part, without the expressed written permission of SMC Diode Solutions.
- 7- The products (technologies) described in the datasheet(s) are not to be provided to any party whose purpose in their application will hinder maintenance of international peace and safety nor are they to be applied to that purpose by their direct purchasers or any third party. When exporting these products (technologies), the necessary procedures are to be taken in accordance with related laws and regulations..