
## Silicon Carbide Schottky Diode



 $V_{RRM}$ 650 V  $I_{F(T_C = 159^{\circ}C)} =$ 10 A 25 nC Qc

#### **Features**

- Revolutionary Low Built-In Voltage (VBI)
- Gen5 Thin Chip Technology for Low V<sub>F</sub>
- Superior Figure of Merit Qc \* VF
- Enhanced Surge Current Robustness Low Thermal Resistance
- Zero Reverse Recovery
- 100% Avalanche (UIL) Tested
- Excellent dV/dt Ruggedness



## **Advantages**

- Low Conduction Losses for All Load Conditions
- Optimal Price Performance
- Increased System Power Density
- High System Reliability
- Reduced Cooling Requirements
- Temperature Independent Fast Switching
- Easy to Parallel without Thermal Runaway

### **Applications**

- Switched Mode Power Supply (SMPS)
- Solar Inverter
- Server and Telecom Power Supply
- **Battery Charger**
- Uninterruptible Power Supply (UPS)
- Motor Control
- Power Factor Correction (PFC)

Parameter	Symbol	Conditions Values		Unit	Note
Repetitive Peak Reverse Voltage	$V_{RRM}$		650	٧	
Continuous Forward Current	l <sub>F</sub>	T <sub>C</sub> = 100°C, D = 1	23		
		$T_C = 135^{\circ}C$ , D = 1	17	Α	Fig. 4
		$T_C = 159^{\circ}C$ , D = 1	10		
Non-Repetitive Peak Forward Surge Current, Half Sine Wave	<b>I</b> F,SM	$T_C$ = 25°C, $t_P$ = 10 ms	70	Α	
		$T_C$ = 150°C, $t_P$ = 10 ms	56		
Repetitive Peak Forward Surge Current, Half Sine Wave	I <sub>F,RM</sub>	$T_C$ = 25°C, $t_P$ = 10 ms	42	Α	
		$T_C$ = 150°C, $t_P$ = 10 ms	29		
Non-Repetitive Peak Forward Surge Current	I <sub>F,MAX</sub>	T <sub>C</sub> = 25°C, t <sub>P</sub> = 10 μs	350	Α	
i <sup>2</sup> t Value	∫i²dt	$T_C$ = 25°C, $t_P$ = 10 ms	24	A <sup>2</sup> s	
Non-Repetitive Avalanche Energy	E <sub>AS</sub>	L = 2.6 mH, I <sub>AS</sub> = 10 A	131	mJ	
Diode Ruggedness	dV/dt	V <sub>R</sub> = 0 ~ 520 V	200	V/ns	
Power Dissipation	P <sub>TOT</sub>	T <sub>C</sub> = 25°C	157	W	Fig. 3
Operating and Storage Temperature	Tj, Tstg		-55 to 175	°C	




#### **Electrical Characteristics** Values **Parameter Symbol Conditions** Unit Note Min. Typ. Max. $I_F = 10 A$ , $T_i = 25$ °C 1.25 1.4 ٧ Diode Forward Voltage $V_{\text{F}}$ Fig. 1 $I_F = 10 A, T_j = 175$ °C 1.75 $V_R = 650 \text{ V, } T_i = 25^{\circ}\text{C}$ 1 10 **Reverse Current** Fig. 2 $I_R$ μΑ $V_R = 650 \text{ V, } T_i = 175^{\circ}\text{C}$ 194 $V_R = 200 V$ 17 **Total Capacitive Charge** $Q_{\mathbb{C}}$ nC Fig. 7 $V_R = 400 V$ 25 $I_F \leq I_{F,MAX}$ $dI_F/dt = 200 A/\mu s$ $V_R = 200 V$ Switching Time < 10 ts ns $V_R = 400 V$ $V_R = 1 V$ , f = 1MHz466 С **Total Capacitance** рF Fig. 6 $V_R$ = 400 V, f = 1MHz 33

Thermal/Package Characteristics										
Symbol	Conditions	Values			Hait	Note				
		Min.	Тур.	Max.	Unit	Note				
RthJC			0.96		°C/W	Fig. 9				
W <sub>T</sub>			0.3		g					
	Symbol R <sub>thJC</sub>	Symbol Conditions  R <sub>thJC</sub>	Symbol Conditions Min.	$\begin{tabular}{c} Symbol & Conditions & \hline & Values \\ \hline Min. & Typ. \\ R_{thJC} & 0.96 \\ \hline \end{tabular}$	Symbol Conditions Values    Min. Typ. Max.	$\begin{tabular}{l lllllllllllllllllllllllllllllllllll$				









 $I_F = f(V_F, T_j); t_P = 250 \ \mu s$ 

Figure 2: Typical Reverse Characteristics




 $I_R = f(V_R, T_j)$ 

**Figure 3: Power Derating Curves** 



 $P_{TOT} = f(T_C); T_j = 175^{\circ}C$ 


Figure 4: Current Derating Curves (Typical V<sub>F</sub>)



 $I_F = f(T_C)$ ; D =  $t_P/T$ ;  $T_j \le 175$ °C;  $f_{SW} > 10$ kHz




Figure 5: Current Derating Curves (Maximum V<sub>F</sub>)




 $I_F = f(T_C)$ ; D =  $t_P/T$ ;  $T_j \le 175$ °C;  $f_{SW} > 10$ kHz

Figure 6: Typical Junction Capacitance vs Reverse Voltage Characteristics




 $C = f(V_R)$ ; f = 1MHz

Figure 7: Typical Capacitive Charge vs Reverse Voltage Characteristics



 $Q_C = f(V_R)$ ; f = 1MHz


Figure 8: Typical Capacitive Energy vs Reverse Voltage Characteristics



 $E_C = f(V_R)$ ; f = 1MHz




Figure 9: Transient Thermal Impedance



 $Z_{th,jc} = f(t_P,D); D = t_P/T$ 

Figure 10: Forward Curve Model



Forward Voltage, V<sub>F</sub> (V)

 $I_F = f(V_F, T_j)$ 

### Forward Curve Model Equation:

 $I_F = (V_F - V_{BI})/R_{DIFF}(A)$ 

### Built-In Voltage (V<sub>BI</sub>):

$$V_{BI}(T_j) = m \times T_j + n (V)$$
  
 $m = -0.00124 (V/^{\circ}C)$   
 $n = 0.72 (V)$ 


## Differential Resistance (RDIFF):

$$R_{DIFF}(T_j) = a \times T_j^2 + b \times T_j + c (\Omega)$$
  
 $a = 9.62e-07 (\Omega/^{\circ}C^2)$   
 $b = 0.000272 (\Omega/^{\circ}C)$   
 $c = 0.0481 (\Omega)$ 

### **Forward Power Loss Equation:**

$$P_{LOSS} = V_{BI}(T_j) \times I_{AVG} + R_{DIFF}(T_j) \times I_{RMS}^2$$





#### **NOTE**

- 1. CONTROLLED DIMENSION IS INCH. DIMENSION IN BRACKET IS MILLIMETER.
- 2. DIMENSIONS DO NOT INCLUDE END FLASH, MOLD FLASH, MATERIAL PROTRUSIONS.





## Compliance

### **RoHS Compliance**

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS 2), as adopted by EU member states on January 2, 2013 and amended on March 31, 2015 by EU Directive 2015/863. RoHS Declarations for this product can be obtained from your GeneSiC representative.

#### **REACH Compliance**

REACH substances of high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact a GeneSiC representative to insure you get the most up-to-date REACH SVHC Declaration. REACH banned substance information (REACH Article 67) is also available upon request.

### **Disclaimer**

GeneSiC Semiconductor, Inc. reserves right to make changes to the product specifications and data in this document without notice. GeneSiC disclaims all and any warranty and liability arising out of use or application of any product. No license, express or implied to any intellectual property rights is granted by this document.

Unless otherwise expressly indicated, GeneSiC products are not designed, tested or authorized for use in life-saving, medical, aircraft navigation, communication, air traffic control and weapons systems, nor in applications where their failure may result in death, personal injury and/or property damage.

#### **Related Links**

SPICE Models: https://www.genesicsemi.com/sic-schottky-mps/GE10MPS06E/GE10MPS06E\_SPICE.zip
 PLECS Models: https://www.genesicsemi.com/sic-schottky-mps/GE10MPS06E/GE10MPS06E\_PLECS.zip
 CAD Models: https://www.genesicsemi.com/sic-schottky-mps/GE10MPS06E/GE10MPS06E\_3D.zip

• Evaluation Boards: https://www.genesicsemi.com/technical-support

Reliability: https://www.genesicsemi.com/reliability
 Compliance: https://www.genesicsemi.com/compliance
 Quality Manual: https://www.genesicsemi.com/guality

### **Revision History**

Rev 21/Jun: Updated with most recent test data

Supersedes: Rev 20/Jul



www.genesicsemi.com/sic-schottky-mps/

