309CNQ SERIES



Technical Data Data Sheet N1219, Rev. C



309CNQ135/309CNQ150 SCHOTTKY RECTIFIER



Features

- 175℃ T_J operation
- Center tap module
- High purity, high temperature epoxy encapsulation for
- enhanced mechanical strength and moisture resistance
- Low forward voltage drop
- High frequency operation
- Guard ring for enhanced ruggedness and long term reliability
- Base plate: Nickel plated; Terminals: Nickel plated
- This is a Pb Free Device
- All SMC parts are traceable to the wafer lot
- Additional testing can be offered upon request

Applications


- High current switching power supply
- Plating power supply
- Free-Wheeling diodes
- Reverse battery protection
- Converters
- UPS System
- Welding

Maximum Ratings(limiting values, at 25 °C unless otherwise specified)

Characteristics	Symbol	Condition		Max.	Units
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage	V _{RRM} V _{RWM}	-	135	309CNQ135	V
DC Blocking Voltage	VRWM VR		150	309CNQ150	
Average Rectified Forward Current	Irmo	50% duty cycle $@T_c = 110^{\circ}C$,		150(Per Leg)	Δ
Average Rectilieur ofward Current	I _{F(AV)}	rectangular wave form 30		00(Per Device)	~
Peak One Cycle Non-Repetitive Surge Current (Per Leg)	I _{FSM}	8.3 ms, half Sine pulse	1440		А

http://www.smc-diodes.com - sales@ smc-diodes.com •

Circuit Diagram





Technical Data Data Sheet N1219, Rev. C

309CNQ SERIES

RoHS 🗩

Electrical Characteristics:

Characteristics	Symbol	Condition	Тур.	Max.	Units
Forward Voltage Drop(Per Leg)*	V _{F1}	@ 150A, Pulse, T _J = 25 °C @ 300A, Pulse, T _J = 25 °C	0.83 0.93	1.03 1.22	V
	V _{F2}	@ 150A, Pulse, T _J = 125 °C @ 300A, Pulse, T _J = 125 °C	0.72 0.79	0.76 0.82	V
Reverse Current(Per Leg)*	I _{R1}	$@V_R = rated V_{R, T_J} = 25 \circ C$	0.06	3	mA
	I _{R2}	$@V_R = rated V_{R,} T_J = 125 \circ C$	3.40	45	mA
Junction Capacitance(Per leg)	Ст	@V _R = 5V, T _C = 25 °C f _{SIG} = 1MHz	2990	4000	pF
Voltage Rate of Change	dv/dt	-	-	10,000	V/µs

* Pulse width < 300 μs, duty cycle < 2%

Thermal-Mechanical Specifications:

Characteristics	Symbol	Condition	Specification		Units
Junction Temperature	TJ	-	-55 to +175		°C
Storage Temperature	T _{stg}	-	-55 to +175		°C
Typical Thermal Resistance Junction to Case(Per leg)	$R_{\theta JC}$	DC operation	0.40		°C/W
Typical Thermal Resistance Junction to Case(Per package)	$R_{ ext{ heta}JC}$	DC operation	0.20		°C/W
Typical Thermal Resistance, case to Heat Sink	$R_{ hetacs}$	Mounting surface, smooth and greased	0.08		°C/W
Mounting Torque	Тм	-	Mounting Torque Terminal Torque	24(min) 35(max) 35(min) 46(max)	Kg-cm
Approximate Weight	wt	-	91		g
Case Style	PRM4 Non-Isolated				

• http://www.smc-diodes.com - sales@ smc-diodes.com •




309CNQ SERIES

Technical Data Data Sheet N1219, Rev. C



Ratings and Characteristics Curves






309CNQ SERIES

Technical Data Data Sheet N1219, Rev. C




Mechanical Dimensions PRM4 Non-Isolated(Millimeters/Inches)



SYMBOI	Millimeters		Inches		
STIVIDOL	Min.	Max.	Min.	Max.	
А	78.74	81.28	3.100	3.200	
В	37.47	42.55	1.475	1.675	
С	6.89	7.69	0.271	0.303	
D	19.51	24.59	0.768	0.968	
E	33.02	38.10	1.300	1.500	
F	17.78	20.32	0.700	0.800	
G	60.96	64.77	2.400	2.550	
Н	17.26	23.25	0.680	0.915	
I	90.17	92.71	3.550	3.650	
J	3.02	3.68	0.119	0.145	
К	14.30	16.15	0.563	0.636	
L	9.27	10.79	0.365	0.425	
М	4.37	5.28	0.172	0.208	

Marking Diagram



Where XXXX is YYWW

309CNQ135	= Part name
SS	= SS
YY	= Year
WW	= Week

Cautions: Molding resin Epoxy resin UL:94V-0

Ordering Information

Device	Package	Shipping
309CNQ SERIES	PRM4(Non- Isolated) (Pb-Free)	9 pcs/box

• http://www.smc-diodes.com - sales@ smc-diodes.com •



Technical Data Data Sheet N1219, Rev. C

309CNQ SERIES



DISCLAIMER:

1- The information given herein, including the specifications and dimensions, is subject to change without prior notice to improve product characteristics. Before ordering, purchasers are advised to contact the SMC Diode Solutions sales department for the latest version of the datasheet(s).

2- In cases where extremely high reliability is required (such as use in nuclear power control, aerospace and aviation, traffic equipment, medical equipment, and safety equipment), safety should be ensured by using semiconductor devices that feature assured safety or by means of users' fail-safe precautions or other arrangement.

3- In no event shall SMC Diode Solutions be liable for any damages that may result from an accident or any other cause during operation of the user's units according to the datasheet(s). SMC Diode Solution assumes no responsibility for any intellectual property claims or any other problems that may result from applications of information, products or circuits described in the datasheets.
4- In no event shall SMC Diode Solutions be liable for any failure in a semiconductor device or any secondary damage resulting from use

at a value exceeding the absolute maximum rating.

5- No license is granted by the datasheet(s) under any patents or other rights of any third party or SMC Diode Solutions. 6- The datasheet(s) may not be reproduced or duplicated, in any form, in whole or part, without the expressed written permission of SMC Diode Solutions.

7- The products (technologies) described in the datasheet(s) are not to be provided to any party whose purpose in their application will hinder maintenance of international peace and safety nor are they to be applied to that purpose by their direct purchasers or any third party. When exporting these products (technologies), the necessary procedures are to be taken in accordance with related laws and regulations..

http://www.smc-diodes.com - sales@ smc-diodes.com •