


Data Sheet SL15 5R007



Mechanical Specifications (mm)

D:	15.5	± .5
T:	5.0	± .2
Lead Diameter	0.8	± .1
S:	7.8	± .30
L:	38.0	± 1.5
Coating Lead Run Down (straight Leads)	5.0	± .70
B:	7.50	± .40
C:	3.60	± .5



Electrical Specifications

Resistance:	5.0 Ω	± 20 %
Max Steady State Current upto 65°c:	7.00 A	
Max Rec. Energy Rating:	Energy Rating: 50	
Resistance @ 100% Max Current:	0.00	Ω
Resistance @ 50% Max Current:	0.30	Ω
Body Temperature at 100% Max Current:	160.00	°C
Dissipation Constant:	15.9	mw/°c
Thermal Time Constant:	54	Sec.
Material Type (for Beta and Curve):	С	

SL15 5R007		
Date: 04/20/2012	Drawn by: Erin Landis	
Ametherm, Inc. 961 Fairview Drive Carson City, Nevada USA 89701 www.ametherm.com	Approved By: Mehdi Samii	
	Revison: A	