

- AR0521 CMOS sensor
- ALVIUM image processing
- MIPI CSI-2 interface
- Various hardware options

Hardware option: Bare Board

Alvium 1500 C – Powerful camera modules for embedded vision

Revolutionary MIPI CSI-2 camera module

Alvium 1500 C-210 with ON Semi AR0521SR (HD mode) runs 119.0 frames per second at 2.1 MP resolution.

Alvium 1500 C is a revolutionary MIPI CSI-2 camera optimized for embedded vision applications. The Alvium 1500 C offers the performance and versatility of industrial cameras for the embedded world. Equipped with industrial-grade CMOS sensors from ON Semiconductor, Alvium 1500 C cameras deliver excellent image quality and high frame rates.

The standardized CSI-2 driver ensures quick integration with the flexibility to change camera models easily.

To operate Alvium CSI-2 cameras on your vision system, Allied Vision provides different access modes: - **Direct Register Access (DRA)** to control the cameras via registers for advanced users. - Video4Linux2 Access allows to control the cameras via established V4L2 API and applications like GStreamer and OpenCV. Open-source CSI-2 drivers are available on [GitHub](#) for different boards and system on chips (SoCs).

In addition to lens mount and housing options, see [Customization and OEM Solutions webpage](#) for additional options.

Specifications

Product code	14627
Interface	MIPI CSI-2, up to 4 lanes
Resolution	1928 (H) × 1088 (V)
Spectral range	300 to 1100 nm
Sensor	ON Semi AR0521SR (HD mode)
Sensor type	CMOS
Shutter mode	RS (Rolling shutter)
Sensor size	Type 1/3.6
Pixel size	2.2 μm × 2.2 μm
Lens mounts (available)	C-Mount, CS-Mount, S-Mount
Max. frame rate at full resolution	119 fps using 2 to 4 lanes, RAW8 (GREY)
ADC	10 Bit
Image buffer (RAM)	256 KByte
Non-volatile memory (Flash)	1024 KByte

Imaging performance

Imaging performance data is based on the evaluation methods in the EMVA 1288 Release 3.1 standard for characterization of image sensors and cameras. Measurements are typical values for monochrome models measured without optical filter.

Quantum efficiency at 529 nm	79 %
Temporal dark noise	5.9 e ⁻
Saturation capacity	9890 e ⁻
Dynamic range	63 dB
Absolute sensitivity threshold	7.1 e ⁻

Output

Bit depth	10-bit
Raw pixel formats	CSI-2: RAW8, RAW10, RAW12 FOURCC: GREY, Y10, Y12

General purpose inputs/outputs (GPIOs)

TTL I/Os	2 programmable GPIOs
----------	----------------------

Operating conditions/dimensions

Operating temperature -20 °C to +85 °C (cooling areas)


Power requirements (DC) 5 VDC over MIPI CSI-2

Power consumption Typical: 1.9 W

Mass 10 g

Body dimensions (L × W × H in mm) 7 × 26 × 26

Quantum efficiency



Features

Image control: Auto

- Auto exposure
- Auto gain
- Auto white balance (color models)

Image control: Other

- Black level
- Color transformation (incl. hue, saturation; color models)
- De-Bayering up to 5×5 (color models)
- DPC (defect pixel correction)
- FPNC (fixed pattern noise correction)
- Gamma
- Reverse X/Y
- ROI (region of interest)

Camera control

- Acquisition frame rate
- Firmware update in the field
- I/O and trigger control
- Temperature monitoring

Technical drawing

