



ThinkeyTM Silicon Schottky Diode Qualified per MIL-PRF-19500/726

DESCRIPTION

This Defense Logistics Agency (DLA) qualified Schottky diodes offer great value for aerospace and defense applications requiring high density power and excellent heat dissipation (typically 0.25 – 0.35 degrees C per Watt (C/W)). The 1N6940UTK3AS through 1N6942UTK3AS device polarity is anode-to-strap (standard) and is also available optionally in 1N6940UTK3CS through 1N6942UTK3CS as cathode-to-strap. This part can also be ordered in a strapless version. Up-screening for high-reliability applications is also available. Microsemi also offers numerous other products to meet higher and lower power voltage regulation applications.

Important: For the latest information, visit our website http://www.microsemi.com.

FEATURES

- JEDEC registered 1N6940 1N6942 number series.
- Oxide passivated structure.
- Guard ring protection for increased reverse energy capability.
- Epitaxial structure minimizes forward voltage drop.
- Hermetically sealed, low profile ceramic surface mount power package.
- JAN, JANTX, and JANTXV qualifications are available per MIL-PRF-19500/726. (See <u>part nomenclature</u> for all available options).
- RoHS compliant versions available (commercial grade only).

APPLICATIONS / BENEFITS

- Low package inductance.
- Very low thermal resistance.
- Also available with no strap as 1N6940UTK3, 1N6941UTK3 and 1N6942UTK3 by special request.
- Rugged ceramic and metal construction with no wire bonds.
- High surge capabilities and enable double-side cooling.

MAXIMUM RATINGS @ $T_c = +25$ °C, unless otherwise noted

Parameters / Test (Symbol	Value	Unit	
Junction and Storage Temperature Range		T_{j} and T_{stg}	-65 to +150	°C
Thermal Resistance Junction to Case (Anode-to-Strap)		R _{ejc}	0.25	°C/W
Thermal Resistance Junction to Case (Cathode-to-Strap) (Also applicable to strapless option)		R _{eJC}	0.35	°C/W
Working Peak Reverse Voltage:	1N6940UTK3,CS,AS		15	
	1N6941UTK3,CS,AS	V _{RWM}	30	V
	1N6942UTK3,CS,AS		45	
Average Rectified Output Current, T _C = +100 °C		lo	150	Α
Non-repetitive Peak Surge Current (tp = 8.3 ms, half sine-wave)		I _{FSM}	2000	A (pk)

<u>Qualified Levels</u>: JAN, JANTX, and JANTXV



ThinKey™ 3 Package

MSC – Lawrence

6 Lake Street, Lawrence, MA 01841 Tel: 1-800-446-1158 or (978) 620-2600 Fax: (978) 689-0803

MSC – Ireland

Gort Road Business Park, Ennis, Co. Clare, Ireland Tel: +353 (0) 65 6840044 Fax: +353 (0) 65 6822298

Website:

www.microsemi.com



MECHANICAL and PACKAGING

- CASE: Ceramic-molybdenum Thinkey 3.
- TERMINALS: Tin/lead solder or RoHS compliant matte/tin (on commercial grade only) plating.
- MARKING: Part number and polarity symbol.
- POLARITY: Standard is anode to strap. Reverse is cathode to strap.
- WEIGHT: Approximately 1.7 grams.
- See package dimensions on page 4.

PART NOMENCLATURE



SYMBOLS & DEFINITIONS				
Symbol	Definition			
f	frequency			
IF	Forward current, dc			
I _R	Reverse current, dc			
Tc	Case temperature			
tp	Pulse time			
VR	Reverse Voltage, dc			



Parameters / Test Conditions		Symbol	MIN	MAX	Unit
Reverse (Leakage) Current					
V _R = 15 V, Tc = 25 °C	1N6940UTK3, CS, AS				
V _R = 30 V, Tc = 25 °C	1N6941UTK3, CS, AS	I _{R1}		5.0	mA
V _R = 45 V, Tc = 25 °C	1N6942UTK3, CS, AS				
V _R = 15 V, Tc = +125 °C	1N6940UTK3, CS, AS			1,200	
V _R = 30 V, Tc = +125 °C	1N6941UTK3, CS, AS	I _{R2}		1,200	mA
V _R = 30 V, Tc = +125 °C	1N6942UTK3, CS, AS			500	
V _R = 45 V, Tc = +125 °C	1N6942UTK3, CS, AS	I _{R3}		1,500	mA
Forward Voltage					
Pulse test, pulse width tp = 300 μ s					
I _F = 75 A (pk), T _C = +25 °C	1N6940UTK3, CS, AS			0.43	
I _F = 25 A (pk), T _C = +25 °C	1N6941UTK3, CS, AS	V _{F1}		0.42	V
I _F = 25 A (pk), T _C = +25 °C	1N6942UTK3, CS, AS			0.40	
I _F = 150 A (pk), T _C = +25 °C	1N6940UTK3, CS, AS			0.50	
I _F = 50 A (pk), T _C = +25 °C	1N6941UTK3, CS, AS	V _{F2}		0.50	V
I _F = 50 A (pk), T _C = +25 °C	1N6942UTK3, CS, AS			0.46	
I _F = 150 A (pk), T _C = +125 °C	1N6940UTK3, CS, AS			0.43	
I _F = 150 A (pk), T _C = +125 °C	1N6941UTK3, CS, AS	V _{F3}		0.50	V
I _F = 110 A (pk), T _C = +125 °C	1N6942UTK3, CS, AS			0.50	
I _F = 150 A (pk), T _C = +125 °C	1N6942UTK3, CS, AS	V_{F4}		0.57	V
Junction Capacitance	1N6940UTK3, CS, AS			10,000	
V _R = 5 V, f = 1 MHz, V _{SIG} = 50 mV (p-p)	1N6941UTK3, CS, AS	CJ		7,500	pF
	1N6942UTK3, CS, AS			7,000	
Breakdown Voltage					
Pulse test, tp = 35 ms					
	1N6940UTK3, CS, AS		16.5		
I _R = 50 mA (pk), T _C = 25 °C	1N6941UTK3, CS, AS	V _{(BR)1}	33		V
· · · ·	1N6942UTK3, CS, AS	. ,	50		
	1N6940UTK3, CS, AS		15		
I _R = 50 mA (pk), T _C = -55 °C	1N6941UTK3, CS, AS	V _{(BR)2}	30		V
	1N6942UTK3, CS, AS	•	45		

ELECTRICAL CHARACTERISTICS @ $T_A = +25$ °C, unless otherwise noted



1N6940UTK3 - 1N6942UTK3, AS and CS

WITHOUT STRAP

PACKAGE DIMENSIONS





	Dimensions				
Ltr	Inch		Millimeters		
	Min	Max	Min	Max	
BL	0.420	0.440	10.67	11.18	
BT	-	0.115	- 2.92		
BLT	-	0.125	-	3.18	
С	0.469	0.509	11.91	12.93	
E	0.038 NOM		0.97 NOM		
F	0.331	0.341	8.41	8.66	
LC	0.040 NOM 1.02		NOM		
LF	0.055	0.075	1.40	1.91	
LT	0.005	0.015	0.127	0.381	
LW	0.185	0.215	4.70	5.46	

NOTES:

- 1. Dimensions are in inches.
- 2. Millimeters are given for general information only.
- 3. In accordance with ASME Y14.5M, diameters are equivalent to Φx symbology.

SEE PAD LAYOUT ON NEXT PAGE.

LDS-0298, Rev. 1 (130371)



PAD LAYOUT

