

DATA SHEET ELECTROSTATIC DISCHARGE PROTECTION DEVICES INDUSTRIAL / CONSUMER UDT23AXXL02 SERIES RoHS compliant & Halogen free



Electrostatic Discharged Protection Devices (ESD) Data Sheet

Description

Brightking's UDT23AXXL02 series are ultra low capacitance TVS arrays designed to protect high speed data interfaces. This series has been specifically designed to protect sensitive components which are connected to high-speed data and transmission lines from overvoltage caused by electrostatic discharge (ESD), cable discharge events(CDE) and electrical fast transients(EFT).The series has a typical capacitance of only 0.8pF. This means it can be used on circuits operating in excess of 3GHz without signal attenuation.

Features

- IEC61000-4-2 ESD 30KV Air, 30KV contact compliance
- SOT-23 surface mount package
- Protects two high speed data line
- Peak power dissipation of 400W under 8/20µs waveform
- Working voltage: 3.3V, 5V, 12V, 15V
- Low leakage current
- Ultra low capacitance and clamping voltage
- Solid-state silicon avalanche technology
- Lead Free/RoHS compliant
- Solder reflow temperature: Pure Tin-Sn, 260~270°C
- Flammability rating UL 94V-0
- Meets MSL level 1, per J-STD-020

Applications

- HDMI interface protection
- Mobile display digital interface
- RF/Antenna circuits
- USB 2.0 & Firewire ports


Maximum Ratings

- GaAs photodetector protection
- HBT power Amp protection
- Infiniband transceiver protection

Rating	Symbol	Value	Unit
Peak pulse power (tp=8/20µs waveform)	P _{PP}	400	W
ESD voltage (Contact discharge)	M	±30	
ESD voltage (Air discharge)	V _{ESD}	±30	kV
Storage & operating temperature range	T _{STG} ,TJ	-55~+150	°C







2 8

8

Electrical Characteristics (TJ=25℃)

UDT23A03L02 (Marking: B LSC)

Parameter	Symbol	Condition	Min.	Тур.	Max.	Unit
Reverse stand-off voltage	V _{RWM}				3.3	V
Reverse breakdown voltage	V _{BR}	I _{BR} =1mA	4			V
Reverse leakage current	I _R	V _R =3.3V each I/O pin			20	μA
Clamping voltage (tp=8/20µs)	Vc	I _{PP} =1A			10	V
Peak Pulse Current (tp=8/20µs)	I _{PP}				19	А
Off state junction capacitance	CJ	0Vdc,f=1MHz Between I/O pins and GND		1.5		pF

UDT23A05L02 (Marking: B LTC)

Parameter	Symbol	Condition	Min.	Тур.	Max.	Unit
Reverse stand-off voltage	V _{RWM}				5	V
Reverse breakdown voltage	V_{BR}	I _{BR} =1mA	6			V
Reverse leakage current	I _R	V _R =5V each I/O pin			5	μA
Clamping voltage (tp=8/20µs)	Vc	I _{PP} =1A			12	V
Peak Pulse Current (tp=8/20µs)	I _{PP}				17	А
Off state junction capacitance	CJ	0Vdc,f=1MHz Between I/O pins and GND		0.8		pF

UDT23A12L02 (Marking: B LUC)

Parameter	Symbol	Condition	Min.	Тур.	Max.	Unit
Reverse stand-off voltage	V _{RWM}				12	V
Reverse breakdown voltage	V _{BR}	I _{BR} =1mA	13.3			V
Reverse leakage current	I _R	V _R =12V each I/O pin			1	μA
Clamping voltage (tp=8/20µs)	Vc	I _{PP} =1A			25	V
Peak Pulse Current (tp=8/20µs)	I _{PP}				10	А
Off state junction capacitance	CJ	0Vdc,f=1MHz Between I/O pins and GND		0.8		pF


YAGEO Circuit Protection


Electrostatic Discharge Protection Devices UDT23AXXL02 SERIES

<u>4</u> 8

Parameter	Symbol	Condition	Min.	Тур.	Max.	Unit
Reverse stand-off voltage	V _{RWM}				15	V
Reverse breakdown voltage	V_{BR}	I _{BR} =1mA	16.7			V
Reverse leakage current	I _R	V _R =15V each I/O pin			1	μA
Clamping voltage (tp=8/20µs)	Vc	I _{PP} =1A			30	V
Peak Pulse Current (tp=8/20µs)	I _{PP}				8	А
Off state junction capacitance	CJ	0Vdc,f=1MHz Between I/O pins and GND		0.8		pF

Typical Characteristics Curves





Jul. 04, 2023 V.4

Figure 3. Non-Repetitive Peak Pulse vs. Pulse Time

Figure 2. Pulse Waveforms






Figure 4. Typical Junction Capacitance



-www.yageo.com


<u>5</u> 8

Applications Information



<u>6</u> 8

Recommended Soldering Conditions






8


YAGEO | Circuit Protection

Electrostatic Discharge Protection Devices UDT23AXXL02 SERIES

Dimensions (SOT-23)



Packaging



LEGAL DISCLAIMER

YAGEO, its distributors and agents (collectively, "YAGEO"), hereby disclaims any and all liabilities for any errors, inaccuracies or incompleteness contained in any product related information, including but not limited to product specifications, datasheets, pictures and/or graphics. YAGEO may make changes, modifications and/or improvements to product related information at any time and without notice.

YAGEO makes no representation, warranty, and/or guarantee about the fitness of its products for any particular purpose or the continuing production of any of its products. To the maximum extent permitted by law, YAGEO disclaims (i) any and all liability arising out of the application or use of any YAGEO product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for a particular purpose, non -infringement and merchantability.

YAGEO products are designed for general purpose applications under normal operation and usage conditions. Please contact YAGEO for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property: Aerospace equipment (artificial satellite, rocket, etc.), Atomic energy-related equipment, Aviation equipment, Disaster prevention equipment, crime prevention equipment, Electric heating apparatus, burning equipment, Highly public information network equipment, data-processing equipment, Medical devices, Military equipment, Power generation control equipment, Safety equipment, Traffic signal equipment, Transportation equipment and Undersea equipment, or for any other application or use in which the failure of YAGEO products could result in personal injury or death, or serious property damage. Particularly **YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.**

Information provided here is intended to indicate product specifications only. YAGEO reserves all the rights for revising this content without further notification, as long as products are unchanged. Any product change will be announced by PCN.