300 WATT MULTI-LINE TVS ARRAY



DESCRIPTION

The DFN6-36 is a multi-line transient voltage suppressor array. This device is designed to protect sensor ports, portable electronics and 36V DC applications from the damaging effects of ESD and EFT.

The DFN6-36 is available in a unidirectional configuration with a working voltage of 33V and a minimum breakdown voltage of 35V. This device is rated for 300 Watt peak pulse power using the $8/20\mu s$ waveform, which is sufficient protection for tertiary type lightning threats at key interface locations.

The DFN6-36 is also suited to protect data lines against ESD and EFT. This device meets the IEC 61000-4-2 and IEC 61000-4 requirements. At higher operating frequencies or faster edge rates, insertion loss and signal integrity are a major concern. This device in conjunction with passive components integrated into a TVS/filter network can be used for EMI/RFI protection.

FEATURES

- Compatible with IEC 61000-4-2 (ESD): Air ± 15kV, Contact ± 8kV
- Compatible with IEC 61000-4-4 (EFT): 40A 5/50ns
- Compatible with IEC 61000-4-5 (Surge): 6A, 8/20μs Level 1(Line-Gnd) & Level 2(Line-Line)
- 300 Watts Peak Pulse Power per Line (tp = 8/20µs)
- ESD Protection > 25 kilovolts
- Low Clamping Voltage
- Protects up to 3 Data Lines
- RoHS Compliant
- REACH Compliant


APPLICATIONS

- Digital Sensor I/O Ports
- · Control & Monitoring Systems
- Portable Electronics
- 36 Volt DC Protection

MECHANICAL CHARACTERISTICS

- Molded JEDEC DFN-6 Package
- Approximate Weight: 6 milligrams
- Lead-Free Pure-Tin Plating (Annealed)
- Solder Reflow Temperature:
 - Pure-Tin Sn, 100: 260-270°C
- 8mm Tape and Reel Per EIA Standard 481
- Flammability Rating UL 94V-0

PIN CONFIGURATION




05319.R7 6/21 Page 1 ISO 9001: 2015 CERTIFIED


TYPICAL DEVICE CHARACTERISTICS


MAXIMUM RATINGS @ 25°C Unless Otherwise Specified						
PARAMETER	SYMBOL	VALUE	UNITS			
Peak Pulse Power (tp = 8/20μs) - See Figure 1	P _{pp}	300	Watts			
Steady State Power	P _{ss}	0.4	Watts			
Max Forward Voltage @ 100mA	V _F	1.4	V			
Max Forward Voltage @ 50mA	V _F	1.3	V			
Operating Temperature	T _A	-55 to 150	°C			
Storage Temperature	T _{stg}	-55 to 150	°C			
Peak Pulse Current(tp = 8/20μs)	I _{PP(MAX)}	6.0	Amps			

ELECTRICAL CHARACTERISTICS PER LINE @ 25°C Unless Otherwise Specified								
PART NUMBER	DEVICE MARKING	RATED STAND-OFF VOLTAGE	MINIMUM BREAKDOWN VOLTAGE @ 1mA	MAXIMUM CLAMPING VOLTAGE (Fig. 2) @Ip = 2A	MAXIMUM LEAKAGE CURRENT @ V _{wm}	TYPICAL CAPACITANCE @0V, 1MHz		
		V _{wM} VOLTS	V _(BR) VOLTS	V _c VOLTS	Ι _D μΑ	C _, pF		
DFN6-36	D36	33.0	35.0	45.0	0.5	50		



TYPICAL DEVICE CHARACTERISTICS







DFN-6 PACKAGE INFORMATION

OUTLINE DIMENSIONS								
DIM	MILLIN	IETERS	INCHES					
	MIN	MAX	MIN	MAX				
А	0.45	0.55	0.017	0.021				
А3	0.13	BSC	0.00	5 BSC				
b	0.35	0.45	0.013	0.017				
D	1.90	2.10	0.074	0.082				
Е	1.40	1.60	0.055	0.063				
е	0.65	BSC	0.025	5 BSC				
L	0.45	0.55	0.017	0.021				
L1	0.55	0.65	0.021	0.025				
L2	0.65	0.75	0.025 0.029					


NOTES

- 1. Controlling dimension: millimeters.
- 2. Dimensioning and tolerances per ANSI Y14.M, 1985.






SIDE VIEW




PAD LAYOUT DIMENSIONS						
DIM	MILLIMETERS	INCHES				
	NOMINAL	NOMINAL				
А	1.78	0.070				
В	1.93	0.076				
С	0.64	0.025				
D	0.86	0.034				
Е	0.51	0.020				
F	0.76	0.030				
G	0.94	0.037				
Н	0.30	0.012				
NOTE						

NOTES

1. Controlling dimension: millimeters.



TAPE AND REEL



SPECIFICATIONS												
REEL DIA.	TAPE WIDTH	A0	В0	ко	D	E	F	W	P0	P2	P	tmax
178mm (7")	8mm	1.70 ± 0.10	2.20 ± 0.10	0.70 ± 0.10	1.50 ± 0.10	1.75 ± 0.10	3.50 ± 0.05	8.00 ± 0.30	4.00 ± 0.10	2.00 ± 0.05	4.00 ± 0.10	0.25

NOTES

- 1. Dimensions are in millimeters.
- 2. Surface mount product is taped and reeled in accordance with EIA-481.
- 3. Suffix T73 = 7" Reel 3,000 pieces per 8mm tape.
- 4. Marking on Part marking code (see page 2) and polarity dot.

ORDERING INFORMATION							
BASE PART NUMBER LEADFREE SUFFIX TAPE SUFFIX QTY/REEL REEL SIZE TUBE QT							
DFN6-36	DFN6-36 n/a -T73 3,000				n/a		
This device is only available in a Lead-Free configuration.							

05319.R7 6/21 Page 5 ISO 9001: 2015 CERTIFIED



COMPANY INFORMATION

COMPANY PROFILE

In business more than 25 years, ProTek Devices™ is a privately held semiconductor company. The company offers a product line of overvoltage protection and overcurrent protection components. These include transient voltage suppressor array (TVS arrays) avalanche breakdown diode, steering diode TVS array and electronics SMD chip fuses. These components deliver circuit protection in electronic systems from numerous overvoltage and overcurrent events. They include lightning; electrostatic discharge (ESD); nuclear electromagnetic pulses (NEMP); inductive switching; and electromagnetic interference (EMI) / radio frequency interference (RFI). ProTek Devices also offers LED wafer die for ESD protection and related high frequency products. ProTek Devices is ISO 9001:2015 certified.

CONTACT US

Corporate Headquarters

2929 South Fair Lane Tempe, Arizona 85282 USA

By Telephone

General: 602-431-8101

Sales: & Marketing: 602-414-5109 Customer Service: 602-414-5114

Product Technical Support: 602-414-5107

By Fax

General: 602-431-2288

By E-mail:

Asia Sales: asiasales@protekdevices.com
Europe Sales: europesales@protekdevices.com
U.S. Sales: ussales@protekdevices.com
Distributor Sales: distysales@protekdevices.com

Customer Service: service@protekdevices.com
Technical Support: support@protekdevices.com

ProTek Devices (Asia Pacific) Pte. Ltd.

8 Ubi Road 2, #06-19

Zervex

Singapore - 408538 Tel: +65-67488312 Fax: +65-67488313

Web

www.protekdevices.com

COPYRIGHT © ProTek Devices 2012 - This literature is subject to all applicable copyright laws and is not for resale in any manner.

SPECIFICATIONS: ProTek reserves the right to change the electrical and or mechanical characteristics described herein without notice

DESIGN CHANGES: ProTek reserves the right to discontinue product lines without notice and that the final judgement concerning selection and specifications is the buyer's and that in furnishing engineering and technical assistance. ProTek assumes no responsibility with respect to the selection or specifications of such products. ProTek makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ProTek assume any liability arising out of the application or use of any product or circuit and specifically disclaims any and all liability without limitation special, consequential or incidental damages.

LIFE SUPPORT POLICY: ProTek Devices products are not authorized for use in life support systems without written consent from the factory.