




Ultra Current Beads

UCB15



Dimensions: $\frac{\text{Inches}}{\text{(mm)}}$



Allied Part Number	Impedance (Ω)	Tolerance (%)	Test Freq MHz, 200mV	DCR Max. (Ω)	Rated Current (mA)Max
UCB15-150T-RC	15	25	100	.012	6000
UCB15-220T-RC	22	25	100	.012	6000
UCB15-300T-RC	30	25	100	.012	6000
UCB15-500T-RC	50	25	100	.015	6000
UCB15-600T-RC	60	25	100	.018	6000
UCB15-800T-RC	80	25	100	0.02	6000
UCB15-101T-RC	100	25	100	0.02	5000
UCB15-121T-RC	120	25	100	0.02	5000
UCB15-201T-RC	200	25	100	0.04	3000
UCB15-221T-RC	220	25	100	0.04	3000
UCB15-301T-RC	300	25	100	0.05	3000
UCB15-331T-RC	330	25	100	0.05	3000

All specifications subject to change without notice.

Features

- Ultra High Current
- Standard 0805 size
- Triple plated RoHS Compliant Terminations
- Excellent Solderability

Electrical

Impedance range: 15Ω to 330Ω

Tolerance: 25% over entire range available in tighter tolerances

Operating Temp: -55°C ~ +125°C

Rated Current: The current at which the temperature rise shall be no more than 30°C. Also, the rated current is de-rated above 85°C to approximately 1000mA at 125°C

Resistance to Solder Heat

Pre-Heat 150°C, 1 minute

Solder Composition: Sn/Ag3.0/Cu0.5(Pb-Free)

Solder Temp: 260°C peak for 10 sec. ± 1 sec.

Test Equipment

(Z): HP4291A RF Impedance/Material Analyzer

(RDC): Chen Hwa 502BC/HP4338B

Physical

Packaging: 4000pcs per reel

Marking: None