


3

FILE NAME: C12346, __A__DTJ_



| Γ | PART | PART NO. OF INCHES | | | | | MILLIMETERS | | | | | | | |
|---|---------|--------------------|--------|--------|-------|--------|-------------|--------|--------|--------|--------|--------|--------|--------|
| | NUMBER | POS. | A±.008 | B±.008 | | D±.010 | E±.020 | F±.015 | A±0.20 | B±0.20 | C±0.38 | D±0.25 | E±0.51 | F±0.38 |
| | A06DTJ_ | 6 | 0.625 | 0.875 | 1.035 | 1.295 | 1.555 | 0.875 | 15.88 | 22.23 | 26.29 | 32.89 | 39.50 | 22.23 |
| | A10DTJ_ | 10 | 1.125 | 1.375 | 1.535 | 1.795 | 2.055 | 1.375 | 28.58 | 34.93 | 38.99 | 45.59 | 52.20 | 34.93 |
| F | A14DTJ_ | 14 | 1.625 | 1.875 | 2.035 | 2.295 | 2.555 | 1.875 | 41.28 | 47.63 | 51.69 | 58.29 | 64.90 | 47.63 |
| | A15DTJ_ | 15 | 1.750 | 2.000 | 2.160 | 2.420 | 2.680 | 2.000 | 44.45 | 50.80 | 54.86 | 61.47 | 68.07 | 50.80 |
| | A18DTJ_ | 18 | 2.125 | 2.375 | 2.535 | 2.795 | 3.055 | 2.375 | 53.98 | 60.33 | 64.39 | 70.99 | 77.60 | 60.33 |
| | A22DTJ_ | 22 | 2.625 | 2.875 | 3.035 | 3.295 | 3.555 | 2.875 | 66.68 | 73.03 | 77.09 | 83.69 | 90.30 | 73.03 |
| | A24DTJ_ | 24 | 2.875 | 3.125 | 3.285 | 3.545 | 3.805 | 3.125 | 73.03 | 79.38 | 83.44 | 90.04 | 96.65 | 79.38 |
| | A25DTJ_ | 25 | 3.000 | 3.250 | 3.410 | 3.670 | 3.930 | 3.250 | 76.20 | 82.55 | 86.61 | 93.22 | 99.82 | 82.55 |
| | A28DTJ_ | 28 | 3.375 | 3.625 | 3.785 | 4.045 | 4.305 | 3.625 | 85.73 | 92.08 | 96.14 | 102.74 | 109.35 | 92.08 |
| | A30DTJ_ | 30 | 3.625 | 3.875 | 4.035 | 4.295 | 4.555 | 3.875 | 92.08 | 98.43 | 102.49 | 109.09 | 115.70 | 98.43 |
| Е | A31DTJ_ | 31 | 3.750 | 4.000 | 4.160 | 4.420 | 4.680 | 4.000 | 95.25 | 101.60 | 105.66 | 112.27 | 118.87 | 101.60 |
| | A32DTJ_ | 32 | 3.875 | 4.125 | 4.285 | 4.545 | 4.805 | 4.125 | 98.43 | 104.78 | 108.84 | 115.44 | 122.05 | 104.78 |
| | A35DTJ_ | 35 | 4.250 | 4.500 | 4.660 | 4.920 | 5.180 | 4.500 | 107.95 | 114.30 | 118.36 | 124.97 | 131.57 | 114.30 |
| | A36DTJ_ | 36 | 4.375 | 4.625 | 4.785 | 5.045 | 5.305 | 4.625 | 111.13 | 117.48 | 121.54 | 128.14 | 134.75 | 117.48 |
| | A40DTJ_ | 40 | 4.875 | 5.125 | 5.285 | 5.545 | 5.805 | 5.125 | 123.83 | 130.18 | 134.24 | 140.84 | 147.45 | 130.18 |
| | A43DTJ_ | 43 | 5.250 | 5.500 | 5.660 | 5.920 | 6.180 | 5.500 | 133.35 | 139.70 | 143.76 | 150.37 | 156.97 | 139.70 |
| | A44DTJ_ | 44 | 5.375 | 5.625 | 5.785 | 6.045 | 6.305 | 5.625 | 136.53 | 142.88 | 146.94 | 153.54 | 160.15 | 142.88 |
| | A49DTJ_ | 49 | 6.000 | 6.250 | 6.410 | 6.670 | 6.930 | 6.250 | 152.40 | 158.75 | 162.81 | 169.42 | 176.02 | 158.75 |
| D | A50DTJ_ | 50 | 6.125 | 6.375 | 6.535 | 6.795 | 7.055 | 6.375 | 155.58 | 161.93 | 165.99 | 172.59 | 179.20 | 161.93 |

PART NUMBER CODING

. A _ _ DTJ _

MATERIAL (INSULATOR/CONTACT)

E = PBT/PHOSPHOR BRONZE

OPERATING TEMP: -65°C TO +125°C PROCESSING TEMP: WAVE/MANUAL SOLDERING

R = PPS/PHOSPHOR BRONZE

OPERATING TEMP: -65°C TO +125°C

PROCESSING TEMP: 260°C FOR 120 SECS MAX

G = PA9T/PHOSPHOR BRONZE

OPERATING TEMP: -65°C TO +125°C PROCESSING TEMP: 260°C FOR 20 SECS MAX

H = PBT/BERYLLIUM COPPER

OPERATING TEMP: -65°C TO +125°C

PROCESSING TEMP: WAVE/MANUAL SOLDERING

A = PPS/BERYLLIUM COPPER

OPERATING TEMP: -65°C TO +150°C

PROCESSING TEMP: 260°C FOR 120 SECS MAX

J = PA 9T/BERYLLIUM COPPER

OPERATING TEMP: -65°C TO +150°C

PROCESSING TEMP: 260°C FOR 20 SECS MAX (CONSULT FACTORY FOR OTHER MATERIALS)

MOUNTING STYLE

H = .125" DIA. CLEARANCE HOLES (PAGE 1)

I = #4-40 THREADED INSERT (PAGE 2)

S = .125" DIA. SIDE MOUNTING (PAGE 2)

D = .250" EARS, FLUSH MTG., .125" DIA CLEARANCE HOLES (PAGE 2)

W = .430" EARS, FLUSH MTG., .125" DIA CLEARANCE HOLES (PAGE 2)

T = .250" EARS, FLUSH MTG., #4-40 THREADED INSERT (PAGE 2)

X = .430" EARS, FLUSH MTG., #4-40 THREADED INSERT (PAGE 2)

Z = FLUSH MTG., .125" DIA SIDE HOLES (PAGE 2)

N = NO MOUNTING EARS (PAGE 2)

NUMBER OF POSITIONS

(CONTACTS PER ROW)

PLATING

ALL PLATINGS ARE LEAD FREE AND HAVE .000050" NICKEL UNDERPLATE

CONTACT SURFACE **TERMINATION**

G = .000010" GOLD.000005" GOLD

Y = .000030" GOLD .000005" GOLD

B = .000010" GOLD .000100" PURE TIN, MATTE .000100" PURE TIN, MATTE

C = .000030" GOLD *E = .000100" PURE TIN, MATTE, OVERALL

S = .000010" GOLD OVERALL

.000010" GOLD OVERALL M = .000030" GOLD

* OVERALL TIN ONLY AVAILABLE ON MATERIAL CODES E, R AND G

CUSTOMER COPY



| | | C | | | |
|----|---|--|---------|--|--|
| | UNLESS UTHERWISE SPECIFIED. | DRAWN | DATE | | |
| | DIMENSIONS ARE IN INCHES [MM] | | 1/29/20 | | |
| 1 | TOLERANCES: | THE INFORMATION HERE PROPIETARY INFORM SULLINS ELECTRONICS TO BE REPRODUCED DISCLOSED TO OTHER | | | |
| | ANGULAR: ± 1° | | | | |
| | DECIMALS .XX=± .02 [.5] | PURPOSE EXCEPT AS AUTHORIZED IN WR OFFICER OF SULLINS E | | | |
| JT | .XXX=± .005 [.13] .XXXX=± .0005 [.013] | | , | | |

| | |) | | | | | | | |
|----|---|-----------|------|--|---|----------|---------------------------|----|--|
| D: | DRAWN | DATE | NAME | | | — | | | |
| M] | | 1/29/2014 | JHSU | | | SULLI | | | |
| | THE INFORMATION HEREIN CONTAINS PROPIETARY INFORMATION OF SULLINS ELECTRONICS AND IS NOT TO BE REPRODUCED, USED OR DISCLOSED TO OTHERS FOR ANY PURPOSE EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY AN OFFICER OF SULLINS ELECTRONICS. | | | EDGECARD, .125 CC HP | | | | | |
| | | | | PART NUMBER | - | | TJ_ | | |
| | |) — | | SIZE CAGE (C 544 SCALE: 2:1 | | OWG. NO. | 12346 SHEET 3 OF 3 | RE | |
| | | | | | | | 1 | | |

FILE NAME: C12346, _ _A_ _DTJ_