

1A, 20V - 150V Schottky Barrier Surface Mount Rectifier

FEATURES

- Ideal for automated placement
- Compact package size, profile <0.85mm
- High surge current capability
- Low power loss, high efficiency
- Moisture sensitivity level: level 1, per J-STD-020
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

APPLICATIONS

- Switching mode power supply (SMPS)
- Adapters
- DC to DC converter

MECHANICAL DATA

- Case: SOD-123HE
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- Polarity: Indicated by cathode band
- Weight: 0.021g (approximately)

KEY PARAMETERS				
PARAMETER	VALUE	UNIT		
I _F	1	А		
V _{RRM}	20 - 150	V		
I _{FSM}	30	А		
T _{J MAX}	125, 150 °C			
Package	SOD-123HE			
Configuration	Single die			





SOD-123HE



ABSOLUTE MAXIMUM RATINGS ($T_A = 25^{\circ}C$ unless otherwise noted)								
PARAMETER	SYMBOL	SS12 LS	SS13 LS	SS14 LS	SS16 LS	SS110 LS	SS115 LS	UNIT
Marking code on the device		12LS	13LS	14LS	16LS	10LS	A5LS	
Repetitive peak reverse voltage	V _{RRM}	20	30	40	60	100	150	V
Reverse voltage, total rms value	V _{R(RMS)}	14	21	28	42	70	105	V
Forward current	I _F				1			А
Peak forward surge current, 8.3ms single half sine-wave superimposed on rated load	I _{FSM}	30				A		
Junction temperature	T_{J}	- 55 to +125 - 55 to +150			°C			
Storage temperature	T _{STG}	- 55 to +150			°C			



THERMAL PERFORMANCE					
PARAMETER	SYMBOL	ТҮР	UNIT		
Junction-to-case thermal resistance	R _{eJC}	25	°C/W		
Junction-to-ambient thermal resistance	R _{eja}	70	°C/W		

ELECTRICAL SPECIFIC						
PARAMETER		CONDITIONS	SYMBOL	ΤΥΡ	MAX	UNIT
	SS12LS		-	-	-	V
	SS13LS	- I _F = 0.5A, T _J = 25°C		-	-	V
	SS14LS			-	0.51	V
	SS16LS			-	0.58	V
	SS110LS			-	0.70	V
– (1)	SS115LS	-	VF	-	0.75	V
Forward voltage ⁽¹⁾	SS12LS			-	0.45	V
	SS13LS			_	0.50	V
	SS14LS	I _F = 1.0A, T _J = 25°C		_	0.55	V
	SS16LS			_	0.70	V
	SS110LS			_	0.80	V
	SS115LS			_	0.90	V
	SS12LS SS13LS SS14LS SS16LS	T _J = 25°C		-	400	μΑ
Reverse current @ rated $V_R^{(2)}$	SS110LS SS115LS		. I _R	-	50	μA
	SS12LS SS13LS SS14LS SS16LS	T _J = 125°C		-	-	mA
	SS110LS SS115LS			-	0.5	mA
Junction capacitance		1MHz, V _R = 4.0V	CJ	80	-	pF

Notes:

1. Pulse test with PW = 0.3ms

2. Pulse test with PW = 30ms

ORDERING INFORMATION				
	PACKAGE	PACKING		
SS1xLS	SOD-123HE	10,000 / Tape & Reel		

Notes:

1. "x" defines voltage from 20V(SS12LS) to 150V(SS115LS)



CHARACTERISTICS CURVES

 $(T_A = 25^{\circ}C \text{ unless otherwise noted})$




Fig.3 Typical Reverse Characteristics





Fig.1 Forward Current Derating Curve Fig.


Fig.2 Typical Junction Capacitance

Fig.4 Typical Forward Characteristics




FORWARD VOLTAGE (V)


Fig.5 Maximum Non-Repetitive Forward Surge Current




PACKAGE OUTLINE DIMENSIONS

5 TAIWAN SEMICONDUCTOR








DIM.	Unit (mm)		Unit	inch)	
	Min.	Max.	Min.	Max.	
A	0.75	0.85	0.030	0.033	
A1	0.00	0.02	0.000	0.001	
b	0.85	1.15	0.033	0.045	
b2	0.95	1.25	0.037	0.049	
с	0.10	0.20	0.004	0.008	
D	1.65	1.95	0.065	0.077	
E	3.50	3.90	0.138	0.154	
E1	2.60	3.00	0.102	0.118	
E2	1.90	2.30	0.075	0.091	
E3	1.35	1.55	0.053	0.061	
L	0.55	0.75	0.022	0.030	
L1	0.35	0.55	0.014	0.022	

SUGGESTED PAD LAYOUT



Symbol	Unit (mm)	Unit (inch)
A	1.40	0.055
В	2.40	0.094
С	0.70	0.028
D	0.90	0.035
E	1.40	0.055

MARKING DIAGRAM



YW = Date Code

F = Factory Code



Taiwan Semiconductor

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.