



Electrical specifications

Center Frequency: 670 MHz
Bandwidth: 50 MHz min
VSWR: 1.5:1
Input / Output Impedance: 50 Ohms
Passband: 645-695 MHz
Passband Insertion Loss: 3.0 dB max
Passband Ripple: 0.4 dB max
Rejection: 45 dB min at DC-470 MHz
Rejection 2: 20 dB min at 512 MHz
Rejection 3: 20 dB min at 850 MHz
Rejection 4: 30 dB min at 900 MHz
Power Handling: 5 W

Mechanical

Mounting Method: SMT
Dimensions: 18.2 x 14 x 5 mm

Environmental

Operating Temperature: -30°C to 85°C
Storage Temperature: -50°C to +90°C

This product is RoHS compliant.

Outline Drawing:

