




## DEUTSCH

TE Internal #: ZPF00000000100306

Rectangular Contact Inserts, Contact Insert, Socket, 20 Pole Configuration, Wire-to-Board, 20 Position, Sealable, 5 A, Power, Signal & High Speed Data

[View on TE.com >](#)
[Connectors > Rectangular Connectors > Rectangular Contact Inserts](#)
Rectangular Connector Insert Type: **Contact Insert**Contact Type: **Socket**Pole Configuration: **20**Connector System: **Wire-to-Board**Number of Positions: **20**

## Features

### Product Type Features

Rectangular Connector Insert Type	Contact Insert
Connector System	Wire-to-Board
Sealable	Yes
Connector & Contact Terminates To	Printed Circuit Board

### Configuration Features

Number of Positions	20
---------------------	----

### Body Features

Primary Product Material	Composite
--------------------------	-----------

### Contact Features

Contact Type	Socket
Pole Configuration	20
Contact Current Rating (Max)	5 A

### Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

### Housing Features

Centerline (Pitch)	2.54 mm[.1 in]
--------------------	----------------

### Usage Conditions



Operating Temperature Range	-55 – 175 °C[-67 – 347 °F]
-----------------------------	----------------------------

### Operation/Application

Circuit Application	Power, Signal & High Speed Data
---------------------	---------------------------------

### Packaging Features

Packaging Quantity	1
Packaging Method	Bag

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Pb (1.2% in alloy) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Customers Also Bought




TE Part #ZPF000000000107608  
DMC-MD 24 B-K-S-T



TE Part #E42160-000  
DWP-125-KIT3

TE Part #ZPF000000000003690  
732-8021-01 B

TE Part #ZPF000000000003691  
732-8021-02 B



TE Part #FTRA6171M5PW-001  
OMNI,Ph,PMT,617-7125MHz



TE Part #3-2176372-8  
RQ 0603 121K 0.1% 10PPM 5K RL

TE Part #ZPF000000000003721  
732-8052-10 M

TE Part #ZPF000000000141393  
DMC-M 85-01

TE Part #ZPF000000000203981  
DMC-MD 83 A 01

TE Part #ZPF000000000200361  
DMC-M 00-00 PN-A1188

## Documents

### Product Drawings

732-8256-22

English

### CAD Files

3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_ZPF000000000100306\\_1.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_ZPF000000000100306\\_1.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_ZPF000000000100306\\_1.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages



**DEUTSCH DMC-M Series Multicavity EN4165 Connectors**

English

**DMC-M Series Single Module EN4165**

English