Non Magnetic MELF PIN Diode

- Non-Magnetic Package Suitable for MRI Applications
- Rectangular MELF SMQ Ceramic Package
- Low Rs for Low Series Loss
- + Longer τ_L for Low Inter-Modulation Distortion
- High Average Incident Power Handling
- RoHS Compliant

Description and Applications

The MA4P7435NM-1091T is a surface mountable PIN diode in a non-magnetic, Metal Electrode Leadless Faced (MELF) package. The device incorporates M/A-COM Technology's proven HIPAX technology to produce a low inductance ceramic package with no ribbons or whisker wires. The package utilizes M/A-COM Technology's new non-magnetic plating process to provide an extremely low magnetic permeability, hermetically sealed package. Incorporated in the package is a glass passivated PIN chip that is full face bonded on both the cathode and anode to maximize surface area for lower series and thermal resistance. The MA4P7435NM-1091T has been comprehensively characterized both electrically and mechanically to ensure repeatable and predictable performance. The diode is well suited for use in low loss, low distortion, high power switching circuits and is especially designed for use in high magnetic field environments from HF through UHF frequencies. The low thermal resistance of this device also provides excellent performance at high incident RF power levels. This device has been designed to perform well in the most rigorous electrical and mechanical MRI environments.

Solderable Surfaces Cathode Full Face Chip Bond Passivated PIN Chip

Diode Cross Section

Designed for Automated Assembly

These SMQ PIN diodes are designed for high volume tape and reel assembly. The rectangular package design provides for ease of use in most automatic pick and place assembly operations. The parallel flat surfaces are suitable for key jaw or vacuum pickup techniques. All solder able surfaces are tin plated and compatible with reflow and vapor phase soldering methods.

Absolute Maximum Ratings¹ @ 25°C

Parameter	Absolute Maximum
Operating Temperature	-65°C to +125°C
Storage Temperature	-65°C to +150°C
Diode Junction Temperature	+175°C Continuous
Diode Mounting Temperature	+265°C for 10 seconds
RF C.W. Incident Power	+ 60 dBm C.W.
Forward D.C. Current	+500mA
Reverse D.C. Voltage @ -10µA	-1100V

1. Exceeding these limits may cause permanent damage.

M/A-COM Technology Solutions Inc. (MACOM) and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice. Visit www.macom.com for additional data sheets and product information.

1

Rev. V4







Electrical Specifications @ T_{AMB} = +25°C

1. Total capacitance is equivalent to the sum of the chip junction capacitance Cj plus package parasitic capacitance .

- 2. Series resistance R_S is the sum of the chip to package contact resistance plus junction resistance Rj.
- 3. Rs is measured on an HP4291A .
- 4. Measured from 50% of control voltage to 90% of output voltage

Environmental Capability

MELF devices are applicable for use in commercial and military applications and are designed to meet the environmental requirements of MIL-STD-750, MIL-STD-202 as well as other military standards. The table below lists some of the typical MIL-STD 750 tests the devices are designed to meet.

MIL-STD-750			
Test	Method	Description	
High Temperature Storage	1031	+150°C, for 340 Hours	
Temperature Shock	1051	-65°C to +125°C, 20 Cycles	
HTRB	1038	880V, +150°C, for 96 Hours	
Moisture Resistance	1021	No Initial Conditioning, 85% RH, +85°C	
Gross Leak	1071 Cond. E	Dye Penetrant Visual	
Vibration Fatigue	2046	20,000G's, 60 Hz, x, y, z axis	
Solderability	2026	Test Temperature = +245°C	

2

масом

Rev. V4

M/A-COM Technology Solutions Inc. (MACOM) and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice. Visit www.macom.com for additional data sheets and product information.



Non Magnetic MELF PIN Diode

Rev. V4



Typical Non-Magnetic Performance

Table 1 - Typical Magnetic Properties

Non Magnetic MA4P7435NM-1091T vs. Magnetic MA4P4001F-1091T

Magnetic Property	MA4P7435NM-1091T Value	MA4P4001-1091T Value
Saturation Moment (EMU) @ H = H_{MAX} Oersteads	1.0 x E-3	1.2 x E-1
Remanance Moment (EMU) @ H = 0 Oersteads	1.5 x E-6	3.4 x E-2
Coercivity (Oersteads) @ EMU = 0 Moment	3.0	51.3

3

M/A-COM Technology Solutions Inc. (MACOM) and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice. Visit www.macom.com for additional data sheets and product information.



Non Magnetic MELF PIN Diode

Mechanical Outline



Case Style 1091 Dimensions in Inches (mm)		
A Square	В	С
Min. / Max.	Min. / Max.	Min. / Max.
0.138 / 0.155	0.180 / 0.200	0.008 / 0.030
(3.50/ 3.94)	(4.57/ 5.08)	(.203 / .762)

Circuit Pad Layout



Dimension	Package Style 1091	
	inches	mm
A	0.150	3.81
В	0.050	1.27
С	0.100	2.54

Ordering Information

Part Number	Package
MA4P7435NM-1091T	Tape and Reel (500pcs/reel)

M/A-COM Technology Solutions Inc. (MACOM) and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice. Visit www.macom.com for additional data sheets and product information.

⁴

Non Magnetic MELF PIN Diode

M/A-COM Technology Solutions Inc. All rights reserved.

Information in this document is provided in connection with M/A-COM Technology Solutions Inc ("MACOM") products. These materials are provided by MACOM as a service to its customers and may be used for informational purposes only. Except as provided in MACOM's Terms and Conditions of Sale for such products or in any separate agreement related to this document, MACOM assumes no liability whatsoever. MACOM assumes no responsibility for errors or omissions in these materials. MACOM may make changes to specifications and product descriptions at any time, without notice. MACOM makes no commitment to update the information and shall have no responsibility whatsoever for conflicts or incompatibilities arising from future changes to its specifications and product descriptions. No license, express or implied, by estoppels or otherwise, to any intellectual property rights is granted by this document.

THESE MATERIALS ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, RELATING TO SALE AND/OR USE OF MACOM PRODUCTS INCLUDING LIABILITY OR WARRANTIES RELATING TO FITNESS FOR A PARTICULAR PURPOSE, CONSEQUENTIAL OR INCIDENTAL DAMAGES, MERCHANTABILITY, OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT. MACOM FURTHER DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. MACOM SHALL NOT BE LIABLE FOR ANY SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS, WHICH MAY RESULT FROM THE USE OF THESE MATERIALS.

MACOM products are not intended for use in medical, lifesaving or life sustaining applications. MACOM customers using or selling MACOM products for use in such applications do so at their own risk and agree to fully indemnify MACOM for any damages resulting from such improper use or sale.

МАСОМ

Rev. V4

⁵

M/A-COM Technology Solutions Inc. (MACOM) and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice. Visit www.macom.com for additional data sheets and product information.