

Features

- ESD Protection for 1 line with Unidirectional
- Provide ESD protection for the protected line to IEC 61000-4-2 (ESD) ±30kV (air), ±30kV (contact)
 IEC 61000-4-4 (EFT) ±80A (5/50ns)
 IEC 61000-4-5 (Lightning) 4.5A (8/20μs)
- Suitable for, 20V and below, operating voltage applications
- 0402 small DFN package saves board space
- Protect one I/O line or one power line
- Fast turn-on and low clamping voltage
- Solid-state silicon-avalanche and active circuit triggering technology
- Green part

Applications

- Power Supply Protection
- Power Management
- LCD Panel
- Portable Devices
- Hand Held Portable Applications
- Low Speed Data or Control lines protection
- Cellular Handsets and Accessories
- Notebooks, desktops, and servers
- Peripherals

Description


AZ4120-01F is a design which includes a unidirectional ESD rated clamping cell to protect one power line, or one control line, or one low speed data line in an electronic system. The AZ4120-01F has been specifically designed to protect sensitive components which are connected to power and control lines from

over-voltage damage caused by Electrostatic Discharging (ESD), Electrical Fast Transients (EFT), Lightning, and Cable Discharge Event (CDE).

AZ4120-01F is a unique design which includes proprietary clamping cell in a single package. During transient conditions, the proprietary clamping cell prevents over-voltage on the power line or control/data lines, protecting any downstream components.

AZ4120-01F may be used to meet the ESD immunity requirements of IEC 61000-4-2, Level 4 (±15kV air, ±8kV contact discharge).

Circuit Diagram / Pin Configuration



SPECIFICATIONS


ABSOLUTE MAXIMUM RATINGS				
PARAMETER	SYMBOL	RATING	UNITS	
Peak Pulse Current (tp=8/20μs)	I _{PP}	4.5	Α	
Operating Supply Voltage (pin-1 to pin-2)	V _{DC}	22	V	
ESD per IEC 61000-4-2 (Air)	V _{ESD-1}	±30	kV	
ESD per IEC 61000-4-2 (Contact)	V_{ESD-2}	±30		
Lead Soldering Temperature	T _{SOL}	260 (10 sec.)	°C	
Operating Temperature	T _{OP}	-55 to +85	°C	
Storage Temperature	T _{STO}	-55 to +150	°C	


ELECTRICAL CHARACTERISTICS						
PARAMETER	SYMBOL	CONDITIONS	MINI	TYP	MAX	UNITS
Reverse Stand-Off Voltage	V_{RWM}	Pin-1 to pin-2, T=25 °C.			20	V
Reverse Leakage Current	I _{Leak}	V_{RWM} = 20V, T=25 °C, pin-1 to pin-2.			0.5	μΑ
Reverse Breakdown Voltage	V _{BV}	I_{BV} = 1mA, T=25 °C, pin-1 to pin-2.	22.2			V
Forward Voltage	V_{F}	$I_F = 15$ mA, T=25 °C, pin-2 to pin-1.	0.6		1.2	V
ESD Clamping Voltage (Note 1)	V _{clamp}	IEC 61000-4-2 +8kV (I_{TLP} = 16A), Contact mode, T=25 °C, pin-1 to pin-2.		29		V
ESD Dynamic Turn-on Resistance	R _{dynamic}	IEC 61000-4-2 0~+8kV, T= 25 °C, Contact mode, pin-1 to pin-2.		0.25		Ω
Channel Input Capacitance	C _{IN}	$V_R = 0V$, $f = 1MHz$, $T=25$ °C, pin-1 to pin-2.		52	65	pF

Note 1: ESD Clamping Voltage was measured by Transmission Line Pulsing (TLP) System.

TLP conditions: Z_0 = 50 Ω , t_p = 100ns, t_r = 1ns.


Typical Characteristics








Mechanical Details DFN1006P2X PACKAGE DIAGRAMS








PACKAGE DIMENSIONS

Cymbol	Millimeters		Inches		
Symbol	min	max	min	max	
Α	0.95	1.05	0.037	0.041	
В	0.55	0.65	0.022	0.026	
С	0.40	0.55	0.016	0.022	
D	0.45		0.0	18	
E	0.20	0.30	0.008	0.012	
F	0.45	0.55	0.018	0.022	


LAND LAYOUT



Notes:

This LAND LAYOUT is for reference purposes only. Please consult your manufacturing partners to ensure your company's PCB design guidelines are met.

MARKING CODE



Top View

F = Device Code

Part Number	Marking Code
AZ4120-01F.R7GR (Green Part)	F

Note. Green means Pb-free, RoHS, and Halogen free compliant.



Ordering Information

PN#	Material	Type	Reel size	MOQ	MOQ/internal box	MOQ/carton
AZ4120-01F.R7GR	Green	T/R	7 inch	12,000/reel	4 reels = 48,000/box	6 boxes = 288,000/carton

Revision History

Revision	Modification Description			
Revision 2016/02/18	Preliminary Release.			
Revision 2017/05/15	Formal Release.			