

# 8-Bit Serial-in, Parallel-out Shift Register

## 1 FEATURES

- **8-Bit Serial Input, Parallel Output Shift**
- **Power-Supply Range: 1.65V to 5.5V**
- **Low Power Consumption: 8 $\mu$ A(Max)**
- **Low Input Current: 1 $\mu$ A(Max)**
- **Gated Serial Data Input**
- **Asynchronous Master Reset**
- **Extended Temperature: -40°C to +125°C**

## 2 APPLICATIONS

- **IP Routers**
- **Programmable Logic Controllers**
- **Enterprise and Communicatios**
- **Industrial**
- **Appliances**
- **LED Displays**
- **Output Expander**

## 3 DESCRIPTIONS

The RS164 is an 8-bit serial-in/parallel-out shift register. The device features two serial data inputs (A and B), eight parallel data outputs (Q0 to Q7).


Data is entered serially through A or B and either input can be used as an active High enable for data entry through the other input. Data is shifted on the Low-to-High transitions of the clock (CLK) input. A Low on the master reset input ( $\overline{\text{CLR}}$ ) clears the register and forces all outputs Low, independently of other inputs. Inputs include clamp diodes. This enables the use of current limiting resistors to interface inputs to voltages in excess of  $V_{CC}$ .

**Device Information (1)**

| PART NUMBER | PACKAGE        | BODY SIZE (NOM) |
|-------------|----------------|-----------------|
| RS164       | SOIC-14(SOP14) | 8.65mm×3.90mm   |
|             | TSSOP-14       | 5.00mm×4.40mm   |

(1) For all available packages, see the orderable addendum at the end of the data sheet.

## 4 Functional Block Diagram



## Table of Contents

|  |    |
|--|----|
| <b>1 FEATURES</b> .....                                    | 1  |
| <b>2 APPLICATIONS</b> .....                                | 1  |
| <b>3 DESCRIPTIONS</b> .....                                | 1  |
| <b>4 Functional Block Diagram</b> .....                    | 1  |
| <b>5 Revision History</b> .....                            | 3  |
| <b>6 PACKAGE/ORDERING INFORMATION</b> <sup>(1)</sup> ..... | 4  |
| <b>7 PIN CONFIGURATIONS</b> .....                          | 5  |
| 7.1 PIN DESCRIPTION .....                                  | 5  |
| 7.2 Functional Table .....                                 | 5  |
| <b>8 SPECIFICATIONS</b> .....                              | 6  |
| 8.1 Absolute Maximum Ratings .....                         | 6  |
| 8.2 ESD Ratings .....                                      | 6  |
| 8.3 Recommended Operating Conditions .....                 | 7  |
| 8.4 ELECTRICAL CHARACTERISTICS .....                       | 7  |
| 8.5 Switching Characteristics .....                        | 8  |
| <b>9 Parameter Measurement Information</b> .....           | 10 |
| <b>10 PACKAGE OUTLINE DIMENSIONS</b> .....                 | 12 |
| <b>11 TAPE AND REEL INFORMATION</b> .....                  | 14 |

## 5 Revision History

Note: Page numbers for previous revisions may differ from page numbers in the current version.

| VERSION | Change Date | Change Item   |
|---------|-------------|---|
| A.0     | 2023/08/28  | Preliminary version completed   |
| A.1     | 2023/09/01  | 1. Update Recommended Operating Conditions<br>2. Update ELECTRICAL CHARACTERISTICS<br>3. Update Switching Characteristics |


**6 PACKAGE/ORDERING INFORMATION <sup>(1)</sup>**

| PRODUCT | ORDERING NUMBER | TEMPERATURE RANGE | PACKAGE LEAD   | PACKAGE MARKING <sup>(2)</sup> | MSL <sup>(3)</sup> | PACKAGE OPTION     |
|---------|-----------------|-------------------|----------------|--------------------------------|--------------------|--------------------|
| RS164   | RS164XP         | -40°C ~+125°C     | SOIC-14(SOP14) | RS164                          | MSL3               | Tape and Reel,4000 |
|         | RS164XQ         | -40°C ~+125°C     | TSSOP-14       | RS164                          | MSL3               | Tape and Reel,4000 |

## NOTE:

- (1) This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the right-hand navigation.
- (2) There may be additional marking, which relates to the lot trace code information (data code and vendor code), the logo or the environmental category on the device.
- (3) MSL, The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications.

## 7 PIN CONFIGURATIONS



### 7.1 PIN DESCRIPTION

| PIN                 | NAME                    | TYPE <sup>(1)</sup> | FUNCTION                                  |
|---------------------|-------------------------|---------------------|---|
| TSSOP-14/SOIC-14    |                         |                     |   |
| 1                   | A                       | I                   | Data input                                |
| 2                   | B                       | I                   | Data input                                |
| 3,4,5,6,10,11,12,13 | Q0~Q7                   | O                   | Parallel data output                      |
| 7                   | GND                     | G                   | Ground.                                   |
| 8                   | CLK                     | I                   | Clock input (Low-to-High, edge-triggered) |
| 9                   | $\overline{\text{CLR}}$ | I                   | Master reset (active Low)                 |
| 14                  | V <sub>CC</sub>         | P                   | Supply voltage                            |

(1) I=input, O=output, P=power, G=Ground.

### 7.2 Functional Table

| Operating modes | Input                   |     |   |   | Output |          |
|-----------------|-------------------------|-----|---|---|--------|----------|
|                 | $\overline{\text{CLR}}$ | CLK | A | B | Q0     | Q1 to Q7 |
| Reset (Clear)   | L                       | X   | X | X | L      | L to L   |
| Shift           | H                       | ↑   | l | l | L      | q0 to q6 |
|                 | H                       | ↑   | l | h | L      | q0 to q6 |
|                 | H                       | ↑   | h | l | L      | q0 to q6 |
|                 | H                       | ↑   | h | h | H      | q0 to q6 |

H = High voltage level

h = High voltage level one set-up time prior to the Low-to-High clock transition

L = Low voltage level

l = Low voltage level one set-up time prior to the Low-to-High clock transition

q = Lower case letters indicate the state of the referenced input one set-up time prior to the Low-to-High clock transition

↑ = Low-to-High clock transition

## 8 SPECIFICATIONS

### 8.1 Absolute Maximum Ratings

Over operating free-air temperature range (unless otherwise noted) <sup>(1)</sup>

| SYMBOL           | PARAMETER                                | CONDITION   | MIN  | MAX | UNIT |
|------------------|--|---|------|-----|------|
| V <sub>CC</sub>  | Supply Voltage Range                     |   | -0.5 | 6.5 | V    |
| I <sub>IK</sub>  | Input Clamp Current                      | V <sub>I</sub> < -0.5 V or V <sub>I</sub> > V <sub>CC</sub> + 0.5 V |      | ±20 | mA   |
| I <sub>OK</sub>  | Output Clamp Current                     | V <sub>O</sub> < -0.5V or V <sub>O</sub> > V <sub>CC</sub> +0.5V    |      | ±20 | mA   |
| I <sub>O</sub>   | Output Current                           | -0.5 V < V <sub>O</sub> < V <sub>CC</sub> + 0.5 V                   |      | ±25 | mA   |
| I <sub>CC</sub>  | Supply Current                           |   |      | 50  | mA   |
| I <sub>GND</sub> | Ground Current                           |   | -50  |     | mA   |
| θ <sub>JA</sub>  | Package thermal impedance <sup>(2)</sup> | TSSOP-14  |      | 90  | °C/W |
|                  |  | SOIC-14(SOP14)  |      | 105 |      |
| T <sub>J</sub>   | Junction Temperature <sup>(3)</sup>      |   | -40  | 150 | °C   |
| T <sub>stg</sub> | Storage Temperature                      |   | -65  | 150 |      |

(1) Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) The package thermal impedance is calculated in accordance with JESD-51.

(3) The maximum power dissipation is a function of T<sub>J(MAX)</sub>, R<sub>θJA</sub>, and T<sub>A</sub>. The maximum allowable power dissipation at any ambient temperature is P<sub>D</sub> = (T<sub>J(MAX)</sub> - T<sub>A</sub>) / R<sub>θJA</sub>. All numbers apply for packages soldered directly onto a PCB.

### 8.2 ESD Ratings

The following ESD information is provided for handling of ESD-sensitive devices in an ESD protected area only.

|                    |                         |   | VALUE | UNIT |
|--------------------|-------------------------|---|-------|------|
| V <sub>(ESD)</sub> | Electrostatic discharge | Human-body model (HBM), MIL-STD-883K METHOD 3015.9      | ±2000 | V    |
|                    |                         | Charged-device model (CDM), ANSI/ESDA/JEDEC JS-002-2018 | ±1000 |      |
|                    |                         | Machine Model (MM), JESD22-A115C (2010)                 | ±200  |      |



#### ESD SENSITIVITY CAUTION

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

### 8.3 Recommended Operating Conditions

Voltages are reference to GND(0V).

| PARAMETER   | SYMBOL      | TEST CONDITIONS         | MIN  | TYP | MAX      | UNIT |
|---|-------------|-------------------------|------|-----|----------|------|
| Supply voltage  | $V_{CC}$    |                         | 1.65 |     | 5.5      | V    |
| Input voltage   | $V_I$       |                         | 0    |     | $V_{CC}$ | V    |
| Output voltage  | $V_O$       |                         | 0    |     | $V_{CC}$ | V    |
| Input transition rise or fall rate( $\Delta t/\Delta v$ ) | Data inputs | $V_{CC}=1.65V$ to 1.95V |      |     | 20       | ns/V |
|   |             | $V_{CC}=2.3V$ to 2.7V   |      |     | 20       |      |
|   |             | $V_{CC}=3V$ to 3.6V     |      |     | 10       |      |
|   |             | $V_{CC}=4.5V$ to 5.5V   |      |     | 5        |      |
| Operating temperature                                     | $T_A$       |                         | -40  |     | 125      | °C   |

### 8.4 ELECTRICAL CHARACTERISTICS

over recommended operating free-air temperature range (unless otherwise noted)

| PARAMETER                 | SYMBOL   | TEST CONDITIONS               | $V_{CC}$      | TEMP | MIN <sup>(1)</sup>   | TYP <sup>(2)</sup> | MAX <sup>(1)</sup>   | UNIT    |
|---------------------------|----------|-------------------------------|---------------|------|----------------------|--------------------|----------------------|---------|
| High-level input voltage  | $V_{IH}$ | $V_{CC}=1.65V$ to 1.95V       |               | FULL | $0.7 \times V_{CCi}$ |                    |                      | V       |
|                           |          | $V_{CC}=2.3V$ to 2.7V         |               |      | 1.7                  |                    |                      |         |
|                           |          | $V_{CC}=3V$ to 3.6V           |               |      | 2                    |                    |                      |         |
|                           |          | $V_{CC}=4.5V$ to 5.5V         |               |      | $0.7 \times V_{CCi}$ |                    |                      |         |
| Low-level input voltage   | $V_{IL}$ | $V_{CC}=1.65V$ to 1.95V       |               | FULL |                      |                    | $0.3 \times V_{CCi}$ | V       |
|                           |          | $V_{CC}=2.3V$ to 2.7V         |               |      |                      |                    | 0.7                  |         |
|                           |          | $V_{CC}=3V$ to 3.6V           |               |      |                      |                    | 0.8                  |         |
|                           |          | $V_{CC}=4.5V$ to 5.5V         |               |      |                      |                    | $0.3 \times V_{CCi}$ |         |
| High-level output voltage | $V_{OH}$ | $V_I = V_{IH}$ or $V_{IL}$    |               |      |                      |                    |                      | V       |
|                           |          | $I_O = -100 \mu A$            | 1.65V to 5.5V | FULL | $V_{CC}-0.1$         |                    |                      |         |
|                           |          | $I_O = -4 \text{ mA}$         | 3V            |      | 1.2                  |                    |                      |         |
|                           |          | $I_O = -8 \text{ mA}$         | 3.3V          | FULL | 1.9                  |                    |                      |         |
|                           |          | $I_O = -10 \text{ mA}$        | 5.5V          |      | 3.8                  |                    |                      |         |
| Low-level output voltage  | $V_{OL}$ | $V_I = V_{IH}$ or $V_{IL}$    |               |      |                      |                    |                      | V       |
|                           |          | $I_O = 100 \mu A$             | 1.65V to 5.5V | FULL |                      |                    | 0.1                  |         |
|                           |          | $I_O = 4 \text{ mA}$          | 3V            |      |                      |                    | 0.45                 |         |
|                           |          | $I_O = 8 \text{ mA}$          | 3.3V          | FULL |                      |                    | 0.4                  |         |
|                           |          | $I_O = 10 \text{ mA}$         | 5.5V          |      |                      |                    | 0.55                 |         |
| Input leakage Current     | $I_I$    | $V_I=5.5V$ or GND             | 0V to 5.5V    | FULL |                      |                    | $\pm 1$              | $\mu A$ |
| Supply current            | $I_{CC}$ | $V_I=5.5V$ or GND;<br>$I_O=0$ | 1.65V to 5.5V | FULL |                      |                    | 8                    |         |
| Input capacitance         | $C_I$    |                               |               | 25°C |                      | 6                  |                      | pF      |

(1) Limits are 100% production tested at 25°C. Limits over the operating temperature range are ensured through correlations using statistical quality control (SQC) method.

(2) Typical values represent the most likely parametric norm as determined at the time of characterization. Actual typical values may vary over time and will also depend on the application and configuration.

## 8.5 Switching Characteristics

GND = 0 V;  $t_r = t_f = 6$  ns;  $C_L = 50$  pF; unless otherwise specified.


| SYMBOL         | PARAMETER                     | TEST CONDITIONS                         | 25°C <sup>(1)</sup> |     |     | -40°C to +125°C <sup>(1)</sup> |     |     | UNIT |
|----------------|-------------------------------|---|---------------------|-----|-----|--------------------------------|-----|-----|------|
|                |                               |   | MIN                 | TYP | MAX | MIN                            | TYP | MAX |      |
| $t_{pd}^{(2)}$ | Propagation delay             | CLK to Qn                               |                     |     |     |                                |     |     | ns   |
|                |                               | $V_{CC}=1.8V\pm 0.15V$                  |                     | 34  |     |                                |     | 68  |      |
|                |                               | $V_{CC}=2.5V\pm 0.2V$                   |                     | 24  |     |                                |     | 48  |      |
|                |                               | $V_{CC}=3.3V\pm 0.3V$                   |                     | 18  |     |                                |     | 36  |      |
|                |                               | $V_{CC}=5V\pm 0.5V$                     |                     | 14  |     |                                |     | 28  |      |
| $t_{PHL}$      | High to Low propagation delay | $\overline{CLR}$ to Qn                  |                     |     |     |                                |     |     | ns   |
|                |                               | $V_{CC}=1.8V\pm 0.15V$                  |                     | 24  |     |                                |     | 48  |      |
|                |                               | $V_{CC}=2.5V\pm 0.2V$                   |                     | 14  |     |                                |     | 28  |      |
|                |                               | $V_{CC}=3.3V\pm 0.3V$                   |                     | 10  |     |                                |     | 20  |      |
|                |                               | $V_{CC}=5V\pm 0.5V$                     |                     | 8   |     |                                |     | 16  |      |
| $t_t^{(3)}$    | transition time               | $V_{CC}=1.65V$                          |                     | 19  |     |                                |     | 60  | ns   |
|                |                               | $V_{CC}=4.5V$                           |                     | 7   |     |                                |     | 22  |      |
|                |                               | $V_{CC}=5.5V$                           |                     | 6   |     |                                |     | 20  |      |
| $t_w$          | Pulse width                   | CLK High or Low                         |                     |     |     |                                |     |     | ns   |
|                |                               | $V_{CC}=1.65V$                          | 110                 |     |     | 110                            |     |     |      |
|                |                               | $V_{CC}=4.5V$                           | 22                  |     |     | 22                             |     |     |      |
|                |                               | $V_{CC}=5.5V$                           | 19                  |     |     | 19                             |     |     |      |
|                |                               | CLR LOW                                 |                     |     |     |                                |     |     | ns   |
|                |                               | $V_{CC}=1.65V$                          | 110                 |     |     | 110                            |     |     |      |
| $V_{CC}=4.5V$  | 22                            |   |                     | 22  |     |                                |     |     |      |
|                |                               | $V_{CC}=5.5V$                           | 19                  |     |     | 19                             |     |     |      |
| $t_{rec}$      | Recovery time                 | $\overline{CLR}$ to CLK                 |                     |     |     |                                |     |     | ns   |
|                |                               | $V_{CC}=1.65V$                          | 50                  |     |     | 50                             |     |     |      |
|                |                               | $V_{CC}=4.5V$                           | 10                  |     |     | 10                             |     |     |      |
|                |                               | $V_{CC}=5.5V$                           | 9                   |     |     | 9                              |     |     |      |
| $t_{su}$       | Set-up time                   | A, and B to CLK                         |                     |     |     |                                |     |     | ns   |
|                |                               | $V_{CC}=1.65V$                          | 55                  |     |     | 55                             |     |     |      |
|                |                               | $V_{CC}=4.5V$                           | 11                  |     |     | 11                             |     |     |      |
|                |                               | $V_{CC}=5.5V$                           | 10                  |     |     | 10                             |     |     |      |
| $t_h$          | Hold width                    | A, and B to CLK                         |                     |     |     |                                |     |     | ns   |
|                |                               | $V_{CC}=1.65V$                          | 3                   |     |     | 3                              |     |     |      |
|                |                               | $V_{CC}=4.5V$                           | 3                   |     |     | 3                              |     |     |      |
|                |                               | $V_{CC}=5.5V$                           | 3                   |     |     | 3                              |     |     |      |
| $f_{max}$      | Maximum frequency             | For CLK                                 |                     |     |     |                                |     |     | MHz  |
|                |                               | $V_{CC}=1.65V$                          | 4                   |     |     | 4                              |     |     |      |
|                |                               | $V_{CC}=4.5V$                           | 20                  |     |     | 20                             |     |     |      |
|                |                               | $V_{CC}=5.5V$                           | 24                  |     |     | 24                             |     |     |      |
| $C_{PD}^{(4)}$ | Power dissipation capacitance | per package;<br>$V_I = GND$ to $V_{CC}$ |                     | 115 |     |                                |     |     | pF   |



## NOTE:


- (1) This parameter is ensured by design and/or characterization and is not tested in production.
- (2)  $t_{pd}$  is the same as  $t_{PHL}$  and  $t_{PLH}$ .
- (3)  $t_t$  is the same as  $t_{THL}$  and  $t_{TLH}$ .
- (4)  $C_{PD}$  is used to determine the dynamic power dissipation ( $P_D$  in  $\mu W$ ).  
 $P_D = C_{PD} \times V_{CC}^2 \times f_i \times N + \sum (C_L \times V_{CC}^2 \times f_o)$  where:  
 $f_i$  = input frequency in MHz;  
 $f_o$  = output frequency in MHz;  
 $\sum (C_L \times V_{CC}^2 \times f_o)$  = sum of outputs;  
 $C_L$  = output load capacitance in pF;  
 $V_{CC}$  = supply voltage in V;  
 $N$  = number of inputs switching.

## 9 Parameter Measurement Information




$V_{OL}$  and  $V_{OH}$  are typical voltage output levels that occur with the output load.

**Figure 1. Waveforms showing the clock (CLK) to output (Qn) propagation delays, the clock pulse width, the output transition times and the maximum clock frequency**




$V_{OL}$  and  $V_{OH}$  are typical voltage output levels that occur with the output load.

**Figure 2. Waveforms showing the master reset ( $\overline{CLR}$ ) pulse width, the master reset to output (Qn) propagation delays and the master reset to clock (CLK) removal time**



$V_{OL}$  and  $V_{OH}$  are typical voltage output levels that occur with the output load. The shaded areas indicate when the input is permitted to change for predictable output performance.

**Figure 3. Waveforms showing the data set-up and hold times for A and B inputs**



Test data is given in Table 1.

Definitions test circuit:

$R_T$  = termination resistance should be equal to output impedance  $Z_o$  of the pulse generator.

$C_L$  = load capacitance including jig and probe capacitance.



**Figure 4. Test circuit for measuring switching times**

**Table 1. Test data**



| TEST              | Input    |            | Load       |
|-------------------|----------|------------|------------|
|                   | $V_i$    | $t_r, t_f$ | $C_L$      |
| $t_{PHL}/t_{PLH}$ | $V_{CC}$ | 6ns        | 15pF, 50pF |

# 10 PACKAGE OUTLINE DIMENSIONS

## SOIC-14(SOP14)<sup>(3)</sup>







RECOMMENDED LAND PATTERN (Unit: mm)



| Symbol            | Dimensions In Millimeters |       | Dimensions In Inches      |       |
|-------------------|---------------------------|-------|---------------------------|-------|
|                   | Min                       | Max   | Min                       | Max   |
| A <sup>(1)</sup>  |                           | 1.750 |                           | 0.069 |
| A1                | 0.100                     | 0.250 | 0.004                     | 0.010 |
| A2                | 1.300                     | 1.500 | 0.051                     | 0.059 |
| b                 | 0.390                     | 0.470 | 0.015                     | 0.019 |
| c                 | 0.200                     | 0.240 | 0.008                     | 0.009 |
| D <sup>(1)</sup>  | 8.550                     | 8.750 | 0.336                     | 0.344 |
| e                 | 1.270(BSC) <sup>(2)</sup> |       | 0.050(BSC) <sup>(2)</sup> |       |
| E                 | 5.800                     | 6.200 | 0.228                     | 0.244 |
| E1 <sup>(1)</sup> | 3.800                     | 4.000 | 0.150                     | 0.157 |
| L                 | 0.500                     | 0.800 | 0.020                     | 0.031 |
| $\theta$          | 0°                        | 8°    | 0°                        | 8°    |

NOTE:

1. Plastic or metal protrusions of 0.15mm maximum per side are not included.
2. BSC (Basic Spacing between Centers), "Basic" spacing is nominal.
3. This drawing is subject to change without notice.

**TSSOP-14 (3)**

**RECOMMENDED LAND PATTERN (Unit: mm)**



| Symbol           | Dimensions In Millimeters |       | Dimensions In Inches      |       |
|------------------|---------------------------|-------|---------------------------|-------|
|                  | Min                       | Max   | Min                       | Max   |
| A <sup>(1)</sup> |                           | 1.200 |                           | 0.047 |
| A1               | 0.050                     | 0.150 | 0.002                     | 0.006 |
| A2               | 0.900                     | 1.050 | 0.035                     | 0.041 |
| b                | 0.200                     | 0.300 | 0.008                     | 0.012 |
| c                | 0.130                     | 0.170 | 0.005                     | 0.007 |
| D <sup>(1)</sup> | 4.860                     | 5.100 | 0.191                     | 0.201 |
| E <sup>(1)</sup> | 4.300                     | 4.500 | 0.169                     | 0.177 |
| E1               | 6.200                     | 6.600 | 0.244                     | 0.260 |
| e                | 0.650(BSC) <sup>(2)</sup> |       | 0.026(BSC) <sup>(2)</sup> |       |
| L                | 0.450                     | 0.750 | 0.018                     | 0.030 |
| H                | 0.250(TYP)                |       | 0.010(TYP)                |       |
| $\theta$         | 0°                        | 8°    | 0°                        | 8°    |

**NOTE:**


1. Plastic or metal protrusions of 0.15mm maximum per side are not included.
2. BSC (Basic Spacing between Centers), "Basic" spacing is nominal.
3. This drawing is subject to change without notice.

# 11 TAPE AND REEL INFORMATION

## REEL DIMENSIONS



## TAPE DIMENSION



NOTE: The picture is only for reference. Please make the object as the standard.

## KEY PARAMETER LIST OF TAPE AND REEL

| Package Type   | Reel Diameter | Reel Width (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P0 (mm) | P1 (mm) | P2 (mm) | W (mm) | Pin1 Quadrant |
|----------------|---------------|-----------------|---------|---------|---------|---------|---------|---------|--------|---------------|
| SOIC-14(SOP14) | 13"           | 16.4            | 6.60    | 9.30    | 2.10    | 4.0     | 8.0     | 2.0     | 16.0   | Q1            |
| TSSOP-14       | 13"           | 12.4            | 6.95    | 5.60    | 1.20    | 4.0     | 8.0     | 2.0     | 12.0   | Q1            |

NOTE:

1. All dimensions are nominal.
2. Plastic or metal protrusions of 0.15mm maximum per side are not included.

## **IMPORTANT NOTICE AND DISCLAIMER**

Jiangsu Runic Technology Co., Ltd. will accurately and reliably provide technical and reliability data (including data sheets), design resources (including reference designs), application or other design advice, WEB tools, safety information and other resources, without warranty of any defect, and will not make any express or implied warranty, including but not limited to the warranty of merchantability Implied warranty that it is suitable for a specific purpose or does not infringe the intellectual property rights of any third party.

These resources are intended for skilled developers designing with Runic products You will be solely responsible for: (1) Selecting the appropriate products for your application; (2) Designing, validating and testing your application; (3) Ensuring your application meets applicable standards and any other safety, security or other requirements; (4) Runic and the Runic logo are registered trademarks of Runic Incorporated. All trademarks are the property of their respective owners; (5) For change details, review the revision history included in any revised document. The resources are subject to change without notice. Our company will not be liable for the use of this product and the infringement of patents or third-party intellectual property rights due to its use.